



## Ordering guide

### Product Code

**TC152-12TP**

TC152-12TP Transformer

Project:

Location:

Cat.No:

Type:

Lamps:

Qty:

Notes:

## Specifications

### Housing

Housing and cover are polyester powdercoated steel with removable door. Internal transformer is epoxy encapsulated. Exterior Mounting - Transformer should be mounted on the wall, structure, or post in the vertical position. Cable entries should be positioned downward.

### Electrical Assembly

The transformer is thermally protected and is shielded between the 120V input and the low voltage output, for safety. Insulation type transformers for safe operation. 6-ft heavy-duty 18-3 AWG, 105° C, SJT power cord with 3 prong grounded wall plug. Voltage control switch: Low = 11.5V, High = 12.5V. Euro-Board terminal block for easy low voltage cable attachment. Line voltage amperage draw: 150VA = .9AMP. Includes integral timer and photocell. 50/60Hz input. Consult factory for details.

### Warranty

Ten-year limited warranty.

### Height

11 1/4" (286mm)

### Width

3 1/2" (89mm)

### Depth

3 3/4" (95mm)

