

Defining general purpose LED downlights

Philips Lightolier LyteCaster LED downlight and adjustable luminaires provide comfortable, quality illumination. LyteCaster's shallow frame height fits into tight plenum spaces and the adaptable design makes it a versatile lighting option.

Benefits

- Frame construction: The frame is includes 90° swivel mounting bar points and offset holes for applications close to joints for easy installation.
- Shallow luminaire height: The shallow 3.5" luminaire height saves plenum space making it ideal in residential and light commercial installations.
- Modular and innovative light engine: An interchangeable and upgradeable modular light engine provides an easy install.
- LyteCaster LED with WarmGlow (2700K- 2200K):
 Provides characteristics of an incandescent lamp when dimmed and is an alternative to a BR30 65W incandescent luminaire.
- Adjustable gimbal design: Low cost solution for slope ceiling and wall washing applications.
- Wet location listed: No need for special lens design.
 Great for bathrooms and shower installations.
- · Remodeler kit: Ideal for renovation spaces



LyteCaster LED

Available in 3 aperture sizes: 4", 5", & 6". The 4" round delivers 650 and 1000 lumens, and 4" square delivers 1000 lumens. The 5" round delivers 1000 and 15000 lumens, and 5" square delivers 1000 lumens. A 5" round is also available with WarmGlow that delivers 700 lumens. The 6" round delivers 1500 and 2000 lumens, and 6" square delivers 1500 lumens.

example: L5S15AE1VA

example: L5S15927VA

Features

- · Trims: Rounds & Squares
- · Lumens: 600 2000lm
- Watts: 7 20 W
- Efficacy: Up to 90lm/W
- · CCT: 2700K, 3000K, 3500K. 4000K, and WarmGlow
- · CRI: 80, 90
- · Dimming: ELV, 0-10V
- Voltage: 120V, 120V/277V
- · Lifetime: 50,000 hrs
- · Warranty: 5 years

Frame-In kit (downlight & adjustable) match series and lumens with	ith light engine
--	------------------

Series	Delivered lui	nens	Housing*	Dimming / Voltage / Version	
L4R LyteCaster LED 4" round L5R LyteCaster LED 5" round	- 650lm - 1000lm	10 1000lm	A NC with screws AN NC with nails	E1VA ELV / 120V / Version A Z10UVA 0-10V / Universal 120V-277V	
L6R LyteCaster LED 6" round	— 1500lm	20 2000lm	R Remodeler	/ Version A	
L4S LyteCaster LED 4" square		10 850lm	A NC with screws		
L5S LyteCaster LED 5" square		15 1000lm	AN NC with nails		
L6S LyteCaster LED 6" square		20 1500lm			
L5R LyteCaster LED 5" round	— 700lm		A NC with screws	EWG1 ELV & Triac / 120V / WarmGlow	
			AN NC with nails		
L5R LyteCaster LED 5" round		07 700lm	R Remodeler		

Light engine (downlight only) select frame-In kit and trim.

Series	Delivered lumens		CRI / CCT / Version	
L4R LyteCaster LED 4" round	- 650lm	10 1000lm	827VA 80CRI / 2700K / Version A	
L5R LyteCaster LED 5" round	— 1000lm	15 1500lm	830VA 80CRI / 3000K / Version A	
L6R LyteCaster LED 6" round	— 1500lm	20 2000lm	835VA 80CRI / 3500K / Version A 840VA 80CRI / 4000K / Version A	
L4S LyteCaster LED 4" square		10 850lm	927VA 80CRI / 2700K / Version A	
L5S LyteCaster LED 5" square		15 1000lm		
L6S LyteCaster LED 6" square		20 1500lm		
L5R LyteCaster LED 5" round		07 700lm	8WG 80CRI / 2700K - 2200K / WarmGlow	

Trim (downlight: three-part system) or Light Engine & Trim (adjustable: two-part system) example: L5SDD

Seri	es	Shape / Style	Type / Finish (downlight) or Lumen, CRI/CCT, Finish (adjustable)
L4 L5 L6	LyteCaster LED 4" LyteCaster LED 5" LyteCaster LED 6"	R Round downlight S Square downlight	DD Open downlight / Clear diffuse (with white flange) DW Open downlight / White (with white flange) BW Baffle downlight / White (with white flange)
L4	LyteCaster LED 4"	RA Round adjustable	06WVA 650lm (CRI/CCT) White (with white flange) Version A 10WVA 1000lm (CRI/CCT) White (with white flange) Version A
L5	LyteCaster LED 5"	RA Round adjustable	10WVA 1000lm (CRI/CCT) White (with white flange) Version A 15WVA 1500lm (CRI/CCT) White (with white flange) Version A
L6	LyteCaster LED 6"	RA Round adjustable	15 WVA 1500lm (CRI/CCT) White (with white flange) Version A 20 WVA 2000lm (CRI/CCT) White (with white flange) Version A

 $^{^{\}ast}$ New construction (NC) and remodeler housings are AirSeal IC.







Visit philips.com/warranties for more information on the standard 5-year limited warranty.

© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Philips Lighting Canada Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008