

HADCO

by  Signify

Landscape

TC654-15

TC654-15 Transformer



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering Guide

Example: TC654-15

Product Code	TC654-15	Transformer
--------------	----------	-------------

Specifications

HOUSING:

Housing is dark gray polyester powder-coat formed steel case with stainless steel screws and lockable captive door, hinged on side. Weather-proof compartment for plug-in time clock and photo cell. 1/2" Knockout on one side for hardwiring or accessory mounting. Internal transformer is epoxy encapsulated. Exterior Mounting - Transformer should be mounted on the wall, structure, or post in the vertical position. Cable entries should be positioned downward.

ELECTRICAL ASSEMBLY:

6-ft heavy-duty 18-3 AWG, 105° C, SJT power cord with 3 prong grounded wall plug. The transformer is thermally protected on primary, and secondary side is protected by circuit breaker. Shielded between primary and secondary. Insulation type transformers for safe operation. Euro-Board terminal block for easy low voltage cable attachment. Line voltage amperage draw: 600VA = 5.5 amps. 12, 13, 14, and 15 volt output taps for design flexibility and longer cable run capability. 2 sets of taps. Four (4) 1/2" knockouts for low-voltage exit, on bottom of housing. One (1) 1-1/2" conduit inlet. 50/60Hz input. Consult factory for details.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. NEMA 3R Rated

WARRANTY:

Ten-year limited warranty.

Height :

12 1/2" (318mm)

Width:

6 3/4" (171mm)

Depth:

6" (152mm)

Max. Weight:

21.08 lb

