


Lumec offers high-quality tunnel, overpass, highmast, and security luminaires designed specifically for these applications to address a variety of roadway lighting needs.

### Tunnel & Overpass



	Best	Best	Best	Best
Product	TunnelView Small	TunnelView Medium	TunnelView Large	TubeLine
Prefix	TULS	TULM	TULL	TBL
Lumen Output Range	Up to 13,450	Up to 26,222	Up to 53,876	Up to 17,956
Efficacy	Up to 134 LPW	Up to 137 LPW	Up to 140 LPW	Up to 125 LPW
Distribution	R2M, TW2,DK, R3M, R3W, 4.5, SN, CBL	R2M, TW2,DK, R3M, R3W, 4.5, SN, CBL	R2M, TW2,DK, R3M, R3W, 4.5, SN, CBL	DTA, DTA-NB, DTA-WB, DTS, DTS-NB, DTS-WB
Color Temperature	2700K, 3000K, 4000K	2700K, 3000K, 4000K	2700K, 3000K, 4000K	3000K, 4000K
Mounting Height Range	10' - 20'	15 - 25'	15' - 35'	15' 25'
Mounting Bracket	Od, N5d, N10d, P5d, P10d, P15d, SLF, SV	Od, N5d, N10d, P5d, P10d, P15d, SLF, SV	Od, N5d, N10d, P5d, P10d, P15d, SLF, SV	Od1, Od2, SV
Rotatable Optical Assembly	✓	✓	✓	✓
Remote install Tool-Less 7 Pin	✓	✓	✓	-
DALI	✓	✓	✓	✓
Sensor Ready Driver	✓	✓	✓	✓
Sensor Ready Receptacle (TLRSR)	✓	✓	✓	✓
Service Tag	✓	✓	✓	✓
Photocell	PH8, PH8/347, PH8480, PH8XL	PH8, PH8/347, PH8480, PH8XL	PH8, PH8/347, PH8480, PH8XL	PH8, PH8/347, PH8480, PH8XL
Receptacle	TLRD7	TLRD7	TLRD7	-
NYX Emera Ready	✓	✓	✓	✓
API (Factory Installed NEMA Label)	✓	✓	✓	✓
Additional Surge Protection	✓	✓	✓	✓
Fusing	✓	✓	✓	✓
Junction Box (JB1, JB2)	✓	✓	✓	✓
Finish	Black, Bronze, Grey	Black, Bronze, Grey	Black, Bronze, Grey	Grey
IP Rating	IP66	IP66	IP66	IP66
Vibration	3G	3G	3G	3G
DLC Listing	Premium	Premium	Premium	Premium
Certifications	cUL	cUL	cUL	cUL
Lifetime Per TM21	L70 > 37,000 hours	L70 > 37,000 hours	L70 > 37,000 hours	L70 > 36,000 hours
Limited Warranty	10 years	10 years	10 years	10 years
Link				

### Highmast



	Best
Product	HighFocus Plus
Prefix	HFP
Lumen Output Range	139,000
Efficacy	191 LPW
Distribution	1, 4, 5N, 5M, 5W, R2M, R3M
Color Temperature	3000K, 4000K, 5000K
Mounting Height Range	40' - 150'
0 Uplight	✓
Rotatable Optical Assembly	✓
Service Tag	✓
Photocell	PH8, PH8/347, PH8/480, PH8XL
Receptacle	TLRD7
Shielding	CSS, FSS, HSS, LSS, RSS
Additional Surge Protection	✓
Fusing	✓
Finish	Black, Bronze, Grey, White
IP Rating	IP66
Vibration	3G
DLC Listing	Premium
Certifications	Dark Skies, cUL
Lifetime Per TM21	L70 > 100,000 hrs
Limited Warranty	10 years
Link	

### Security



	Best
Product	RoadFocus Plus Roadway Security Light
Prefix	RPRS
Lumen Output Range	Up to 13,120
Efficacy	Up to 184 LPW
Distribution	4, 5, R2M, R3M
Color Temperature	2700K, 3000K, 4000K
Mounting Height Range	15' - 35'
0 Uplight	✓ (without refractor)
Service Tag	✓
Photocell	PH8, PHXL
Receptacle	TLRD7, TLRSR
Shielding	CSS, FSS, HSS, LSS, RSS
Additional Surge Protection	SP1, SP1X, SP2, SP2x
Finish	Not painted (Standard), Optional colors
IP Rating	IP66
Vibration	3G
DLC Listing	Premium
Certifications	Dark Skies, cUL
Lifetime Per TM21	L70 > 77,000 hrs
Limited Warranty	5 years, 10 years with SP1
Link	