

## CUSTOMIZE YOUR LINEAR SYSTEM indoor



### P22

P22 è un profilo lineare in alluminio anodizzato naturale adatto per le applicazioni in interni.  
P22 is a natural anodized aluminum linear profile for indoor applications.

#### INFORMAZIONI GENERALI GENERAL INFORMATION

Dimensioni Dimensions	max 3m
Colore/finitura apparecchio Luminaire color/finish	alluminio anodizzato anodized aluminium

#### FINITURA FINISHING


**AA** Alluminio anodizzato naturale / Natural anodized aluminium

#### NASTRI LED COMPATIBILI COMPATIBLE LED STRIPS

<b>N07</b>	LED strip bianca / White LED strip
<b>N17</b>	LED strip bianca / White LED strip
<b>N09</b>	LED strip bianca / White LED strip
<b>N10</b>	LED strip bianca / White LED strip
<b>N11</b>	LED strip bianca / White LED strip
<b>N06</b>	LED strip bianco dinamico 24VDC / Tunable white LED strip 24VDC
<b>N13</b>	LED strip RGB / RGB LED strip
<b>N14</b>	LED strip RGB / RGB LED strip
<b>N15</b>	LED strip RGBW / RGBW LED strip

#### DISEGNO TECNICO DIMENSIONAL DRAWINGS

Dimensioni (mm)  
Dimensions (mm)




#### SCHERMI COMPATIBILI COMPATIBLE SCREENS

**S02** Schermo opale / Opal screen




#### FISSAGGIO FIXATION


**F01**  
Plafone/ceiling



**F09**  
Parete/wall



**F02**  
Sospensione/suspension



**F08**  
Incasso trimless/recessed trimless

