

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED CANDLE & LUSTRE DESIGNED FOR ATMOSPHERE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⊗
non dimmable



MZD LED 25W E14 827 B35 FR ND

12NC: **929001253032**
EAN1: **3139188161351**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W E27 827 P45 FR ND

12NC: **929001253332**
EAN1: **3139188161399**

4 WATT **25** WATT **2700 K**
250 lm

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 25W E14 827 B35 FR ND	B35	4	15000	2700	250	35 x 103	929001253032	3139188161351
MZD LED 25W B35 E14 CW FR ND	B35	3	15000	4000	250	35 x 103	929001359432	3139188162549
MZD LED 25W B35 E14 CDL FR ND	B35	3	15000	6500	250	35 x 103	929001388832	3139188162563
MZD LED 25W E27 827 P45 FR ND	P45	4	15000	2700	250	45 x 79	929001253332	3139188161399
MZD LED 25W E14 827 P45 FR ND	P45	4	15000	2700	250	45 x 84	929001253232	3139188161375
MZD LED 25W P45 E14 CW FR ND	P45	4	15000	4000	250	45 x 84	929001263832	3139188162822
MZD LED 25W P45 E14 CDL FR ND	P45	3	15000	6500	250	45 x 84	929001388932	3139188162587
MZD LED 25W B35 E14 827 CL ND 1CT/10	B35	2	20000	2700	250	35x97	929001238332	3139188163942
MZD LED 25W B35 E14 840 CL ND 1CT/10	B35	2	20000	4000	250	35x97	929002215232	3139188164123
MZD LEDCLA 25W P45 E14 827 CL ND 1CT/10	P45	2	20000	2700	250	45x80	929001238632	3139188163881
MZD LED 25W B35 E14 840 CL ND 1CT/10	P45	2	20000	4000	250	45x80	929002215132	3139188164109

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED CANDLE & LUSTRE DESIGNED FOR ATMOSPHERE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⊗
non dimmable



**MZD LED 40W P45 E14
WW FR ND 1CT/10**

12NC: **929001253732**
EAN1: **3139188162785**

6 WATT > **40** WATT
2700 K
470 lm

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 40W B35 E14 WW FR ND 1CT/10	B35	6	15000	2700	470	35 x 103	929001253632	3139188162723
MZD LED 40W B35 E14 CW FR ND 1CT/10	B35	5	15000	4000	470	35 x 103	929001263732	3139188162884
MZD LED 40W B35 E14 CDL FR ND 1CT/10	B35	5	15000	6500	470	35 x 103	929001389032	3139188162686
MZD LED 40W P45 E27 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 79	929001253832	3139188162808
MZD LED 40W P45 E14 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 84	929001253732	3139188162785
MZD LED 40W P45 E27 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 79	929001264032	3139188162860
MZD LED 40W P45 E14 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 84	929001263932	3139188162846
MZD LED 40W P45 E27 CDL FR ND 1CT/10	P45	5	15000	6500	470	45 x 79	929001389232	3139188162624
MZD LED 40W P45 E14 CDL FR ND 1CT/10	P45	5	15000	6500	470	45 x 84	929001389132	3139188162600
MZD LEDCLA 40W B35 E14 827 CL ND 1CT/10	B35	5	20000	2700	470	35 x 97	929001889732	3139188163966
MZD LEDCLA 40W B35 E14 840 CL ND 1CT/10	B35	5	20000	4000	470	35 x 97	929002214932	3139188163980
MZD LEDCLA 40W P45 E14 827 CL ND 1CT/10	P45	5	20000	2700	470	45 x 80	929001890432	3139188163904
MZD LED 40W P45 E14 840 CL ND 1CT/10	P45	5	20000	4000	470	45 x 80	929002214632	3139188163928



**MZD LEDCLA 40W P45 E14
827 CL ND 1CT/10**

12NC: **929001890432**
EAN1: **3139188163904**

5 WATT > **40** WATT

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED CANDLE & LUSTRE DESIGNED FOR ATMOSPHERE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⊗
non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 60W B35 E14 827 FR ND 1CT/10	B35	8	15000	2700	806	39 x 114	929001907632	3139188163201
MZD LED 60W B35 E14 840 FR ND 1CT/10	B35	8	15000	4000	806	39 x 114	929001907732	3139188163225
MZD LED 60W B35 E14 865 FR ND 1CT/10	B35	8	15000	6500	806	39 x 114	929001907832	3139188163249
MZD LEDCLA 60W B35 E14 827 CL ND 1CT/10	B35	6	20000	2700	806	35 x 97	929002215332	3139188164147
MZD LED 60W B35 E14 840 CL ND 1CT/10	B35	6	20000	4000	806	35 x 97	929002215432	3139188164161



**MZD LED 60W B35 E14
827 FR ND 1CT/10**

12NC: **929001907632**
EAN1: **3139188163201**

8 WATT **60** WATT **2700 K**
806 lm



**MZD LED 60W B35 E14
827 FR ND 1CT/10**

12NC: **929001907632**
EAN1: **3139188163201**

8 WATT **60** WATT **2700 K**
806 lm