

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED SPOTS

SPOTLIGHT ON STYLE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⊗
non dimmable

Product type	Lamp type	LED	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
		W		°		mA	Hz	mm		
MZD LEDspot50W GU10Kit_R 827 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040532	3139188163423
MZD LEDspot50W GU10Kit_R 840 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040732	3139188163447
MZD LEDspot50W GU10Kit_S 827 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040632	3139188163461
MZD LEDspot50W GU10Kit_S 840 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040832	3139188163485
MZD LED 50W GU10 827 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001250432	3139188161252
MZD LED 50W GU10 840 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001247032	3139188162662
MZD LED 50W GU10 865 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001259132	3139188162648
MZD LED 50W GU10 WH 60D ND 1CT/10	PAR16	4.7	5	60	15000	38	50	50 x 55	929001912232	3139188161276
MZD LED 50W GU10 CW 60D ND 1CT/10	PAR16	4.7	5	60	15000	38	50	50 x 55	929001912332	3139188161290
MZD LED 65W GU10 827 36D ND 1CT/10	PAR16	6	6	36	15000	48	50	50 x 56	929001371132	3139188161634
MZD LED 65W GU10 840 36D ND 1CT/10	PAR16	5.5	6	36	15000	44	50	50 x 56	929001371232	3139188161658
MZD LED 350lm GU10 840 120D ND 1CT/10	PAR16	4.5	6	120	15000	40	50	50 x 58	929001358532	3139188161672
MZD LED 500lm GU10 827 120D ND 1CT/10	PAR16	6	6	120	15000	58	50	50 x 56	929001372032	3139188161719
MZD LED 500lm GU10 840 120D ND 1CT/10	PAR16	5	5	120	15000	50	50	50 x 58	929001358632	3139188161696
MZD LED 500lm GU10 865 120D ND 1CT/10	PAR16	5	5	120	15000	50	50	50 x 58	929001372132	3139188161733
MZD LED 720lm GU10 830 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093332	3139188163584
MZD LED 720lm GU10 840 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093432	3139188163607
MZD LED 720lm GU10 865 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093532	3139188163621



**MZD LEDspot50W
GU10Kit_R 827 36D 1CT/10**

12NC: **929002040532**
EAN1: **3139188163423**

5 WATT **50** WATT **2700 K**
345 lm



**MZD LED 500lm GU10
840 120D ND 1CT/10**

12NC: **929001358632**
EAN1: **3139188161696**

5 WATT **4000 K**
500 lm

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED SPOTS

SPOTLIGHT ON STYLE

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
15,000h

⊗
non dimmable

Product type	Lamp type	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 35W GU5.3 827 12V 36D ND 1CT/10	MR16	6	36	15000	550	50	50 x 46	929001210932	3139188161832
MZD LED 35W GU5.3 840 12V 36D ND 1CT/10	MR16	6	36	15000	550	50	50 x 46	929001245932	3139188161856
MZD LED 50W GU5.3 827 12V 36D ND 1CT/10	MR16	8	36	15000	710	50	50 x 44	929001912632	3139188163287
MZD LED 50W GU5.3 840 12V 36D ND 1CT/10	MR16	8	36	15000	710	50	50 x 44	929001912732	3139188163263
MZD LED 50W GU5.3 830 12V 60D ND 1CT/10	MR16	8	60	15000	700	50	50 x 44	929001912432	3139188161313
MZD LED 50W GU5.3 840 12V 60D ND 1CT/10	MR16	8	60	15000	700	50	50 x 44	929001912532	3139188161337



**MZD LED 35W GU5.3
827 12V 36D ND 1CT/10**

12NC: **929001210932**
EAN1: **3139188161832**

4.5 WATT **35** WATT **2700 K**
345 lm



**MZD LED 50W GU5.3
840 12V 36D ND 1CT/10**

12NC: **929001912732**
EAN1: **33139188163263**

7.5 WATT **50** WATT **4000 K**
621 lm