

Since
1894
Sauter

BEAUTIFUL LIGHT, BUILT TO PERFORM

 MAZDA

GREAT LIGHT SOLID DESIGN



6

Indoor
luminaires



10

Outdoor
luminaires



16

Bulbs



22

Candles
& Lustrés



30

Spots



34

Tubes

There's an art to creating a quality lighting scheme that exceeds your customers' expectations - without going over their budget. Now you can master it beautifully with MAZDA's portfolio of LED lamps and MAZDA's recently introduced luminaires.

QUALITY WHEN IT COUNTS

The MAZDA name has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting. From retail and residential projects to commercial and industrial installations, they have been developed to meet the challenging requirements of a wide range of lighting applications.

We've designed our range using the very latest LED technology, from classic bulbs and elegant candles to hand-working tubes and directional spots. The MAZDA portfolio now also offers indoor and outdoor luminaires to meet your customer's needs. So you can promise your customers excellent performance and efficiency from their lighting installation, with instant energy savings.

They'll love the light quality too. With a choice of lumens, color temperatures and beam angles, our high quality LED solutions create the perfect ambience for every space. Light that's designed to create a great first impression, with value that lasts.



MASTERING LIGHT SINCE 1894

MAZDA has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting:

- Engineered for performance
- Up to 35,000 hours reliable lifetime
- Superb light quality
- Save up to 85% energy



A modern office interior featuring a glass-walled meeting room. Inside the room, there is a desk with a computer monitor and two office chairs. The room is illuminated by track lighting on the ceiling. A large, semi-transparent green circle is overlaid on the image, and a green diagonal line runs across it. The floor is made of light-colored wood.

LUMINAIRES

MAZDA INDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS

Instant energy savings with MAZDA's range of luminaires.

- Instant energy savings
- 2 years warranty
- 35,000 hours lifetime

PANELS



NEW

MAZDA RC007B LED32S/840
PSU W60L60 NOC

12NC: **911401801280**
EAN1: **8710163340180**

4000 K
3200 lm



NEW

MAZDA RC007B LED12S/840
PSU W30L30 NOC

12NC: **911401801380**
EAN1: **8710163340197**

4000 K
1200 lm

INDOOR BATTENS & WALLMOUNTS



MAZDA BN007C LED32S/840
PSU L1200

12NC: **911401800480**
EAN1: **8710163338040**

1200 mm
IP20



MAZDA WL007C LED14S/740
PSU OVL WH

12NC: **911401800780**
EAN1: **8710163338071**

IP65 / IK06
Silver trim included




MAZDA WL007C LED13S/740
PSU RND MDU WH

12NC: **911401800880**
EAN1: **8710163338088**

IP54 / IK06
Silver trim included
Motion sensor


INDOOR WATERPROOF



MAZDA WT007C LED17S/740
PSU L600

12NC: **911401800980**
EAN1: **8710163338774**


600 mm
IP65 / IK06



MAZDA WT007C LED34S/740
PSU L1200

12NC: **911401800580**
EAN1: **8710163338057**

1200 mm
IP65 / IK06



MAZDA WT007C LED54S/740
PSU L1500

12NC: **911401800680**
EAN1: **8710163338064**

1500 mm
IP65 / IK06

DOWNLIGHTS



MZD DN020B LED12/830
16W 220-240V WH

12NC: **929002219402**
EAN1: **3139188163645**

3000 K
1200 lm



MZD DN020B LED12/840
16W 220-240V WH

12NC: **929002219502**
EAN1: **3139188163669**

4000 K
1200 lm



MZD DN020B LED12/865
16W 220-240V WH

12NC: **929002219602**
EAN1: **3139188163683**

6500 K
1200 lm

DOWNLIGHTS



MZD DN020B LED20/830
24W 220-240V WH

12NC: **929002219702**
EAN1: **3139188163706**

3000 K
2000 lm



MZD DN020B LED20/840
24W 220-240V WH

12NC: **929002219802**
EAN1: **3139188163720**

4000 K
2000 lm



MZD DN020B LED20/865
24W 220-240V WH

12NC: **929002219902**
EAN1: **3139188163744**

6500 K
2000 lm

SPOTS



MZD SL252 EC RD 070
3W 27K W HV 06

12NC: **929002222432**
EAN1: **3139188164000**

2700 K
200 lm



MZD SL252 EC RD 070
3W 40K W HV 06

12NC: **929002222532**
EAN1: **3139188164024**

4000 K
210 lm



MZD SL252 EC RD 070 5W
27K W HV 06

12NC: **929002222632**
EAN1: **3139188164048**

2700 K
330 lm



MZD SL252 EC RD 070 5W
40K W HV 06

12NC: **929002222732**
EAN1: **3139188164062**

4000 K
350 lm

A
EEI label

A⁺
EEI label

80
CRI


220-240 Vac


15,000h


non dimmable

Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
	lm	W	K					
Batten								
MAZDA BN007C LED32S/840 PSU L1200	3200	32	4000	IP20		I	911401800480	8710163338040
Wallmount								
MAZDA WL007C LED14S/740 PSU OVL WH	1400	15	4000	IP65 / IK06		II	911401800880	8710163338088
MAZDA WL007C LED13S/740 PSU RND MDU WH	1300	15	4000	IP54 / IK06	Yes	II	911401800780	8710163338071
Waterproof								
MAZDA WT007C LED17S/740 PSU L600	1700	17	4000	IP65 / IK06		II	911401800980	8710163338774
MAZDA WT007C LED34S/740 PSU L1200	3400	34	4000	IP65 / IK06		II	911401800580	8710163338057
MAZDA WT007C LED54S/740 PSU L1500	5400	54	4000	IP65 / IK06		II	911401800680	8710163338064
Downlights								
MZD DN020B LED12/830 16W 220-240V WH	1200	16	3000	IP20 / IK03		II	929002219402	3139188163645
MZD DN020B LED12/840 16W 220-240V WH	1200	16	4000	IP20 / IK03		II	929002219502	3139188163669
MZD DN020B LED12/865 16W 220-240V WH	1200	16	6500	IP20 / IK03		II	929002219602	3139188163683
MZD DN020B LED20/830 24W 220-240V WH	2000	24	3000	IP20 / IK03		II	929002219702	3139188163706
MZD DN020B LED20/840 24W 220-240V WH	2000	24	4000	IP20 / IK03		II	929002219802	3139188163720
MZD DN020B LED20/865 24W 220-240V WH	2000	24	6500	IP20 / IK03		II	929002219902	3139188163744
Spots								
MZD SL252 EC RD 070 3W 27K W HV 06	200	3	2700	IP20 / IK03		II	929002222432	3139188164000
MZD SL252 EC RD 070 3W 40K W HV 06	210	3	4000	IP20 / IK03		II	929002222532	3139188164024
MZD SL252 EC RD 070 5W 27K W HV 06	330	5	2700	IP20 / IK03		II	929002222632	3139188164048
MZD SL252 EC RD 070 5W 40K W HV 06	350	5	4000	IP20 / IK03		II	929002222732	3139188164062

A⁺⁺
EEI label

80
CRI


220-240 Vac


35,000h



non dimmable

Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
	lm	W	K					
Panels								
MAZDA RC007B LED32S/840 PSU W60L60 NOC	3200	36	4000	IP20		II	911401801280	8710163340180
MAZDA RC007B LED12S/840 PSU W30L30 NOC	1200	15	4000	IP20		II	911401801380	8710163340197

NEW

MAZDA OUTDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS

Instant energy savings with MAZDA's range of luminaires.



- Instant energy savings
- 2 years warranty
- 35,000 hours lifetime

OUTDOOR FLOODLIGHTS



MAZDA BVP007
10W 4000K

12NC: **911401737432**
EAN1: **8710163337371**

IP65 / IK06



MAZDA BVP007
20W 4000K

12NC: **911401737442**
EAN1: **8710163337388**

IP65 / IK06



MAZDA BVP007
50W 4000K

12NC: **911401737452**
EAN1: **8710163337395**

IP65 / IK06



MAZDA BVP007
20W 4000K MDU

12NC: **911401741582**
EAN1: **8710163338200**

IP65 / IK06

Motion sensor



MAZDA BVP007
50W 4000K MDU

12NC: **911401741592**
EAN1: **8710163338217**

IP65 / IK06

Motion sensor

MAZDA OUTDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS



	Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
		lm	W	K					
NEW	MAZDA BVP007 10W 4000K	850	10	4000	IP65 / IK06		I	911401737432	8710163337371
NEW	MAZDA BVP007 20W 4000K	1700	20	4000	IP65 / IK06		I	911401737442	8710163337388
NEW	MAZDA BVP007 50W 4000K	4250	50	4000	IP65 / IK06		I	911401737452	8710163337395
NEW	MAZDA BVP007 20W 4000k MDU	1700	20	4000	IP65 / IK06	Yes	I	911401741582	8710163338200
NEW	MAZDA BVP007 50W 4000k MDU	4250	50	4000	IP65 / IK06	Yes	I	911401741592	8710163338217





LAMPS

MAZDA LED BULBS INSTANT ENERGY SAVINGS

With MAZDA's
range of LED bulbs
you can create
exactly the right
ambience.

- Classic bulb shape
- Frosted or clear finish
- 2700K, 4000K or 6500K
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy

INDOOR BULBS



MZD LED 40W E27 840
A60 ND 1CT/6

12NC: **929002060332**
EAN1: **3139188161436**

5 WATT > **40** WATT **4000 K**
500 lm



MZD LED 40W E27 827
A60 ND 1CT/6

12NC: **929002061732**
EAN1: **3139188161412**

5 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W A60 E27
CDL FR ND 1CT/6

12NC: **929002060732**
EAN1: **3139188162266**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 60W A60 E27
827 FR ND 1CT/6

12NC: **929001913132**
EAN1: **3139188161450**

9 WATT > **60** WATT **2700 K**
806 lm



MZD LED 60W A60 B22
WW FR ND RF 1BC 1CT/6

12NC: **929001913532**
EAN1: **3139188162969**

9 WATT > **60** WATT **2700 K**
806 lm



MZD LED 60W A60 E27
CDL FR ND 1CT/6

12NC: **929001913432**
EAN1: **3139188162327**

9 WATT > **60** WATT **6500 K**
806 lm



MZD LED 60W A60 E27
840 FR ND 1CT/6

12NC: **929001913332**
EAN1: **3139188161474**

9 WATT > **60** WATT **4000 K**
806 lm



MZD LED 75W A60 E27
827 FR ND 1CT/6

12NC: **929001365532**
EAN1: **3139188161498**

11 WATT > **75** WATT **2700 K**
1055 lm



MZD LED 75W A60 E27
840 FR ND 1CT/6

12NC: **929001365632**
EAN1: **3139188161511**

10 WATT > **75** WATT **4000 K**
1055 lm



MZD LED 75W A60 E27
865 FR ND 1CT/6

12NC: **929001359132**
EAN1: **3139188162488**

10 WATT > **75** WATT **6500 K**
1055 lm



MZD LED 100W E27 827
A67 FR ND 1CT/6

12NC: **929001252932**
EAN1: **3139188161535**

14 WATT **100** WATT **2700 K**
1521 lm



MZD LED 100W A60 E27
CDL FR ND 1CT/6

12NC: **929001359232**
EAN1: **3139188162501**

14 WATT **100** WATT **6500 K**
1521 lm



MZD LEDCLA 40W A60 E27
827 CL ND 1CT/10

12NC: **929001890032**
EAN1: **3139188163768**

5 WATT **40** WATT **2700 K**
470 lm



MZD LEDCLA 40W A60 E27
840 CL ND 1CT/10

12NC: **929002214432**
EAN1: **3139188163782**

5 WATT **40** WATT **4000 K**
470 lm



MZD LEDCLA 60W A60 E27
827 CL ND 1CT/10

12NC: **929001387332**
EAN1: **3139188163805**

7 WATT **60** WATT **2700 K**
806 lm



MZD LEDCLA 60W A60 E27
840 CL ND 1CT/10

12NC: **929002062532**
EAN1: **3139188163829**

7 WATT **60** WATT **4000 K**
806 lm



MZD LEDCLA 75W A60 E27
827 CL ND 1CT/10

MZD LEDCLA 75W A60 E27
840 CL ND 1CT/10

12NC: **929002061032**
EAN1: **3139188163843**

12NC: **929002060432**
EAN1: **3139188163867**

8 WATT **75** WATT **2700 K**
1055 lm

8 WATT **75** WATT **4000 K**
1055 lm



MZD LEDCLA 100W A70 E27
827 CL ND 1CT/10

MZD LEDCLA 100W A70 E27
840 CL ND 1CT/10

12NC: **929002062132**
EAN1: **3139188164086**

12NC: **929002214132**
EAN1: **3139188164208**

11 WATT **100** WATT **2700 K**
1521 lm

11 WATT **100** WATT **4000 K**
1521 lm

MAZDA LED BULBS INSTANT ENERGY SAVINGS



80
CRI

⚡
220-240 Vac

🕒
15,000h

⚠️
non dimmable

Product type	Lamp Type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm			
MZD LED 40W E27 840 A60 ND 1CT/6	A60	5	15000	4000	470	60 x 105	929002060332	3139188161436
MZD LED 40W E27 827 A60 ND 1CT/6	A60	5	15000	2700	470	60 x 105	929002061732	3139188161412
MZD LED 40W A60 E27 865 FR ND 1CT/6	A60	5	15000	6500	470	60 x 105	929002060732	3139188162266
MZD LED 40W A60 E27 827 FR ND 2CT/5*	A60	5	15000	2700	470	60 x 105	929002061733	3139188163560
MZD LED 40W A60 E27 840 FR ND 2CT/5*	A60	5	15000	4000	470	60 x 105	929002060333	3139188163546
MZD LED 60W A60 E27 827 FR ND 1CT/6	A60	9	15000	2700	806	60 x 105	929001913132	3139188161450
MZD LED 60W A60 E27 827 FR ND 2CT/5*	A60	9	15000	2700	806	60 x 105	929001913133	3139188163508
MZD LED 60W A60 B22 827 FR ND 1CT/6	A60	9	15000	2700	806	60 x 105	929001913532	3139188162969
MZD LED 60W A60 E27 865 FR ND 1CT/6	A60	9	15000	6500	806	60 x 105	929001913432	3139188162327
MZD LED 60W A60 E27 840 FR ND 1CT/6	A60	9	15000	4000	806	60 x 105	929001913332	3139188161474
MZD LED 60W A60 E27 840 FR ND 2CT/5*	A60	9	15000	4000	806	60 x 105	929001913333	3139188163522
MZD LED 75W A60 E27 827 FR ND 1CT/6	A60	11	15000	2700	1055	60 x 120	929001365532	3139188161498
MZD LED 75W A60 E27 840 FR ND 1CT/6	A60	10	15000	4000	1055	60 x 120	929001365632	3139188161511
MZD LED 75W A60 E27 865 FR ND 1CT/6	A60	10	15000	6500	1055	60 x 120	929001359132	3139188162488
MZD LED 100W E27 827 A67 FR ND 1CT/6	A67	14	15000	2700	1521	60 x 120	929001252932	3139188161535
MZD LED 100W A60 E27 865 FR ND 1CT/6	A67	14	15000	6500	1521	60 x 120	929001359232	3139188162501
MZD LEDCLA 40W A60 E27 827 CL ND 1CT/10	A60	5	20000	2700	470	60 x 104	929001890032	3139188163768
MZD LEDCLA 40W A60 E27 840 CL ND 1CT/10	A60	5	20000	4000	470	60 x 104	929002214432	3139188163782
MZD LEDCLA 60W A60 E27 827 CL ND 1CT/10	A60	7	20000	2700	806	60 x 104	929001387332	3139188163805
MZD LEDCLA 60W A60 E27 840 CL ND 1CT/10	A60	7	20000	4000	806	60 x 104	929002062532	3139188163829
MZD LEDCLA 75W A60 E27 827 CL ND 1CT/10	A60	8	20000	2700	1055	60 x 104	929002061032	3139188163843
MZD LEDCLA 75W A60 E27 840 CL ND 1CT/10	A60	8	20000	4000	1055	60 x 104	929002060432	3139188163867
MZD LEDCLA 100W A70 E27 827 CL ND 1CT/10	A70	11	20000	2700	1521	70 x 126	929002062132	3139188164086
MZD LED 100W A67 E27 840 FR ND 1CT/6	A67	14	15000	4000	1521	65x120	929002214132	3139188164208

* Multipack

MAZDA LED CANDLES & LUSTRE DESIGNED FOR ATMOSPHERE

With an elegant design and frosted finish, our LED candles also offer significant energy savings.

- Elegant shape
- Frosted finish
- 2700K or 4000K
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy

INDOOR CANDLES & LUSTRES



MZD LED 25W E14 827
B35 FR ND

12NC: **929001253032**
EAN1: **3139188161351**

4 WATT	25 WATT	2700 K
		250 lm



MZD LED 25W B35 E14
CW FR ND

12NC: **929001359432**
EAN1: **3139188162549**

3 WATT	25 WATT	4000 K
		250 lm



MZD LED 25W B35 E14
CDL FR ND

12NC: **929001388832**
EAN1: **3139188162563**

3 WATT	25 WATT	6500 K
		250 lm



MZD LED 25W E27 827
P45 FR ND

12NC: **929001253332**
EAN1: **3139188161399**

4 WATT	25 WATT	2700 K
		250 lm



MZD LED 25W E14 827
P45 FR ND

12NC: **929001253232**
EAN1: **3139188161375**

4 WATT	25 WATT	2700 K
		250 lm



MZD LED 25W P45 E14
CW FR ND

12NC: **929001263832**
EAN1: **3139188162822**

4 WATT	25 WATT	4000 K
		250 lm



MZD LED 25W P45 E14
CDL FR ND

12NC: **929001388932**
EAN1: **3139188162587**

3 WATT	25 WATT	6500 K
		250 lm



MZD LED 40W B35 E14
WW FR ND 1CT/10

12NC: **929001253632**
EAN1: **3139188162723**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W B35 E14
CW FR ND 1CT/10

12NC: **929001263732**
EAN1: **3139188162884**

5 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W B35 E14
CDL FR ND 1CT/10

12NC: **929001389032**
EAN1: **3139188162686**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 40W P45 E27
WW FR ND 1CT/10

12NC: **929001253832**
EAN1: **3139188162808**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E14
WW FR ND 1CT/10

12NC: **929001253732**
EAN1: **3139188162785**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E27
CW FR ND 1CT/10

12NC: **929001264032**
EAN1: **3139188162860**

6 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W P45 E14
CW FR ND 1CT/10

12NC: **929001263932**
EAN1: **3139188162846**

6 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W P45 E27
CDL FR ND 1CT/10

12NC: **929001389232**
EAN1: **3139188162624**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 40W P45 E14
CDL FR ND 1CT/10

12NC: **929001389132**
EAN1: **3139188162600**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 60W B35 E14
827 FR ND 1CT/10

12NC: **929001907632**
EAN1: **3139188163201**

8 WATT **60** WATT **2700 K**
806 lm



MZD LED 60W B35 E14
840 FR ND 1CT/10

12NC: **929001907732**
EAN1: **3139188163225**

8 WATT **60** WATT **4000 K**
806 lm



MZD LED 60W B35 E14
865 FR ND 1CT/10

12NC: **929001907832**
EAN1: **3139188163249**

8 WATT **60** WATT **6500 K**
806 lm



MZD LEDCLA 25W B35 E14
827 CL ND 1CT/10

12NC: **929001238332**
EAN1: **3139188163942**

2 WATT > **25** WATT **2700 K**
250 lm



MZD LED 25W B35 E14
840 CL ND 1CT/10

12NC: **929002215232**
EAN1: **3139188164123**

2 WATT > **25** WATT **4000 K**
250 lm



MZD LEDCLA 25W P45 E14
827 CL ND 1CT/10

12NC: **929001238632**
EAN1: **3139188163881**

2 WATT > **25** WATT **2700 K**
250 lm



MZD LED 25W B35 E14
840 CL ND 1CT/10

12NC: **929002215132**
EAN1: **3139188164109**

2 WATT > **25** WATT **4000 K**
250 lm



MZD LEDCLA 40W B35 E14
827 CL ND 1CT/10

12NC: **929001889732**
EAN1: **3139188163966**

5 WATT > **40** WATT **2700 K**
470 lm



MZD LEDCLA 40W B35 E14
840 CL ND 1CT/10

12NC: **929002214932**
EAN1: **3139188163980**

5 WATT > **40** WATT **4000 K**
470 lm



MZD LEDCLA 40W P45 E14
827 CL ND 1CT/10

12NC: **929001890432**
EAN1: **3139188163904**

5 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E14
840 CL ND 1CT/10

12NC: **929002214632**
EAN1: **3139188163928**

5 WATT > **40** WATT **4000 K**
470 lm



MZD LEDCLA 60W B35 E14
827 CL ND 1CT/10

12NC: **929002215332**
EAN1: **3139188164147**

6 WATT > **60** WATT **2700 K**
806 lm



MZD LED 60W B35 E14
840 CL ND 1CT/10

12NC: **929002215432**
EAN1: **3139188164161**

6 WATT > **60** WATT **4000 K**
806 lm

MAZDA LED CANDLES & LUSTRE DESIGNED FOR ATMOSPHERE



A⁺

EEI label

80

CRI



220-240 Vac



15,000h



non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 25W E14 827 B35 FR ND 1CT/10	B35	4	15000	2700	250	35 x 103	929001253032	3139188161351
MZD LED 25W B35 E14 840 FR ND 1CT/10	B35	3	15000	4000	250	35 x 103	929001359432	3139188162549
MZD LED 25W B35 E14 865 FR ND 1CT/10	B35	3	15000	6500	250	35 x 103	929001388832	3139188162563
MZD LED 25W E27 827 P45 FR ND 1CT/10	P45	4	15000	2700	250	45 x 79	929001253332	3139188161399
MZD LED 25W E14 827 P45 FR ND 1CT/10	P45	4	15000	2700	250	45 x 84	929001253232	3139188161375
MZD LED 25W P45 E14 840 FR ND 1CT/10	P45	4	15000	4000	250	45 x 84	929001263832	3139188162822
MZD LED 25W P45 E14 865 FR ND 1CT/10	P45	3	15000	6500	250	45 x 84	929001388932	3139188162587
MZD LEDCLA 25W B35 E14 827 CL ND 1CT/10	B35	2	20000	2700	250	35x97	929001238332	3139188163942
MZD LEDCLA 25W B35 E14 840 CL ND 1CT/10	B35	2	20000	4000	250	35x97	929002215232	3139188164123
MZD LEDCLA 25W P45 E14 827 CL ND 1CT/10	P45	2	20000	2700	250	45x80	929001238632	3139188163881
MZD LEDCLA 25W P45 E14 840 CL ND 1CT/10	P45	2	20000	4000	250	45x80	929002215132	3139188164109

A⁺
EEI label80
CRI
220-240 Vac
15,000h
non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 40W B35 E14 827 FR ND 1CT/10	B35	6	15000	2700	470	35 x 103	929001253632	3139188162723
MZD LED 40W B35 E14 840 FR ND 1CT/10	B35	5	15000	4000	470	35 x 103	929001263732	3139188162884
MZD LED 40W B35 E14 865 FR ND 1CT/10	B35	5	15000	6500	470	35 x 103	929001389032	3139188162686
MZD LED 40W P45 E27 827 FR ND 1CT/10	P45	6	15000	2700	470	45 x 79	929001253832	3139188162808
MZD LED 40W P45 E14 827 FR ND 1CT/10	P45	6	15000	2700	470	45 x 84	929001253732	3139188162785
MZD LED 40W P45 E27 840 FR ND 1CT/10	P45	6	15000	4000	470	45 x 79	929001264032	3139188162860
MZD LED 40W P45 E14 840 FR ND 1CT/10	P45	6	15000	4000	470	45 x 84	929001263932	3139188162846
MZD LED 40W P45 E27 865 FR ND 1CT/10	P45	5	15000	6500	470	45 x 79	929001389232	3139188162624
MZD LED 40W P45 E14 865 FR ND 1CT/10	P45	5	15000	6500	470	45 x 84	929001389132	3139188162600
MZD LEDCLA 40W B35 E14 827 CL ND 1CT/10	B35	5	20000	2700	470	35 x 97	929001889732	3139188163966
MZD LEDCLA 40W B35 E14 840 CL ND 1CT/10	B35	5	20000	4000	470	35 x 97	929002214932	3139188163980
MZD LEDCLA 40W P45 E14 827 CL ND 1CT/10	P45	5	20000	2700	470	45 x 80	929001890432	3139188163904
MZD LEDCLA 40W P45 E14 840 CL ND 1CT/10	P45	5	20000	4000	470	45 x 80	929002214632	3139188163928

A⁺
EEI label80
CRI
220-240 Vac
15,000h
non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 60W B35 E14 827 FR ND 1CT/10	B35	8	15000	2700	806	39 x 114	929001907632	3139188163201
MZD LED 60W B35 E14 840 FR ND 1CT/10	B35	8	15000	4000	806	39 x 114	929001907732	3139188163225
MZD LED 60W B35 E14 865 FR ND 1CT/10	B35	8	15000	6500	806	39 x 114	929001907832	3139188163249
MZD LEDCLA 60W B35 E14 827 CL ND 1CT/10	B35	6	20000	2700	806	35 x 97	929002215332	3139188164147
MZD LEDCLA 60W B35 E14 840 CL ND 1CT/10	B35	6	20000	4000	806	35 x 97	929002215432	3139188164161

MAZDA LED SPOTS

SPOTLIGHT ON STYLE

Create warm or cool lighting accents with our range of LED spotlights to highlight interior décor or architectural features.

- Direction or wide beam options
- 2700K, 3000K and 4000K, 6500K
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy

INDOOR SPOTS



MZD LEDspot50W
GU10Kit_R 827 36D 1CT/10

12NC: **929002040532**
EAN1: **3139188163423**

5 WATT	50 WATT	2700 K
		345 lm



MZD LEDspot50W
GU10Kit_R 840 36D 1CT/10

12NC: **929002040732**
EAN1: **3139188163447**

5 WATT	50 WATT	4000 K
		380 lm



MZD LEDspot50W
GU10Kit_S 827 36D 1CT/10

12NC: **929002040632**
EAN1: **3139188163461**

5 WATT	50 WATT	2700 K
		345 lm



MZD LEDspot50W
GU10Kit_S 840 36D 1CT/10

12NC: **929002040832**
EAN1: **3139188163485**

5 WATT	50 WATT	4000 K
		380 lm



MZD LED 50W GU10
827 36D ND 1CT/10

12NC: **929001250432**
EAN1: **3139188161252**

5 WATT	50 WATT	2700 K
		345 lm



MZD LED 50W GU10
840 36D ND 1CT/10

12NC: **929001247032**
EAN1: **3139188162662**

5 WATT	50 WATT	4000 K
		380 lm



MZD LED 50W GU10
865 36D ND 1CT/10

12NC: **929001259132**
EAN1: **3139188162648**

5 WATT	50 WATT	6500 K
		380 lm



MZD LED 50W GU10 WH
60D ND 1CT/10

12NC: **929001912232**
EAN1: **3139188161276**

5 WATT	50 WATT	3000 K
		345 lm



MZD LED 50W GU10 CW
60D ND 1CT/10

12NC: **929001912332**
EAN1: **3139188161290**

5 WATT	50 WATT	4000 K
		360 lm



MZD LED 65W GU10
827 36D ND 1CT/10

12NC: **929001371132**
EAN1: **3139188161634**

5.5 WATT **65** WATT **2700 K**
490 lm



MZD LED 65W GU10
840 36D ND 1CT/10

12NC: **929001371232**
EAN1: **3139188161658**

5.5 WATT **65** WATT **4000 K**
500 lm



MZD LED 350lm GU10
840 120D ND 1CT/10

12NC: **929001358532**
EAN1: **3139188161672**

5.5 WATT **4000 K**
350 lm



MZD LED 500lm GU10
827 120D ND 1CT/10

12NC: **929001372032**
EAN1: **3139188161719**

5.5 WATT **2700 K**
500 lm



MZD LED 500lm GU10
840 120D ND 1CT/10

12NC: **929001358632**
EAN1: **3139188161696**

5 WATT **4000 K**
500 lm



MZD LED 500lm GU10
865 120D ND 1CT/10

12NC: **929001372132**
EAN1: **3139188161733**

5 WATT **6500 K**
500 lm



MZD LED 720lm GU10
830 120D ND 1CT/10

12NC: **929002093332**
EAN1: **3139188163584**

3000 K
720 lm



MZD LED 720lm GU10
840 120D ND 1CT/10

12NC: **929002093432**
EAN1: **3139188163607**

4000 K
720 lm



MZD LED 720lm GU10
865 120D ND 1CT/10

12NC: **929002093532**
EAN1: **3139188163621**

6500 K
720 lm



MZD LED 35W GU5.3
827 12V 36D ND 1CT/10

12NC: **929001210932**
EAN1: **3139188161832**

4.5 WATT **35** WATT **2700 K**
345 lm



MZD LED 35W GU5.3
840 12V 36D ND 1CT/10

12NC: **929001245932**
EAN1: **3139188161856**

4.5 WATT **35** WATT **4000 K**
380 lm



MZD LED 50W GU5.3
827 12V 36D ND 1CT/10

12NC: **929001912632**
EAN1: **3139188163287**

7.5 WATT **50** WATT **2700 K**
621 lm



MZD LED 50W GU5.3
840 12V 36D ND 1CT/10

12NC: **929001912732**
EAN1: **33139188163263**

7.5 WATT **50** WATT **4000 K**
621 lm



MZD LED 50W GU5.3 830
12V 60D ND 1CT/10

12NC: **929001912432**
EAN1: **3139188161313**

7.5 WATT **50** WATT **3000 K**
621 lm



MZD LED 50W GU5.3 840
12V 60D ND 1CT/10

12NC: **929001912532**
EAN1: **3139188161337**

7.5 WATT **50** WATT **4000 K**
621 lm

*Wattage equivalence cannot be claimed as, due to their wide beam (120D) these spots are not directional lamps



Product type	Lamp type	LED	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
		W		°		mA	Hz	mm		
MZD LEDspot50W GU10Kit_R 827 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040532	3139188163423
MZD LEDspot50W GU10Kit_R 840 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040732	3139188163447
MZD LEDspot50W GU10Kit_S 827 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040632	3139188163461
MZD LEDspot50W GU10Kit_S 840 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040832	3139188163485
MZD LED 50W GU10 827 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001250432	3139188161252
MZD LED 50W GU10 840 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001247032	3139188162662
MZD LED 50W GU10 865 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001259132	3139188162648
MZD LED 50W GU10 WH 60D ND 1CT/10	PAR16	4.7	5	60	15000	38	50	50 x 55	929001912232	3139188161276
MZD LED 50W GU10 CW 60D ND 1CT/10	PAR16	4.7	5	60	15000	38	50	50 x 55	929001912332	3139188161290
MZD LED 65W GU10 827 36D ND 1CT/10	PAR16	6	6	36	15000	48	50	50 x 56	929001371132	3139188161634
MZD LED 65W GU10 840 36D ND 1CT/10	PAR16	5.5	6	36	15000	44	50	50 x 56	929001371232	3139188161658
MZD LED 350lm GU10 840 120D ND 1CT/10	PAR16	4.5	6	120	15000	40	50	50 x 58	929001358532	3139188161672
MZD LED 500lm GU10 827 120D ND 1CT/10	PAR16	6	6	120	15000	58	50	50 x 56	929001372032	3139188161719
MZD LED 500lm GU10 840 120D ND 1CT/10	PAR16	5	5	120	15000	50	50	50 x 58	929001358632	3139188161696
MZD LED 500lm GU10 865 120D ND 1CT/10	PAR16	5	5	120	15000	50	50	50 x 58	929001372132	3139188161733
MZD LED 720lm GU10 830 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093332	3139188163584
MZD LED 720lm GU10 840 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093432	3139188163607
MZD LED 720lm GU10 865 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093532	3139188163621



Product type	Lamp type	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 35W GU5.3 827 12V 36D ND 1CT/10	MR16	6	36	15000	550	50	50 x 46	929001210932	3139188161832
MZD LED 35W GU5.3 840 12V 36D ND 1CT/10	MR16	6	36	15000	550	50	50 x 46	929001245932	3139188161856
MZD LED 50W GU5.3 827 12V 36D ND 1CT/10	MR16	8	36	15000	710	50	50 x 44	929001912632	3139188163287
MZD LED 50W GU5.3 840 12V 36D ND 1CT/10	MR16	8	36	15000	710	50	50 x 44	929001912732	3139188163263
MZD LED 50W GU5.3 830 12V 60D ND 1CT/10	MR16	8	60	15000	700	50	50 x 44	929001912432	3139188161313
MZD LED 50W GU5.3 840 12V 60D ND 1CT/10	MR16	8	60	15000	700	50	50 x 44	929001912532	3139188161337

MAZDA LED TUBES FOR BRIGHTER LIGHTING

Our LED tubes provide high quality light to illuminate any space.

- 600mm, 1200mm and 1500mm lengths
- 4000K and 6500K
- Instant start
- 25,000 hours lifetime
- Save up to 55% energy

INDOOR TUBES



MZD LEDtube 600mm
8W 840

12NC: **929001855632**
EAN1: **8718696717455**

8 WATT > **18** WATT **4000 K**
800 lm



MZD LEDtube 600mm
8W 865

12NC: **929001855732**
EAN1: **8718696717479**

8 WATT > **18** WATT **6500 K**
800 lm



MZD LED tube 1200mm
14.5W 840

12NC: **929001855832**
EAN1: **8718696717417**

14.5 WATT > **36** WATT **4000 K**
1600 lm



MZD LEDtube 1200mm
14.5W 865

12NC: **929001855932**
EAN1: **8718696717431**

14.5 WATT > **36** WATT **6500 K**
1600 lm



MZD LEDtube 1500mm
20W 840

12NC: **929001855432**
EAN1: **8718696717370**

20 WATT > **58** WATT **4000 K**
2200 lm



MZD LEDtube 1500mm
20W 865

12NC: **929001855532**
EAN1: **8718696717394**

20 WATT > **58** WATT **6000 K**
2200 lm



MZD LED PLC7
5W 840

12NC: **929001879032**
EAN1: **3139188162983**

7.5 WATT > **13** WATT **4000 K**
806 lm



MZD LED PLC
7.5W 865

12NC: **929001879132**
EAN1: **3139188163003**

7.5 WATT > **13** WATT **6500 K**
806 lm



MZD LED PLC
9W 840

12NC: **929001879332**
EAN1: **3139188163027**

9 WATT > **18** WATT **4000 K**
1050 lm



MZD LED PLC
9W 865

12NC: **929001879432**
EAN1: **3139188163041**

9 WATT > **18** WATT **6500 K**
1050 lm

MAZDA LED TUBES FOR BRIGHTER LIGHTING



TSHAPES



MZD LED 26-24W E27
830 HB 1CT/6



MZD LED 28-24W E27
840 HB 1CT/6



MZD LED 48-42W E27
830 HB 1CT/6



MZD LED 50-42W E27
840 HB 1CT/6

12NC: **929001937632**
EAN1: **3139188164260**

24 WATT **40** WATT **3000 K**
2600 lm

12NC: **929001937732**
EAN1: **3139188164284**

24 WATT **40** WATT **4000 K**
2800 lm

12NC: **929001938232**
EAN1: **3139188164222**

42 WATT **70** WATT **3000 K**
4800 lm

12NC: **929001938332**
EAN1: **3139188164246**

42 WATT **70** WATT **4000 K**
5000 lm



Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LEDtube 600mm 8W 840	LEDtube	8	38	50/60	604h / 27,80ø	929001855632	871869671745500
MZD LEDtube 600mm 8W 865	LEDtube	8	38	50/60	604h / 27,80ø	929001855732	871869671747900
MZD LEDtube 1200mm 14.5W 840	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	871869671741700
MZD LEDtube 1200mm 14.5W 865	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	871869671743100
MZD LEDtube 1500mm 20W 840	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855432	871869671737000
MZD LEDtube 1500mm 20W 865	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855532	871869671739400




Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LED PLC 7.5W 840 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879032	3139188162983
MZD LED PLC 7.5W 865 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879132	3139188163003
MZD LED PLC 9W 840 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879332	3139188163027
MZD LED PLC 9W 865 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879432	3139188163041



Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LED 26-24W E27 830 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	x	3139188164260
MZD LED 28-24W E27 840 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	x	3139188164284
MZD LED 48-42W E27 830 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	x	3139188164222
MZD LED 50-42W E27 840 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	x	3139188164246

GREAT LIGHT SOLID DESIGN





Engineered for performance
Up to 35,000 hours reliable lifetime
Superb light quality
Save up to 85% energy

MAZDA | I.B.R.S. / C.C.R.I. Numéro 10461 | 5600 VB Eindhoven, the Netherlands | WWW.MAZDALIGHTING.COM

© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

 **MAZDA**