

LUMINÁRIAS DE INTERIOR MAZDA

POUPANÇA ENERGÉTICA INSTANTÂNEA



**MZD DN020B LED12/865
16W 220-240V WH**

12NC: **929002219602**
EOC: **16368300**
1200lm
6500K
20.000 horas
IP20



**MZD DL252 LED17/840
20W RD 220-240V 06**

12NC: **929002357932**
EOC: **54031300**
1750lm
25.000 horas

Tipo de producto	Flujo luminoso	Consumo energético	Temperatura de cor	IP / IK	Sensor de movimento	Classe I/II	12NC	EOC
	lm	W	K					
Slim Downlights								
MZD DN020B LED12/830 16W 220-240V WH	1200	16	3000	IP20 / IK03		II	929002219402	16364500
MZD DN020B LED12/840 16W 220-240V WH	1200	16	4000	IP20 / IK03		II	929002219502	16366900
MZD DN020B LED12/865 16W 220-240V WH	1200	16	6500	IP20 / IK03		II	929002219602	16368300
MZD DN020B LED20/830 24W 220-240V WH	2000	24	3000	IP20 / IK03		II	929002219702	16370600
MZD DN020B LED20/840 24W 220-240V WH	2000	24	4000	IP20 / IK03		II	929002219802	16372000
MZD DN020B LED20/865 24W 220-240V WH	2000	24	6500	IP20 / IK03		II	929002219902	16374400
UltraSlim Downlight								
NOVO MZD DL252 LED6/830 9W RD 220-240V 06	630	9	3000	IP20 / IK03		II	929002357532	54033700
MZD DL252 LED6/840 9W RD 220-240V 06	630	9	4000	IP20 / IK03		II	929002357632	54035100
MZD DL252 LED17/830 20W RD 220-240V 06	1750	20	3000	IP20 / IK03		II	929002357832	54029000
MZD DL252 LED17/840 20W RD 220-240V 06	1750	20	4000	IP20 / IK03		II	929002357932	54031300
Downlight de superfície								
NOVO MZD DN027C LED9/830 11W 220V D175 RD	950	11					929002034132	54037500
MZD DN027C LED9/840 11W 220V D175 RD	1000	11					929002034232	54039900
MZD DN027C LED19/830 23W 220V D225 RD	1900	23					929002035032	54041200
MZD DN027C LED19/840 23W 220V D225 RD	2000	23					929002035132	54043600

LUMINARIAS DE INTERIOR MAZDA

POUPANÇA ENERGÉTICA INSTANTÂNEA



MZD SL252 EC RD 070
3W 27K W HV 06

12NC: **929002222432**
EOC: **16400000**

200lm
2700K
20.000 horas

Tipo de producto	Flujo luminoso	Consumo energético	Temperatura de cor	IP / IK	Sensor de movimento	Classe I/II	12NC	EOC
	lm	W	K					
Accent								
MZD SL252 EC RD 070 3W 27K W HV 06	200	3	2700	IP20 / IK03		II	929002222432	16400000
MZD SL252 EC RD 070 3W 40K W HV 06	210	3	4000	IP20 / IK03		II	929002222532	16402400
MZD SL252 EC RD 070 5W 27K W HV 06	330	5	2700	IP20 / IK03		II	929002222632	16404800
MZD SL252 EC RD 070 5W 40K W HV 06	350	5	4000	IP20 / IK03		II	929002222732	16406200
NOVO MZD RS251 EC RD 075 6.8W 827	500	6.8					929002256632	54025200
NOVO MZD RS251 EC RD 075 6.8W 840	500	6.8					929002256732	54027600



NOVO

MZD RS251 EC RD 075
6.8W 840

12NC: **929002256732**

EOC: **54027600**
500lm
25.000 horas