

# MAZDA LED SPOTS

## PUNTOS DE LUZ CON ESTILO

A<sup>+</sup>  
EEI label

80  
CRI

⚡  
220-240 Vac

🕒  
15,000h

⚠️  
No regulable

Tipo de producto	Forma	LED	Consumo energía	Ángulo de apertura	Número de encendidos	Input actual	Frecuencia	Dimensión W x H	12NC	EOC
		W		°		mA	Hz	mm		
MZD LEDspot50W GU10Kit_R 827 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040532	16342300
MZD LEDspot50W GU10Kit_R 840 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040732	16344700
MZD LEDspot50W GU10Kit_S 827 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040632	16346100
MZD LEDspot50W GU10Kit_S 840 36D 1CT/10	PAR16	4.7	4,7	36	50000	38	50	91 x 91	929002040832	16348500
MZD LED 50W GU10 827 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001250432	16125200
MZD LED 50W GU10 840 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001247032	16266200
MZD LED 50W GU10 865 36D ND 1CT/10	PAR16	4.7	5	36	15000	38	50	50 x 54	929001259132	16264800
MZD LED 50W GU10 WH 60D ND 1CT/10	PAR16	4.7	5	60	15000	38	50	50 x 55	929001912232	16127601
MZD LED 50W GU10 CW 60D ND 1CT/10	PAR16	4.7	5	60	15000	38	50	50 x 55	929001912332	16129001
MZD LED 65W GU10 827 36D ND 1CT/10	PAR16	6	6	36	15000	48	50	50 x 56	929001371132	16163400
MZD LED 65W GU10 840 36D ND 1CT/10	PAR16	5.5	6	36	15000	44	50	50 x 56	929001371232	16165800
MZD LED 500lm GU10 827 120D ND 1CT/10	PAR16	6	6	120	15000	58	50	50 x 56	929001372032	16171900
MZD LED 500lm GU10 840 120D ND 1CT/10	PAR16	5	5	120	15000	50	50	50 x 58	929001358632	16169600
MZD LED 500lm GU10 865 120D ND 1CT/10	PAR16	5	5	120	15000	50	50	50 x 58	929001372132	16173300
MZD LED 720lm GU10 830 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093332	16358400
MZD LED 720lm GU10 840 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093432	16360700
MZD LED 720lm GU10 865 120D ND 1CT/10	PAR16	7.5	8	120	15000	56	50	58h / 50φ	929002093532	16362100



MZD LEDspot50W  
GU10Kit\_R 827 36D 1CT/10

12NC: **929002040532**  
EOC: **16342300**

**5** WATT **50** WATT **2700 K**  
**345 lm**



MZD LED 500lm GU10  
840 120D ND 1CT/10

12NC: **929001358632**  
EOC: **16169600**

**5** WATT **4000 K**  
**500 lm**

GREAT LIGHT,  
SOLID DESIGN

# MAZDA LED SPOTS

## PUNTOS DE LUZ CON ESTILO

A<sup>+</sup>  
EEI label

80  
CRI

⚡  
220-240 Vac

🕒  
15,000h

⚠️  
No regulable

Tipo de producto	Forma	Consumo de energía	Ángulo de apertura	Número encendidos	Input actual	Frecuencia	Dimensión W x H	12NC	EOC
			°		mA	Hz	mm		
MZD LED 50W GU5.3 830 12V 60D ND 1CT/10	MR16	8	60	15000	700	50	50 x 44	929001912432	16131301
MZD LED 50W GU5.3 840 12V 60D ND 1CT/10	MR16	8	60	15000	700	50	50 x 44	929001912532	16133701



MZD LED 50W GU5.3  
WH 12V 60D ND 1CT/10

12NC: 929001212432  
EOC: 16131301

8 WATT > 50 WATT 3000 K  
621 lm



MZD LED 50W GU5.3  
CW 12V 60D ND 1CT/10

12NC: 929001912532  
EOC: 16133701

8 WATT > 50 WATT 4000 K  
630 lm