

# MAZDA LED VELAS Y ESFÉRICAS DISEÑADAS PARA CREAR AMBIENTE

**A<sup>+</sup>**  
EEI label

**80**  
CRI

**⚡**  
220-240 Vac

**🕒**  
15,000h

**⊗**  
No regulable

Tipo de producto	Forma	Consumo energía	Número de encendidos	Temperatura de color	Flujo luminoso	Dimensiones W x H	12NC	EOC
				K	lm	mm		
MZD LED 25W E14 827 B35 FR ND	B35	4	15000	2700	250	35 x 103	929001253032	16135100
MZD LED 25W B35 E14 CW FR ND	B35	3	15000	4000	250	35 x 103	929001359432	16254900
MZD LED 25W B35 E14 CDL FR ND	B35	3	15000	6500	250	35 x 103	929001388832	16256300
MZD LED 25W E27 827 P45 FR ND	P45	4	15000	2700	250	45 x 79	929001253332	16139900
MZD LED 25W E14 827 P45 FR ND	P45	4	15000	2700	250	45 x 84	929001253232	16137500
MZD LED 25W P45 E14 CW FR ND	P45	4	15000	4000	250	45 x 84	929001263832	16282200
MZD LED 25W B35 E14 827 CL ND 1CT/10	B35	2	20000	2700	250	35x97	929001238332	16394200
MZD LED 25W B35 E14 840 CL ND 1CT/10	B35	2	20000	4000	250	35x97	929002215232	16412300
MZD LEDCLA 25W P45 E14 827 CL ND 1CT/10	P45	2	20000	2700	250	45x80	929001238632	16388100
MZD LED 25W B35 E14 840 CL ND 1CT/10	P45	2	20000	4000	250	45x80	929002215132	16410900



**MZD LED 25W E14 827  
B35 FR ND**

12NC: **929001253032**  
EOC: **16135100**

**4** WATT **25** WATT **2700 K**  
**250 lm**



**MZD LED 25W E27 827  
P45 FR ND**

12NC: **929001253332**  
EOC: **16139900**

**4** WATT **25** WATT **2700 K**  
**250 lm**

# MAZDA VELAS Y ESFÉRICAS DISEÑADAS PARA CREAR AMBIENTE

**A<sup>+</sup>**  
EEI label

**80**  
CRI

**⚡**  
220-240 Vac

**🕒**  
15,000h

**⊗**  
No regulable



**MZD LED 40W P45 E14  
WW FR ND 1CT/10**

12NC: **929001253732**  
EOC: **16278500**

**6** WATT > **40** WATT  
**2700 K**  
**470 lm**



**MZD LEDCLA 40W P45 E14  
827 CL ND 1CT/10**

12NC: **929001890432**  
EOC: **16390400**

**5** WATT > **40** WATT

Tipo de producto	Forma	Consumo energía	Número de encendidos	Temperatura de color	Flujo luminoso	Dimensiones W x H	12NC	EOC
				K	lm	mm		
MZD LED 40W B35 E14 WW FR ND 1CT/10	B35	6	15000	2700	470	35 x 103	929001253632	16272300
MZD LED 40W B35 E14 CW FR ND 1CT/10	B35	5	15000	4000	470	35 x 103	929001263732	16288400
MZD LED 40W B35 E14 CDL FR ND 1CT/10	B35	5	15000	6500	470	35 x 103	929001389032	16268600
MZD LED 40W P45 E27 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 79	929001253832	16280800
MZD LED 40W P45 E14 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 84	929001253732	16278500
MZD LED 40W P45 E27 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 79	929001264032	16286000
MZD LED 40W P45 E14 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 84	929001263932	16284600
MZD LED 40W P45 E27 CDL FR ND 1CT/10	P45	5	15000	6500	470	45 x 79	929001389232	16262400
MZD LED 40W P45 E14 CDL FR ND 1CT/10	P45	5	15000	6500	470	45 x 84	929001389132	16260000
MZD LEDCLA 40W B35 E14 827 CL ND 1CT/10	B35	5	20000	2700	470	35 x 97	929001889732	16396600
MZD LEDCLA 40W B35 E14 840 CL ND 1CT/10	B35	5	20000	4000	470	35 x 97	929002214932	16398000
MZD LEDCLA 40W P45 E14 827 CL ND 1CT/10	P45	5	20000	2700	470	45 x 80	929001890432	16390400
MZD LED 40W P45 E14 840 CL ND 1CT/10	P45	5	20000	4000	470	45 x 80	929002214632	16392800

# MAZDA LED VELAS Y ESFÉRICAS DISEÑADAS PARA CREAR AMBIENTE

**A<sup>+</sup>**  
EEI label

**80**  
CRI

**⚡**  
220-240 Vac

**🕒**  
15,000h

**⚠️**  
No regulable

Tipo de producto	Forma	Consumo energía	Número de encendidos	Temperatura de color	Flujo luminoso	Dimensiones W x H	12NC	EOC
				K	lm	mm		
MZD LED 60W B35 E14 827 FR ND 1CT/10	B35	8	15000	2700	806	39 x 114	929001907632	16320100
MZD LED 60W B35 E14 840 FR ND 1CT/10	B35	8	15000	4000	806	39 x 114	929001907732	16322500
MZD LED 60W B35 E14 865 FR ND 1CT/10	B35	8	15000	6500	806	39 x 114	929001907832	16324900
MZD LEDCLA 60W B35 E14 827 CL ND 1CT/10	B35	6	20000	2700	806	35 x 97	929002215332	16414700
MZD LED 60W B35 E14 840 CL ND 1CT/10	B35	6	20000	4000	806	35 x 97	929002215432	16416100



**MZD LED 60W B35 E14  
827 FR ND 1CT/10**

12NC: **929001907632**  
EOC: **16320100**

**8** WATT **60** WATT **2700 K**  
**806 lm**



**MZD LEDCLA 60W B35  
E14 827 FR ND 1CT/10**

12NC: **929002215332**  
EOC: **16414700**

**6** WATT **60** WATT **2700 K**  
**806 lm**