

PHILIPS

Ledinaire



Trusted



Reliable



Great value



Real pros install great-value panels with extra flexibility.

The new Philips Ledinaire panel with a wide range of mounting accessories. The ideal solution for everyday performance.

**REAL
PROs**
**REAL
QUALITY**

More choice for every challenge.

Mounting LED panels from Philips Ledinaire is easy, convenient and effective. What's more, its wide range of accessories offers even greater flexibility and installation ease. This, combined with its long service life and clean design makes it the right choice for off-the-shelf luminaire with greater value and performance.

Features and benefits

- ✓ Accessories for plaster, surface mounted and suspension available
- ✓ Energy-saving comfortable light
- ✓ Modern, unobtrusive design
- ✓ Hassle-free installation
- ✓ Reliable Philips quality

Application

- ✓ General lighting

New




For warranty conditions, visit
www.lighting.philips.com/main/support/support/warranty




Product data

Mains voltage	CRI	Connection	Power factor	Safety Class	Housing	Color
220-240 V / 50-60 Hz	> 80	Push-in with pull-relief	0.9	Class II	Painted steel	WH White (RAL9016)

Dimensions



Available mounting accessories



		EOC code
1	RC125Z SME-2 WH Suspension	07334699
2	RC125Z SMB-PLC Plaster ceiling version (PCV)	07333999
3	RC125Z SMB W60L60 Surface-mounted (SM)	07330899
3	RC125Z SMB W62L62 Surface-mounted (SM)	36592399
4	RC125Z SC Safety cable	07335399

Order information



50000h/L70

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC065B LED34S/840 PSU W60L60 OC	34	3400	4000	IP20	38647499
RC065B LED34S/865 PSU W60L60 OC			6500		36204599
RC065B LED34S/865 PSU W60L60 NOC			6500		36206999
RC065B LED34S/840 PSU W60L60 NOC			4000		79180399
RC066B LED34S/840 PSU W62L62 OC			4000		36558999

