

PHILIPS

Ledinaire



Trusted



Reliable



Great value

Real pros combine great value with extreme robustness.

The new Philips Ledinaire waterproof.
Water-resistant performance for everyday demands.

Efficient, great value and ready to perform.

The **Ledinaire waterproof** range provides maximum performance and durability with an equally attractive price. As an off-the-shelf LED luminaire solution, it comes in a normal and slim version and can be deployed in a wide variety of locations.

Features and benefits

- ✓ Robust (IK08) and waterproof (up to IP66) luminaire
- ✓ Multiple lengths and light levels available
- ✓ Mounting brackets can be positioned over full length of luminaire for easy installation
- ✓ Tested Philips quality
- ✓ Diffuse comfortable light

Applications

- ✓ Covered car parks
- ✓ Industrial halls (up to 4m in height)
- ✓ (Cold) storage rooms

**REAL
PROs
REAL
QUALITY**

2 Ledinaire waterproof
WT060C

1 Ledinaire slim waterproof
WT055C

**New versions
available**



For warranty conditions, visit
www.lighting.philips.com/main/support/support/warranty




Product data


Mains voltage	Lifetime (hrs)	CRI	Connection	IP rating
220-240 V / 50-60 Hz	50,000 hrs L65 (WT055C) 50,000 hrs L70 (WT060C)	> 80	Connection block: push-in connector	IP65 (WT055C) IP66 (WT060C)
Glow wire test	Power factor	Safety Class	Housing	Color
850°	0.9	Class II	Polycarbonate	GR Grey (RAL7035)

Dimensions


WT055C (L600)




WT055C TW (L600)




WT055C (L1200)




WT055C TW (L1200)




WT055C (L1500)




WT055C TW (L1500)



WT060C



WT060C TW



WT060C (mm)	A	B	C	D	E	F	G
L600	69	59	90	611	100-150	100-150	
L1200	69	59	90	1201	200-250	200-250	
L1500	69	59	90	1501	100-150	100-150	
L1800	69	59	90	1801	150-250	150-250	900.5

WT060C TW (mm)	A	B	C	D	E	F
L1200	69	59	90	1258	230-280	230-280
L1500	69	59	90	1558	180-280	180-280

Order information

WT055C



50000h/L65

WT060C



50000h/L70

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
1 Ledinaire slim waterproof					
WT055C LED18S/840 PSU L600	16.5	1800	4000	IP65	79296199
WT055C LED18S/840 PSU TW1 L600		1800	4000	IP65	79297899
WT055C LED36S/840 PSU L1200	33	3600	4000	IP65	79298599
WT055C LED36S/840 PSU TW1 L1200		3600	4000	IP65	79299299
WT055C LED56S/840 PSU L1500	51	5600	4000	IP65	79300599
WT055C LED56S/840 PSU TW1 L1500		5600	4000	IP65	79301299
2 Ledinaire waterproof					
WT060C LED18S/840 PSU L600	15	1800	4000	IP66	36007299
WT060C LED25S/840 PSU TW1 L1200	20	2500	4000	IP66	36292299
WT060C LED25S/840 PSU L1200		2500	4000	IP66	36291599
WT060C LED34S/840 PSU L1500	28	3400	4000	IP66	36293999
WT060C LED34S/840 PSU TW1 L1500		3400	4000	IP66	36294699
WT060C LED36S/865 PSU L1200	30	3600	6500	IP66	36015799
WT060C LED36S/840 PSU L1200		3600	4000	IP66	36009699
WT060C LED36S/840 PSU TW1 L1200		3600	4000	IP66	36010299
WT060C LED56S/865 PSU L1500		5600	6500	IP66	36017199
WT060C LED56S/840 PSU L1500	46	5600	4000	IP66	36011999
WT060C LED56S/840 PSU TW1 L1500		5600	4000	IP66	36012699
WT060C LED80S/840 PSU L1800	65	8000	4000	IP66	36295399

