

PHILIPS

CoreLine Panel



Innovative



Easy to install



High quality

**REAL
PROs**
**REAL
QUALITY**

Panel rejection or panel perfection?

Real professionals count on the new **Philips Coreline Panel - Office Compliant UGR19.**

This is the slimmest panel with class leading efficiency. There are two offers featuring two lumen packages and with three sizes: 300X1200, 600x600 and 600x1200.

Key Features and Benefits

- ✓ 60% more energy efficient compared to conventional TL Solutions
- ✓ Up to 110 lumens/W
- ✓ 50,000 hours to L80
- ✓ Suspended, Flush or recessed mount
- ✓ IP20
- ✓ 5 years warranty
- ✓ UGR19 office compliant
- ✓ Options available for Interact Pro connected lighting system



Applications

- ✓ Offices
- ✓ Schools
- ✓ Meeting rooms
- ✓ Lunch rooms
- ✓ Hallways & corridors

50,000
hours
@L70

Up to
110
lm/w

IP20

5
years
warranty


interact
ready.

www.clubblue.co.nz

Simple installation and different mounting options


The installation of the new Coreline UGR19 office compliant Panel is simple and flexible with three mounting options: recessed, suspended and direct mount (for applications such as plaster ceilings).

Dimensions



Dimensions show above are nominal measurement. Slight variation in dimension may occur in production.

Polar intensity



LED40S 840 W30L120

LED40S 840 W60L60

LED40S 840 W60L120

LED60S 840 W60L120

Order codes for the Coreline Panel - Office Compliant UGR19

Coreline Panel - Office Compliant UGR19

Specification	Part Number	Shortcode
36W, 4000lm, 4000K, 12X3	911401761042 RC160V LED40S 840 W30L120 PSU OC CAU	RC16V484312POF
36W, 4000lm, 4000K, 6X6	911401761052 RC160V LED40S 840 W60L60 PSU OC CAU	RC16V48466POF
36W, 4000lm, 4000K, 1200X600	911401761062 RC160V LED40S 840 W60L120 PSU OC CAU	RC16V484612POF
55W, 6000lm, 4000K, 1200X600	911401761072 RC160V LED60S 840 W60L120 PSU OC CAU	RC16V684612POF

Coreline Panel - Office Compliant UGR19 Interact Ready

Specification	Part Number	Shortcode
36W, 4000lm, 4000K, 12X3, IAR	911401755052 RC160X LED40S 840 W30L120 IAP OC CAU	RC16V484312IOF
36W, 4000lm, 4000K, 6X6, IAR	911401755032 RC160X LED40S 840 W60L60 IAP OC CAU	RC16V48466IOF
36W, 3600lm, 4000K, 1200X600, IAR	On Request RC160X LED40S 840 W60L120 IAP OC CAU	

*Note: All the above options come with Flex & Plug

