

PHILIPS

CoreLine Batten



Innovative



Easy to install



High quality

REAL
PROs
REAL
QUALITY

Lower standards or raise the bar?

Real professionals count on the new **Philips CoreLine Batten.**

These battens deliver superior performance, output and energy efficiency in an affordable package. It is the perfect retrofit solution for conventional battens.

With a wider base and no visible mounting brackets, replacement of an existing batten has never been so easy.

Key Features and Benefits

- ✓ Excellent replacement for T8 and older battens.
- ✓ Surface mount with no visible brackets.
- ✓ Emergency options available (AS2293 compliant).



Applications

- ✓ Warehouses
- ✓ Retail
- ✓ Stairwells
- ✓ General industrial applications

50,000
hours
@L70

Up to
100
lm/w

IP20

IK03


5
year
warranty

www.clubblue.co.nz

Simple installation


Speed and ease of install is key with features such as large terminal block, central feed as well as multiple knock outs for through wiring.

Dimensions



Dimensions shown above are nominal measurement. Slight variation in dimension may occur in production.

Polar intensity



LED 40

LED 60

Order codes for the CoreLine Batten

Specification	Part Number	Shortcode
40W, 4100lm, 4000K, 4ft	911401761112 BN008C LED40/NW L1200 PSU CL	BN840NW12P
40W, 4100lm, 6500K, 4ft	911401761102 BN008C LED40/CW L1200 PSU CL	BN840CW12P
60W, 6000lm, 4000K, 5ft	911401761152 BN008C LED60/NW L1500 PSU CL	BN860NW15P
60W, 6000lm, 6500K, 5ft	911401761142 BN008C LED60/CW L1500 PSU CL	BN860CW15P

*Note: Emergency options also available on request.

