

PHILIPS

The time is now – make the big switch with Philips LED!



Are you ready for the upcoming fluorescent ban?

Reduce energy and maintenance costs with enhanced lighting results and longer lifetime.

Five-colour Shatterproof T8 LED Tube



50,000 hr
Lifetime

CRI
80

Up to
122
lm/W



- Available in 5ft, 4ft and 2ft
- Five-colour temperatures in one tube: 2700K/3000K/4000K/5000K/6500K
- Shatterproof design for food industry compliance

CorePro T8 LED Tubes New Generation



50,000 hr
Lifetime

CRI
80

100
lm/W



- Available in 5ft, 4ft and 2ft
- Glass housing offering a large 240° beam angle for various applications

T5 LED Tubes




60,000 hr
Lifetime

CRI
80

Up to
138
lm/W



- Available in 5ft, 4ft and 2ft
- Retrofit solution with long lifetime of 60,000 hrs
- Mains installation only



Signify product code	Signify short code	Description	Consumption	Brightness	Lifetime	Colour Temperature	Base Cap	Lamp Width	Lamp Length	Lamp Shape	Dimmable
12NC			W	lm	hrs	K		mm	mm		
929004265719	LEDT85CCT5FT	CorePro LEDtube 1,500mm 24W 5CCT T8 AU	24	2400-2640	50,000	2700-3000-4000-5000-6500	G13	28	1,500	T8	No
929004265619	LEDT85CCT4FT	CorePro LEDtube 1,200mm 18W 5CCT T8 AU	18	1800-1980	50,000	2700-3000-4000-5000-6500	G13	28	1,200	T8	No
929004265519	LEDT85CCT2FT	CorePro LEDtube 600mm 9W 5CCT T8 AU	9	900-1100	50,000	2700-3000-4000-5000-6500	G13	28	600	T8	No



Signify product code	Signify short code	Description	Consumption	Brightness	Lifetime	Colour Temperature	Base Cap	Lamp Width	Lamp Length	Lamp Shape	Dimmable
12NC			W	lm	hrs	K		mm	mm		
929003547420	TLED1500840G4	CorePro LEDtube 1,500mm 21.4W 840 T8 AU 1CT	21.4	2200	50,000	4000	G13	28	1,500	T8	No
929003547520	TLED1500865G4	CorePro LEDtube 1,500mm 21.4W 865 T8 AU 1CT	21.4	2200	50,000	6500	G13	28	1,500	T8	No
929003519720	TLED1200840G4	CorePro LEDtube 1,200mm 17W 840 T8 AU 1CT	17	1800	50,000	4000	G13	28	1,200	T8	No
929003519820	TLED1200865G4	CorePro LEDtube 1,200mm 17W 865 T8 AU 1CT	17	1800	50,000	6500	G13	28	1,200	T8	No
929003547220	TLED600840G4	CorePro LEDtube 600mm 8.8W 840 T8 AU 1CT	8.8	900	50,000	4000	G13	28	600	T8	No
929003547320	TLED600865G4	CorePro LEDtube 600mm 8.8W 865 T8 AU 1CT	8.8	900	50,000	6500	G13	28	600	T8	No



Signify product code	Signify short code	Description	Consumption	Brightness	Lifetime	Colour Temperature	Base Cap	Lamp Width	Lamp Length	Lamp shape	Dimmable
12NC			W	lm	hrs	K		mm	mm		
929002421319	TLEDT51500840	CorePro LEDtube 1,500mm HE 22W 840 T5AU	22	3000	60,000	4000	G5	19	1,463.2	T5	No
929003044519	TLEDT51200840	CorePro LEDtube 1,200mm HE 18W 840 T5AU	18	2500	60,000	4000	G5	19	1,163.2	T5	No
929003795519	TLEDT5600840	CorePro LEDtube 600mm HE 7.7W 840 T5AU	7.7	1000	60,000	4000	G5	19	563.2	T5	No