


Philips TrueForce LED lamps

Save energy and provide the perfect light for every space



Industry leading LED lamps for HID replacement:

- Powerful light output, optically efficient
- Instant upgrade – no need to replace or modify fixture
- 50,000 hours lifetime, 5 years warranty

TrueForce LED
Road

More features at a glance



Using existing optics of conventional luminaire



Pleasant white light with CRI 70



Optically efficient, emits light towards direction of use

TrueForce LED Industrial and Retail

- Plug & play: EM system compatible
- Up to 65% energy savings*
- Pleasant white light (CRI 80)
- IP 40 rating

* Compared to conventional systems



TrueForce LED Urban

- Perfect Fit – compact size
- Energy saving up to 75%*
- Optically efficient
- IP65 rating
- Pleasant white light with CRI 80
- Overheating protection



NEW! Portfolio upgrade
and range extension

LED HID

The affordable LED solution for High Intensity Discharge (HID) lamp replacement, Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) lamps.

TrueForce Urban-Post Top HPL & SON Replacement

lighting.philips.co.uk/products/trueforce-led-lamps



Product Type	Traditional W	LED W	Lumen Output lm	Efficacy lm/W	Beam Angle °	Dimmable	CRI	Colour Temp K	Lifetime Hrs.	EEL	12 NC	EOC code
TrueForce Urban												
1 TForce LED HPL ND 30-21W E27 840	80 (HPL 80W, SON 50W)	21	3000	142	360	<input checked="" type="checkbox"/>	80	4000	50000	A++	929002006202	99638160
1 TForce LED HPL ND 28-21W E27 830		21	2850	135	360	<input checked="" type="checkbox"/>	80	3000	50000	A++	929002006102	99638146
2 TForce LED HPL ND 40-28W E27 840	125 (HPL 125W, SON 70W)	28	4000	142	360	<input checked="" type="checkbox"/>	80	4000	50000	A++	929002006402	99638207
2 TForce LED HPL ND 38-28W E27 830		28	3800	135	360	<input checked="" type="checkbox"/>	80	3000	50000	A++	929002006302	99638184
3 TForce LED HPL ND 57-42W E27 830		42	5700	135	360	<input checked="" type="checkbox"/>	80	3000	50000	A++	929002006502	99638221
3 TForce LED HPL ND 60-42W E27 840	200 (HPL 200W, SON 100W)	42	6000	142	360	<input checked="" type="checkbox"/>	80	4000	50000	A++	929002006602	99638245
4 TForce LED HPL ND 57-42W E40 830		42	5700	135	360	<input checked="" type="checkbox"/>	80	3000	50000	A++	929002006702	99638269
4 TForce LED HPL ND 60-42W E40 840		42	6000	142	360	<input checked="" type="checkbox"/>	80	4000	50000	A++	929002006802	99638283
TrueForce Urban Core												
5 TForce Core LED HPL 13W E27 830 FR	50	13	2000	154	360	<input checked="" type="checkbox"/>	80	3000	25000	A++	929002349702	99750251
5 TForce Core LED HPL 13W E27 840 FR		13	2000	154	360	<input checked="" type="checkbox"/>	80	4000	25000	A++	929002349802	99750275
6 TForce Core LED PT 30-27W E27 830 FR	80	27	3000	111	360	<input checked="" type="checkbox"/>	80	3000	25000	A+	929001925302	99594381
7 TForce Core LED HPL 18W E27 830 FR		18	3000	167	360	<input checked="" type="checkbox"/>	80	3000	25000	A++	929002349902	99750299
7 TForce Core LED HPL 18W E27 840 FR	125	18	3000	167	360	<input checked="" type="checkbox"/>	80	4000	25000	A++	929002350002	99750312
8 TForce Core LED PT 50-42W E27 830 FR		42	5000	119	360	<input checked="" type="checkbox"/>	80	3000	25000	A+	929001925002	99594428
9 TForce Core LED HPL 26W E27 830 FR		26	4000	154	360	<input checked="" type="checkbox"/>	80	3000	25000	A++	929002350102	99750336
9 TForce Core LED HPL 26W E27 840 FR	26	4000	154	360	<input checked="" type="checkbox"/>	80	4000	25000	A++	929002350202	99750350	

TrueForce Highbay HPIT, HPI, SON-T, SON & HPL Replacement



Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Colour Temp	Lifetime	EEL	12 NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.			
Trueforce Highbay Universal												
TForce LED HPI UN 88W E40 840 NB ■	250	95	13000	128	-	✗	80	4000	50000	A+ (Mains)	929002350702	99753672
TForce LED HPI UN 88W E40 840 WB ■		95	13000	140	-	✗	80	4000	50000	A++ (Mains)	929002350802	99753696
TForce LED HPI UN 145W E40 840 NB ■	400	140	20000	133	-	✗	80	4000	50000	A+ (Mains)	929002350902	99753719
TForce LED HPI UN 145W E40 840 WB ■		140	20000	140	-	✗	80	4000	50000	A++ (Mains)	929002351002	99753733
1 Trueforce Highbay Instantfit												
TForce LED HPI ND 110-88W E40 840 60D	250	88	11000	125	60	✗	80	4000	50000	A+	929001356802	96713785
TForce LED HPI ND 110-88W E40 840 120D		88	11000	125	120	✗	80	4000	50000	A+	929001356902	96713822
TForce LED HPI ND 200-145W E40 840 60D	400	145	20000	137	60	✗	80	4000	50000	A+	929001357002	96713860
TForce LED HPI ND 200-145W E40 840 120D		145	20000	137	120	✗	80	4000	50000	A+	929001357102	96713884
2 Trueforce Highbay Direct Mains												
TForce LED HB MV ND 120-100W E40 840 NB	250	100	12000	120	60	✗	80	4000	50000	A+	929001929702	99596767
TForce LED HB MV ND 120-100W E40 840 WB		100	12000	120	120	✗	80	4000	50000	A+	929001929802	99596781
TForce LED HB MV ND 200-160W E40 840 NB	400	160	20000	125	60	✗	80	4000	50000	A+	929001812402	99596705
TForce LED HB MV ND 200-160W E40 840 WB		160	20000	125	120	✗	80	4000	50000	A+	929001812502	99596729

■ Expected September 2020

LED HID

TrueForce Road SONT



● = Dimmable

⊗ = Non-dimmable



4 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Colour Temp	Lifetime	EEL	12 NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.			
TrueForce Road SONT HF Instantfit												
1 TForce LED Road 40-25W E27 730	50	25	4000	160	360	⊗	70	3000	50000	A++	929001999402	99632519
1 TForce LED Road 42-25W E27 740		25	4200	168	360	⊗	70	4000	50000	A++	929001999502	99632533
2 TForce LED Road 55-35W E27 730	70	35	5500	157	360	⊗	70	3000	50000	A++	929001898402	96811153
2 TForce LED Road 60-35W E27 740		35	6000	171	360	⊗	70	4000	50000	A++	929001898502	96811177
3 TForce LED Road 84-55W E40 730	100	55	8400	152	360	⊗	70	3000	50000	A++	929002007402	99639044
3 TForce LED Road 90-55W E40 740		55	9000	163	360	⊗	70	4000	50000	A++	929002007502	99639068
4 TForce LED Road 112-68W E40 730	100-150	68	11200	164	360	⊗	70	3000	50000	A++	929002007602	99639082
4 TForce LED Road 120-68W E40 740		68	12000	176	360	⊗	70	4000	50000	A++	929002007702	99639105
TrueForce Road SONT Direct Mains												
2 TForce LED Road 35W E27 730 MV	70	35	5500	157	360	⊗	70	3000	50000	A++	929002221708	99674830
2 TForce LED Road 35W E27 740 MV		35	6000	171	360	⊗	70	4000	50000	A++	929002068508	99674854
3 TForce LED Road 55W E40 730 MV	100	55	8400	153	360	⊗	70	3000	50000	A++	929002221608	99674779
3 TForce LED Road 55W E40 740 MV		55	9000	164	360	⊗	70	4000	50000	A++	929002068708	99674793

Decorative Range

Vintage (spiral) filament lamps



● = Dimmable

⊗ = Non-dimmable



4 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Colour Temp	Lifetime	EEL	12 NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.			
Vintage: spiral filament bulbs												
1 LED classic 25W A60 E27 GOLD SP D SRT4	25	5.5	250	45	-	●	80	2000	15000	A	929002223801	99676032
Vintage: spiral filament candle B35												
2 LED classic 15W B35 E14 GOLD SP D SRT4	15	3.5	136	39	-	●	80	2000	15000	A	929002224301	99676131
Vintage: spiral filament candle P45												
3 LED classic 15W P45 E27 GOLD SP D SRT4	15	3.5	136	38	-	●	80	2000	15000	A	929002224201	99676117
4 LED classic 15W P45 E14 GOLD SP D SRT4		3.5	136	39	-	●	80	2000	15000	A	929002224401	99676155
Vintage: spiral filament ST64												
5 LED classic 25W ST64 E27 GOLD SP D SRT4	25	5.5	250	45	-	●	80	2000	15000	A	929002223901	99676056
Vintage: spiral filament globe												
6 LED classic 25W G93 E27 GOLD SP D SRT4	25	5.5	250	45	-	●	80	2000	15000	A	929002224001	99676070

Vintage cord pendants



● = Dimmable

⊗ = Non-dimmable



4 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Colour Temp	Lifetime	EEL	12 NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.			
Vintage cord pendants												
1 CORD/classic/E27/gold 1CT EU	40	40	-	-	-	-	-	-	-	-	929001978001	96167779
2 CORD/modern/E27/black 1CT EU	40	40	-	-	-	-	-	-	-	-	929001977901	96167762

Decorative Range

Smoky filament lamps & Eyecatch

Smoky filament lamps, Eyecatch & Crown Mirror




= Dimmable
 = Non-dimmable



Product Type	Traditional	LED	Lumen Output	Efficacy	Beam Angle	Dimmable	CRI	Colour Temp	Lifetime	EEL	12 NC	EOC code
	W	W	lm	lm/W	°			K	Hrs.			
Giant filament lamps												
6 LED classic-giant 40W E27 G200 GOLD DIM	40	6.5	470	72	-		80	2000	15000	A+	929001873401	96803479
7 LED classic-giant 40W E27 A160 GOLD DIM		6.5	470	72	-		80	2000	15000	A+	929001873501	96803493
8 LED classic-giant 40W E27 T65 GOLD DIM		6.5	470	72	-		80	2000	15000	A+	929001873601	96803516
Smoky filament lamps												
1 LED giant 25W E27 G200 4000K smoky D	25	6.5	270	41	-		80	4000	15000	A	929001903101	96815069
2 LED giant 25W E27 A160 4000K smoky D		6.5	270	41	-		80	4000	15000	A	929001903201	96815106
3 LED giant 25W E27 T65 4000K smoky D		6.5	270	41	-		80	4000	15000	A	929001903301	96815120
Eyecatch												
4 LED classic 30W Mushroom E27 2000K GOLD D	30	5	350	70	-		80	2000	15000	A+	929001935601	99593513
5 LED classic 40W Diamond E27 2700K CL D	40	5	500	100	-		80	2700	15000	A+	929001935701	99593537
Crown Mirror												
9 LED classic CM 48W A60 E27 WW CL D SRT4	48	7.5	610	81	-		80	2700	15000	A+	929001333501	96709269
10 LED classic 50W G120 E27 2700K CM D	50	8	700	87	-		80	2700	15000	A+	929001935401	99593414

PHILIPS

Lighting



Philips Conversion Tool for conventional lamps

Tired of sourcing lamps from multiple suppliers?
Are some of your popular conventional lamp stock items now discontinued?

With our Lamps and **Drivers Conversion Tool**, you can find the Philips equivalent of **any conventional lamp and driver!**



3 simple steps:



1 Register or sign in



2 Enter the name, part code or description of the product you need (can be a non-Philips product)



3 Click the relevant lamp in the search results ...

... the Conversion Tool will then display the Philips version of the same product!

Great features:

- Use the comprehensive product filter to assist in the search
- Compare the products side-by-side for any differences (dimensions, wattage, temperature range, etc).
- Export your search results with all associated specification
- Search multiple items at the same time

Try it now: www.philips.com/conversiontool

