

PHILIPS

LED lamps

Candles and decorative lamps



Breathtaking brilliance and sparkling white light

Philips LED candles and decorative shapes incorporate a beautiful filament aesthetic. With amazing light quality, the ability to be used in wet locations, and superior energy savings these lamps can create an intimate atmosphere. Perfect for chandeliers, sconces and general lighting.


Benefits

- Lowers maintenance costs by reducing re-lamp frequency
- Contains no mercury

Features

- Installs into existing candelabra and medium base fixtures
- Up to a 15,000-hour life¹
- Wet location
- Select models feature incandescent emulation to offer a familiar feel

Philips LED Candles and Decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend	
A15 - 25W equivalent lamps non-dimming														
W	556555	929002260203	3.3A15/VIN/820/E26/CL/GL/DIM 4/1BC T20	3.3	200	E26	120	80	2000	15,000	CP	Glass	Amber	A
W	543165	929002001103	3A15/MOD/840/E26/CL/GL/DIM 4/1BC	3	100	E26	120	80	4000	15,000	CP	Glass	Smokey	B
A15 - 40W equivalent lamps dimming														
W	549378	929002208104	3.8A15/PER/927-922/CL/G/E12/WGX1FB T20	3.8	350	E12	120	90	2700-2200	15,000	MC	Glass	Clear	C
W	549386	929002208304	3.8A15/PER/927-922/CL/G/E26/WGX1FB T20	3.8	350	E26	120	90	2700-2200	15,000	MC	Glass	Clear	D
W	548305	929002209004	5A15/PER/950/CL/G/E26/DIM 1FB T20	5	450	E26	120	90	5000	15000	CP	Glass	Clear	E
A15 - 60W equivalent lamps dimming														
W	549394	929002208404	5.5A15/PER/927-922/CL/G/E12/WGX1FB T20	5.5	500	E12	120	90	2700-2200	15,000	MC	Glass	Clear	C
W	549402	929002208604	5.5A15/PER/927-922/CL/G/E26/WGX1FB T20	5.5	500	E26	120	90	2700-2200	15,000	MC	Glass	Clear	D
W	548313	929002209304	8A15/PER/950/CL/G/E26/DIM 1FB T20	8	800	E26	120	90	5000	15,000	CP	Glass	Clear	E



Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend	
G16.5 - 25W equivalent lamps dimming														
W	537597	929001951353	4.5G16.5/VIN/820/E12/CL/GL/DIM 4/BC T20	4.5	300	E12	120	80	2000	15,000	CP	Glass	Amber	F
W	556829	929001951333	4.5G16.5/VIN/820/E12/CL/GL/DIM FBH T20	4.5	300	E12	120	80	2000	15,000	-	Glass	Amber	F
WD	549253	929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	2.7	250	E26	120	90	2700-2200	15,000	MC	Glass	Clear	G
WD	549261	929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	2.7	250	E12	120	90	2700-2200	15,000	MC	Glass	Clear	H
W	543157	929002001403	3G16.5/MOD/840/E12/CL/GL/DIM 4/BC	3	100	E12	120	80	4000	15,000	CP	Glass	Smokey	I
G16.5 - 40W equivalent lamps dimming														
WD	549287	929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	3.8	350	E12	120	90	2700-2200	15,000	MC	Glass	Clear	J
WD	549279	929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	3.8	350	E26	120	90	2700-2200	15,000	MC	Glass	Clear	K
WD	549311	929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	3.8	350	E26	120	90	2700-2200	15,000	MC	Glass	Frosted	L
G16.5 - 60W equivalent lamps dimming														
WD	549303	929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	5.5	500	E12	120	90	2700-2200	15,000	MC	Glass	Clear	J
WD	549295	929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	5.5	500	E26	120	90	2700-2200	15,000	MC	Glass	Clear	K

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures ENERGY STAR® qualified Title 20 compliant Not regulated by Title 20

Philips LED Candles and Decorative lamps



E12 E26

Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend	
Candles - 15W equivalent lamps dimming														
W	543181	929002001303	3B11/MOD/840/E12/CL/GL/DIM 8/1BC	3	100	E12	120	80	4000	15000	CP	Glass	Smokey	A
W	543173	929002001203	3BA11/MOD/840/E12/CL/GL/DIM 8/1BC	3	100	E12	120	80	4000	15000	CP	Glass	Smokey	B
Candles - 25W equivalent lamps dimming														
WD	549329	929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	2	180	E12	120	90	2700-2200	15,000	MC	Glass	Clear	C
WD	549246	929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	2	180	E12	120	90	2700-2200	15,000	MC	Glass	Clear	D
Candles - 40W equivalent lamps dimming														
W	537621	929001951453	4.5B11/VIN/820/E12/CL/GL/DIM 8/1BC T20	4.5	300	E12	120	80	2000	15,000	CP	Glass	Amber	E
W	556852	929001951433	4.5B11/VIN/820/E12/CL/GL/DIM FBH T20	4.5	300	E12	120	80	2000	15,000	CP	Glass	Amber	E
W	537613	929001951153	4.5BA11/VIN/820/E12/CL/GL/DIM 4/1BC T20	4.5	300	E12	120	80	2000	15,000	CP	Glass	Amber	F
W	556845	929001951133	4.5BA11/VIN/820/E12/CL/GL/DIM 4/FBHT20	4.5	300	E12	120	80	2000	15,000	CP	Glass	Amber	F
WD	549568	929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	3.3	300	E12	120	90	2700-2200	15,000	MC	Glass	Clear	C
WD	549584	929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	3.3	300	E26	120	90	2700-2200	15,000	MC	Glass	Clear	K
WD	549543	929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	3.3	300	E12	120	90	2700-2200	15,000	MC	Glass	Clear	D
WD	549550	929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	3.3	300	E26	120	90	2700-2200	15,000	MC	Glass	Clear	L
WD	549147	929002205904	3.3B11/PER/950/CL/G/E12/DIM 1FBT20	3.3	300	E12	120	90	5000	15,000	CP	Glass	Clear	G
WD	549154	929002206004	3.3B11/PER/950/CL/G/E26/DIM 1FBT20	3.3	300	E26	120	90	5000	15,000	CP	Glass	Clear	H
WD	549121	929002205704	3.3BA11/PER/950/CL/G/E12/DIM 1FB T20	3.3	300	E12	120	90	5000	15,000	CP	Glass	Clear	I
WD	549139	929002205804	3.3BA11/PER/950/CL/G/E26/DIM 1FB T20	3.3	300	E26	120	90	5000	15,000	CP	Glass	Clear	J
Candles - 60W equivalent lamps dimming														
WD	549337	929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	5.5	500	E12	120	90	2700-2200	15,000	MC	Glass	Clear	C
WD	549345	929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	5.5	500	E26	120	90	2700-2200	15,000	MC	Glass	Clear	K
WD	550250	929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	5.5	500	E12	120	90	2700-2200	15,000	MC	Glass	Clear	D
WD	549576	929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	5.5	500	E26	120	90	2700-2200	15,000	MC	Glass	Clear	L
WD	547959	929002091503	5.5F15/PER/927-922/CL/G/E26/WGX 1BC T20	5.5	500	E26	120	90	2700-2200	15,000	MC	Glass	Clear	Q
WD	549410	929002206304	5.5B11/PER/950/CL/G/E12/DIM 1FBT20	5.5	500	E12	120	90	5000	15,000	CP	Glass	Clear	M
WD	549428	929002206404	5.5B11/PER/950/CL/G/E26/DIM 1FBT20	5.5	500	E26	120	90	5000	15,000	CP	Glass	Clear	N
WD	549162	929002206104	5.5BA11/PER/950/CL/G/E12/DIM 1FB T20	5.5	500	E12	120	90	5000	15,000	CP	Glass	Clear	O
WD	549170	929002206204	5.5BA11/PER/950/CL/G/E26/DIM 1FB T20	5.5	500	E26	120	90	5000	15,000	CP	Glass	Clear	P
Candles - 75W equivalent lamps dimming														
W	557462	929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	6.6	600	E26	120	90	2700-2200	15,000	MC	Glass	Clear	R
W	557470	929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	6.6	600	E12	120	90	2700-2200	15,000	MC	Glass	Clear	S

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim. Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures
 ■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
 200 Franklin Square Drive,
 Somerset, NJ 08873
 Telephone 855-486-2216

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.