



Mayores beneficios,
al mejor costo.



80 CRI ⚡ 120-277V~ ⌚ 20,000 h ⓧ No dimeable

PILA Proyector Flood

Características técnicas:

911401858580 / 911401858680
911401858780 / 911401858880

Potencia	10 W	20 W	30 W	50 W
Eficacia	100 LPW	100 LPW	100 LPW	100 LPW
Voltaje	120-277V~	120-277V~	120-277V~	120-277V~
Flujo luminoso	1 000 lm	2 000 lm	3 000 lm	5 000 lm
Temperatura de color	6 500 K	6 500 K	6500 K	6 500 K
CRI	80	80	80	80
Frecuencia	50/60Hz	50/60Hz	50/60Hz	50/60Hz
Factor potencia	>0.9	>0.9	>0.9	>0.9
Hermeticidad	IP65	IP65	IP65	IP65
Protección de impacto	IK07	IK07	IK07	IK07
Vida	20k h	20k h	20k h	20k h


Aplicaciones:

- Oficinas
- Industria
- Edificios
- Aeropuertos
- Ideal para estacionamientos


Beneficios:

- Eficiente
- Ahorro de energía
- Fácil y rápido de instalar
- 2 años de garantía

Dimensiones:



Potencia	A (mm)	B (mm)	C (mm)	D (mm)
10W	103	137	34	111
20W	122	164	34	140
30W	145	193	34	160
50W	176	239	39	205

12NC	Descripción	Temperatura de color (K)	Dimensiones Ax B x C (mm)	 Kg
911401858580	10W 120-277 CW	6 500	103x137x34	0.28
911401858680	20W 120-277 CW	6 500	122x164x34	0.39
911401858780	30W 120-277 CW	6 500	145x193x34	0.50
911401858880	50W 120-277 CW	6 500	176x239x39	0.91