


Luminaire Wall Pack



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____


Product offering

UPC Code	Catalog Code	Description	Case Qty. (pc/carton)	Pallet Qty. (pc/pallet)
190096130771	TWP20W40K1	20W, 2400 lumens, 4000k, 120-277v, Bronze finish, includes photocontrol	10	240

Technical specifications

Nominal power	20 W
Nominal lumens	2400 lumens
Input voltage	120-277V, 50/60Hz
CCT	4000K
CRI	≥70
System efficacy	120 lm/W (typical) ±10%
Mounting	Wall mount
Power connection	Round our octagonal junction box, or 1/2" conduit entry on bottom.
Material and finishing	Plastic housing with textured bronze finish
Operating temperature	-40°C to +40°C
Weight	1.39 lbs.
IP/IK rating	Wet locations/IP65 / IK08
Compliance	cETLus/FCC
Warranty	3-year limited warranty





Dimensions

