



2020
Lamps

**Solid lighting,
saving energy**

PILA portfolio

Bulb Type	Product No.	12NC	Description	Watts	Lumens	Beam Angle	Volts
A19	D 358556	929001359531	PILA 6.5-40W/A19/LED/827/FR/E26/ND 24PK	6.5	450	N/A	120
	D 600100	929001359533	PILA 6.5-40W/A19/LED/827/FR/E26/ND 8PK	6.5	450	N/A	120
	D 358564	929001359631	PILA 6.5-40W/A19/LED/850/FR/E26/ND 24PK	6.5	450	N/A	120
	D 600110	929001359633	PILA 6.5-40W/A19/LED/850/FR/E26/ND 8PK	6.5	450	N/A	120
	D 358572	929001359731	PILA 10.5-60W/A19/LED/827/FR/E26/ND24PK	10.5	800	N/A	120
	D 600010	929001359733	PILA 10.5-60W/A19/LED/827/FR/E26/ND 8PK	10.5	800	N/A	120
	D 358580	929001359831	PILA 10.5-60W/A19/LED/850/FR/E26/ND24PK	10.5	800	N/A	120
	D 600120	929001359833	PILA 10.5-60W/A19/LED/850/FR/E26/ND 8PK	10.5	800	N/A	120
	D 358598	929001359931	PILA 11.5-75W/A19/LED/827/FR/E26/ND24PK	11.5	1000	N/A	120
	D 600130	929001359933	PILA 11.5-75W/A19/LED/827/FR/E26/ND 8PK	11.5	1000	N/A	120
	D 358606	929001360031	PILA 11.5-75W/A19/LED/850/FR/E26/ND24PK	11.5	1000	N/A	120
	D 600148	929001360033	PILA 11.5-75W/A19/LED/850/FR/E26/ND 8PK	11.5	1000	N/A	120
A21	D 358614	929001360131	PILA 14-100W/A21/LED/827/FR/E26/ND 16PK	14	1300	N/A	120
	D 600150	929001360133	PILA 14-100W/A21/LED/827/FR/E26/ND 8PK	14	1300	N/A	120
	D 358622	929001360231	PILA 14-100W/A21/LED/850/FR/E26/ND 16PK	14	1400	N/A	120
	D 600160	929001360233	PILA 14-100W/A21/LED/850/FR/E26/ND 8PK	14	1400	N/A	120
BA11	D 358697	929001842531	PILA 4.5-40W/BA11/LED/827/CL/E12/ND 12PK	4.5	300	N/A	120
	D 358713	929001842731	PILA 4.5-40W/BA11/LED/827/CL/E26/ND 12PK	4.5	300	N/A	120
A15	D 358705	929001843631	PILA 4.5-40W/A15/LED/827/CL/E26/ND 10PK	4.5	300	N/A	120
B11	D 344606	929001910131	PILA 4.5-40W/B11/LED/827/CL/E12/ND 12PK	4.5	300	N/A	120
	D 344614	929001910331	PILA 4.5-40W/B11/LED/827/CL/E26/ND 12PK	4.5	300	N/A	120
R20	D 344598	929001887831	PILA 6-45W/R20/LED/850/FR/E26/ND 6PK	6	450	N/A	120
BR30	D 358648	929001947931	PILA 9-65W/BR30/LED/827/FR/E26/ND 12PK	9	650	N/A	120
	D 600170	929001947932	PILA 9-65W/BR30/LED/827/FR/E26/ND 8PK	9	650	N/A	120
	D 358655	929001948031	PILA 9-65W/BR30/LED/850/FR/E26/ND 12PK	9	650	N/A	120
BR40	D 358671	929001195031	PILA 10-65W/BR40/LED/850/FR/E26/ND 12PK	10	800	N/A	120
T8	D 344416	929001968084	16T8/PILA/48-840/A/18/G 25/1	16	1800	N/A	120-277, 347
	D 344424	929001968184	16T8/PILA/48-850/A/18/G 25/1	16	1800	N/A	120-277, 347
	D 344473	929002253184	15T8/PILA/48-840/B/18/G/DL 25/1	15	1800	N/A	120-277
	D 344499	929002253284	15T8/PILA/48-850/B/18/G/DL 25/1	15	1800	N/A	120-277
	D 344432	929002252984	12T8/PILA/48-835/A/17/G/DL 25/1	12	1700	N/A	120-277, 347
	D 344440	929002012284	12T8/PILA/48-840/A/18/G/DL 25/1	12	1800	N/A	120-277, 347
	D 344457	929002012384	12T8/PILA/48-850/A/18/G/DL 25/1	12	1800	N/A	120-277, 347
	D 344507	929002253384	16T8/PILA/48-840/B/16/G 25/1	16	1600	N/A	120-277
	D 344515	929002253484	16T8/PILA/48-850/B/16/G 25/1	16	1600	N/A	120-277
	D 344523	929002253584	8T8/PILA/24-840/B/8/G 25/1	8	800	N/A	120-277
	D 344531	929002253684	8T8/PILA/24-850/B/8/G 25/1	8	800	N/A	120-277
PAR38	D 344564	929001362131	PILA 90W/PAR38/LED/830/40D/ND 6PK	12	900	40	120
	D 344572	929002257331	PILA 120W/PAR38/LED/830/40D/ND 6PK	15.5	1200	40	120
MR16	D 344580	929001362931	PILA 35W/MR16/LED/830/35D/ND 6PK	5.5	380	35	12

D Damp location

E Enclosable



CRI	LED Lifetime ^{1,2}	CCT	Case Size	Material	Finish	UL Type	DLC ID	Legend
80	10,000	2700	24	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	8	Plastic	Frosted	N/A	N/A	A
80	10,000	5000	24	Plastic	Frosted	N/A	N/A	A
80	10,000	5000	8	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	24	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	8	Plastic	Frosted	N/A	N/A	A
80	10,000	5000	24	Plastic	Frosted	N/A	N/A	A
80	10,000	5000	8	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	24	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	8	Plastic	Frosted	N/A	N/A	A
80	10,000	5000	24	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	8	Plastic	Frosted	N/A	N/A	A
80	10,000	2700	16	Plastic	Frosted	N/A	N/A	B
80	10,000	2700	8	Plastic	Frosted	N/A	N/A	B
80	10,000	5000	16	Plastic	Frosted	N/A	N/A	B
80	10,000	5000	8	Plastic	Frosted	N/A	N/A	B
80	10,000	2700	12	Glass	Clear	N/A	N/A	H
80	10,000	2700	12	Glass	Clear	N/A	N/A	I
80	10,000	2700	10	Glass	Clear	N/A	N/A	J
80	10,000	2700	12	Glass	Clear	N/A	N/A	K
80	10,000	2700	12	Glass	Clear	N/A	N/A	L
80	10,000	5000	6	Plastic	Frosted	N/A	N/A	C
80	10,000	2700	12	Plastic	Frosted	N/A	N/A	D
80	10,000	2700	8	Plastic	Frosted	N/A	N/A	D
80	10,000	5000	12	Plastic	Frosted	N/A	N/A	D
80	10,000	5000	12	Plastic	Frosted	N/A	N/A	E
80	36000	4000	25	Glass	Frosted	A	No	O
80	36000	5000	25	Glass	Frosted	A	No	O
80	50000	4000	25	Glass	Frosted	B	Pending	P
80	50000	5000	25	Glass	Frosted	B	Pending	P
80	50000	3500	25	Glass	Frosted	A	Pending	M
80	50000	4000	25	Glass	Frosted	A	Pending	M
80	50000	5000	25	Glass	Frosted	A	Pending	M
80	32000	4000	25	Glass	Frosted	B	No	O
80	32000	5000	25	Glass	Frosted	B	No	O
80	32000	4000	25	Glass	Frosted	B	No	N
80	32000	5000	25	Glass	Frosted	B	No	N
80	10,000	3000	6	Plastic	White	N/A	N/A	F
80	10,000	3000	6	Plastic	White	N/A	N/A	F
80	10,000	3000	6	Plastic	White	N/A	N/A	G



H



I



J



K



L



An established brand

PILA is the answer to the needs of those customers who are looking for affordable and yet reliable LED products. Our LED lamps are an excellent replacement for their conventional equivalents.

Benefits:

- Affordable/economical products
- Efficient
- Product portfolio dedicated to basic applications
- Guaranteed luminous flux and durability
- Simple conversion from conventional luminaires to LED
- Simple and quick assembly

The factory in Pila started production of traditional bulbs in 1958. Due to the transformation of technology into LED, the first PILA LED bulbs appeared on the market in 2014 and LED tubes in 2017.

In some European markets, PILA is a brand with high reputation and awareness among consumers (34% source: HeartBeat) and it's highly recognized in the professional market among installers.

Therefore, in 2018, we decided to expand the offer with a full category of economical professional installation fittings.

