

Luminaire Shop light

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Notes: _____



Product offering


Catalog Code	Description	UPC Code	Case Qty. (pc/carton)	Pallet Qty. (pc/pallet)
SH45L40K1	45W, 4500 LUMENS, 4000K, 120VAC INPUT, WHITE FINISH	190096130719	12	108

Technical specifications

Nominal power	45W
Nominal lumens	4500lm
Input voltage	AC120V, 60HZ
CCT	4000K
CRI	>80
Beam spread	120°±10°
Power connection	5.5ft. white power cord, 2-prong 16ga, Up to 8 shoplights may be plugged together, 11" pull chain
Material and finishing	White painted steel, acrylic lens
Mounting	Suspended, 6" hanging cables provided (2) Surface, mounting screws provided (2)

Weight	1.7lb (0.77kg)
Operating temperature range	-20°C to +40°C
Safety class	Class II
IP/IK rating	IP20 / IK03
Compliance	cETLus for damp locations
Warranty	3-year limited warranty





Dimensions

45W

