



PILA floodlights



Product description	PILA BVP007 10W 4000k	PILA BVP007 20W 4000k	PILA BVP007 50W 4000k	PILA BVP007 10W 3000k	PILA BVP007 20W 3000k	PILA BVP007 50W 3000k	PILA BVP007 20W 4000k MDU	PILA BVP007 50W 4000k MDU
Light output (lm)	850	1700	4250	800	1600	4000	1700	4250
Power (W)	10	20	50	10	20	50	20	50
CCT (K)	4000	4000	4000	3000	3000	3000	4000	4000
Mains voltage	220-240V / 50-60Hz	220-240V / 50-60Hz	220-240V / 50-60Hz	220-240V / 50-60Hz	220-240V / 50-60Hz	220-240V / 50-60Hz	220-240V / 50-60Hz	220-240V / 50-60Hz
Lifetime	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs	35,000 hrs
CRI	80	80	80	80	80	80	80	80
Connection	Flying wire	Flying wire	Flying wire	Flying wire	Flying wire	Flying wire	Flying wire	Flying wire
IP rating	IP65 / IK06	IP65 / IK06	IP65 / IK06	IP65 / IK06	IP65 / IK06	IP65 / IK06	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9	> 0.9	> 0.9	> 0.9	> 0.9	> 0.9	> 0.9
Safety class	Class I	Class I	Class I	Class I	Class I	Class I	Class I	Class I
Housing material	Glass/Aluminium	Glass/Aluminium	Glass/Aluminium	Glass/Aluminium	Glass/Aluminium	Glass/Aluminium	Glass/Aluminium	Glass/Aluminium
Color	Black	Black	Black	Black	Black	Black	Black	Black
EOC	871016332987199	871016332988899	871016332989599	871016332990199	871016332991899	871016332992599	871016332994999	871016332995699
12NC	911401732202	911401732212	911401732222	911401732232	911401732242	911401732252	911401732272	911401732282

- Benefits**
- ▶ Energy saving
 - ▶ Robust luminaire
 - ▶ Reliable quality