



Product description	criptionPILA LED 35W GU5.3PILA LED 50W GU5.3PILA LED 65W GU10WW 12V 36D NDWW 12V 36D NDCW 36D ND		PILA LED 20W GU5.3 WW 12V 36D ND		
Light output (lm)	345	680	xxx	250	
Power (W)	5.5	8	XXX	2.8	
CCT (K)	2700	2700	4000	2700	
Mains voltage	12V	12V	220-240V / 50Hz	12V	
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs	
CRI	80	80	80	80	
Dimming	No	No	No	No	
Lamp shape	Spot	MR16	Spot	MR16	
Color	Warm White	Warm White	Cool White	Warm White	
Energy efficiency class	А	A +	A+	A++	
EAN	8718696485163	8727900964790	8718696534229	8727900964639	
12NC					

- ▶ Different kinds of versions
- ► Suitable for different applications





Product description	PILA LED 50W GU10 CW 36D ND	PILA LED 35W GU10 CW 36D ND	PILA LED 50W GU5.3 CW 12V 36D ND	PILA LED 50W GU10 WW 36D ND	
Light output (lm)	420	280	700	345	
Power (W)	4.7	3	8	5.5	
CCT (K)	4000	4000	4000	2700	
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	12V	220-240V / 50Hz	
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs	
CRI	80	80	90	80	
Dimming	No	No	No No		
Lamp shape	GU10	GU10	MR16	Spot	
Color	Cool White	Cool White	Cool White	Warm White	
Energy efficiency class	A+	A++	A+	A+	
EAN	8727900964899	8727900964875	8727900964851	8718696485200	
12NC					

- ▶ Different kinds of versions
- ► Suitable for different applications





Product description	PILA LED 65W GU10 WW 36D ND	PILA LED 50W GU10 CW 60D ND	PILA LED 50W GU10 WW 36D ND	PILA LED 60W E27 WW R63 36D DIM	
Light output (lm)	460	370	380	380	
Power (W)	5.5	5.5	4.7	5	
CCT (K)	2700	4000	2700	2700	
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs	
CRI	80	80	80	80	
Dimming	No	No	No	Yes	
Lamp shape	GU10	Spot	GU10	Bulb	
Color	Warm White	Cool White	Warm White	Warm White	
Energy efficiency class	A++	A +	A+	A+	
EAN	8727900964592	8718696537015	8727900964516	8718696527092	
12NC					

- ▶ Different kinds of versions
- ► Suitable for different applications





Product description	PILA LED 35W GU10 WW 36D ND	PILA LED 35W GU10 WW 36D ND	PILA LED 65W GU10 WW 36D ND	PILA LED 40W E14 WW R50 36D DIM
Light output (lm)	250	230	xxx	xxx
Power (W)	3	3.3	XXX	3.5
CCT (K)	2700	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	No	Yes
Lamp shape	GU10	Spot	Spot	Spot
Color	Warm White	Warm White	Warm White	Warm White
Energy efficiency class	A++	A+	A+	A+
EAN	8727900964479	8718696485187	8718696534205	8718696485422
12NC				

- ▶ Different kinds of versions
- ► Suitable for different applications





Product description	PILA LED 65W GU10 CW 36D ND	PILA LED 35W GU5.3 CW 12V 36D ND	PILA LED 40W E14 WW R50 36D ND	PILA LED 35W GU5.3 WW 12V 36D ND	PILA LED 50W GU10 CDL 36D ND
Light output (lm)	460	420	xxx	380	420
Power (W)	5.5	4.5	2.9	4.5	4.7
ССТ (К)	4000	4000	2700	2700	6500
Mains voltage	220-240V / 50Hz	12V	220-240V / 50Hz	12V	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80	80
Dimming	No	No	No	No	No
Lamp shape	GU10	MR16	R50	MR16	GU10
Color	Cool White	Cool White	Warm White	Warm White	Warm White
Energy efficiency class	A++	A+	A++	A+	A+
EAN	8727900964615	8727900964837	8727900964912	8727900964653	8727900964530
12NC					

- ▶ Different kinds of versions
- ► Suitable for different applications