



Specifications - PILA LED 60W E27 WW A60 ND

Product description	PILA LED 60W E27 WW A60 ND
Light output (lm)	806
Power (W)	9,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Bulb
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485385
null	/8718696485385_Pila_EEL

Energy efficiency label





Specifications - PILA LED 15W E14 WW T25 ND

Product description	PILA LED 15W E14 WW T25 ND
Light output (lm)	140
Power (W)	15
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Spot
Colour	Warm White
Energy efficiency class	A++
Average lifespan	15000
EAN	8718696485408
null	/8718696485408_Pila_EEL

Energy efficiency label





Specifications - PILA LED 40W A60 E27 WW FR DIM 1CT/6

Product description	PILA LED 40W A60 E27 WW FR DIM 1CT/6
Dimensions	60*108
Light output (lm)	470 lumen
Power (W)	6W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	Yes
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	470 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	37 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964318
Energy Consumption kWh/1000 h	6W
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 60W A60 E27 WW FR DIM 1CT/6

Product description	PILA LED 60W A60 E27 WW FR DIM 1CT/6
Dimensions	60*108
Light output (lm)	1055 lumen
Power (W)	9W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	Yes
Voltage	220-240
Voltage type	220-240V
Luminous intensity	1055 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	55 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964332
Energy Consumption kWh/1000 h	9W
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 60W E27 CW A60 ND

Product description	PILA LED 60W E27 CW A60 ND
Light output (lm)	850
Power (W)	9,5
CCT (K)	4000
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Bulb
Colour	Cool White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696491089
null	/8718696491089_Pila_EEL

Energy efficiency label





Specifications - PILA LED 75W A60 E27 CW FR ND 1CT/6

Product description	PILA LED 75W A60 E27 CW FR ND 1CT/6
Dimensions	60*108
Light output (lm)	1100 lumen
Power (W)	10W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	1100 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Cool white
Lamp current	85 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964134
Energy Consumption kWh/1000 h	10
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 100W A67 E27 CW FR ND 1CT/6

Product description	PILA LED 100W A67 E27 CW FR ND 1CT/6
Dimensions	65*120
Light output (lm)	1521 lumen
Power (W)	13W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	1521 lumen
Lamp shape	A67
Type of glass/cover	Frosted
Colour	Cool white
Lamp current	100 mA
Diameter	65 mm

SPECIFICATIONS (continued)

Diameter	65 mm
Length	120 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964714
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 60W A60 E27 WW FR ND 1CT/6

Product description	PILA LED 60W A60 E27 WW FR ND 1CT/6
Dimensions	60*110.7
Light output (lm)	810 lumen
Power (W)	8W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	200-240V
Voltage type	200-240V
Luminous intensity	810 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	78 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Length	110.7 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964073
Energy Consumption kWh/1000 h	8
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 40W A60 E27 CW FR ND 1CT/6

Product description	PILA LED 40W A60 E27 CW FR ND 1CT/6
Dimensions	60*108
Light output (lm)	500 lumen
Power (W)	6W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240
Voltage type	220-240
Luminous intensity	500 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Cool white
Lamp current	55 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964059
Energy Consumption kWh/1000 h	6
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 75W A60 E27 WW FR DIM 1CT/6

Product description	PILA LED 75W A60 E27 WW FR DIM 1CT/6
Dimensions	60*108
Light output (lm)	1055 lumen
Power (W)	10.5W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	Yes
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	1055 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	65 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964356
Energy Consumption kWh/1000 h	11
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 40W A60 E27 WW FR ND 1CT/6

Product description	PILA LED 40W A60 E27 WW FR ND 1CT/6
Dimensions	60*108
Light output (lm)	470 lumen
Power (W)	6W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	470 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	55 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964035
Energy Consumption kWh/1000 h	6
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - Pila LEDClassic 40W A60 E27 WW ND 1CT/1

Product description	Pila LEDClassic 40W A60 E27 WW ND 1CT/1
Dimensions	60*110
Light output (lm)	470 lumen
Power (W)	5W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	470 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	35 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Length	110 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900963915
Energy Consumption kWh/1000 h	5
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 100W E27 WW A67 FR ND

Product description	PILA LED 100W E27 WW A67 FR ND
Light output (lm)	1521
Power (W)	15,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240/50Hz
Lamp shape	Bulb
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696526934
null	/8718696526934_Pila_EEL

Energy efficiency label





Specifications - Pila LEDClassic 60W A60 E27 WW ND 1CT/10

Product description	Pila LEDClassic 60W A60 E27 WW ND 1CT/10
Dimensions	60*110
Light output (lm)	806 lumen
Power (W)	7W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	806 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	50 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Length	110 mm
Energy efficiency class	A++
Average lifespan	15000h
EAN	8727900963939
Energy Consumption kWh/1000 h	7
Mercury content [in mg]	0mg

Energy efficiency label





Specifications - PILA LED 100W A67 E27 WW FR ND 1CT/6

Product description	PILA LED 100W A67 E27 WW FR ND 1CT/6
Dimensions	65*120
Light output (lm)	1521 lumen
Power (W)	14W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	1521 lumen
Lamp shape	A67
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	110 mA
Diameter	65 mm

SPECIFICATIONS (continued)

Length	120 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900963977
Energy Consumption kWh/1000 h	14
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 75W E27 WW A60 FR ND

Product description	PILA LED 75W E27 WW A60 FR ND
Light output (lm)	1055
Power (W)	12
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240/50Hz
Lamp shape	Bulb
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696526910
null	/8718696526910_Pila_EEL

Energy efficiency label





Specifications - PILA LED 40W E27 CW A60 ND

Product description	PILA LED 40W E27 CW A60 ND
Light output (lm)	500
Power (W)	5,5
CCT (K)	4000
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Bulb
Colour	Cool White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696491065
null	/8718696491065_Pila_EEL

Energy efficiency label





Specifications - PILA LED 40W E27 WW A60 ND

Product description	PILA LED 40W E27 WW A60 ND
Light output (lm)	470
Power (W)	5,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Bulb
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485361
null	/8718696485361_Pila_LED

Energy efficiency label





Specifications - PILA LED 60W A60 E27 CW FR ND 1CT/6

Product description	PILA LED 60W A60 E27 CW FR ND 1CT/6
Dimensions	60*109.6
Light output (lm)	810 lumen
Power (W)	7.5W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	200-240V
Voltage type	200-240V
Luminous intensity	810 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Cool white
Lamp current	72 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Length	109.6 mm
Energy efficiency class	a+
Average lifespan	15000h
EAN	8727900964097
Energy Consumption kWh/1000 h	8
Average life (at 2.7 hrs/day)	15 years
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 75W A60 E27 WW FR ND 1CT/6

Product description	PILA LED 75W A60 E27 WW FR ND 1CT/6
Dimensions	60*108
Light output (lm)	1055 lumen
Power (W)	10W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	1055 lumen
Lamp shape	A60
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	85 mA
Diameter	60 mm

SPECIFICATIONS (continued)

Diameter	60 mm
Length	108 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964110
Energy Consumption kWh/1000 h	10
Average life (at 2.7 hrs/day)	15 year
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W E14 WW B35 FR ND

Product description	PILA LED 25W E14 WW B35 FR ND
Light output (lm)	250
Power (W)	3,2
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Candle
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485248
null	/8718696485248_Pila_EEL

Energy efficiency label





Specifications - PILA LED 25W B35 E14 WW FR ND 1CT/10

Product description	PILA LED 25W B35 E14 WW FR ND 1CT/10
Dimensions	35*106
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	B35
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	30 mA
Diameter	35 mm

SPECIFICATIONS (continued)

Diameter	35 mm
Length	106 mm
Energy efficiency class	A+
Average lifespan	15000 h
EAN	8727900964158
Energy Consumption kWh/1000 h	4
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 40W B35 E14 WW FR ND 1CT/10

Product description	PILA LED 40W B35 E14 WW FR ND 1CT/10
Dimensions	35*106
Light output (lm)	470 lumen
Power (W)	5.5
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	470 lumen
Lamp shape	B35
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	45 mA
Diameter	35 mm

SPECIFICATIONS (continued)

Diameter	35 mm
Length	106 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964196
Energy Consumption kWh/1000 h	6
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W E14 WW B35 CL ND

Product description	PILA LED 25W E14 WW B35 CL ND
Light output (lm)	250
Power (W)	3,3
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Candle
Type of glass/cover	Clear
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485224
null	/8718696485224_Pila_EEL

Energy efficiency label





Specifications - PILA LED 40W B35 E14 WW FR DIM 1CT/10

Product description	PILA LED 40W B35 E14 WW FR DIM 1CT/10
Dimensions	35*103
Light output (lm)	470 lumen
Power (W)	6W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	Yes
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	470 lumen
Lamp shape	B35
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	30 mA
Diameter	35 mm

SPECIFICATIONS (continued)

Diameter	35 mm
Length	106 mm
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696549230
Energy Consumption kWh/1000 h	6
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 40W E14 WW B35 FR ND

Product description	PILA LED 40W E14 WW B35 FR ND
Light output (lm)	470
Power (W)	5,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Candle
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485262
null	/8718696485262_Pila_LED

Energy efficiency label





Specifications - PILA LED 40W E14 WW B35 FR DIM

Product description	PILA LED 40W E14 WW B35 FR DIM
Dimming	Yes
Lamp shape	Candle
Type of glass/cover	Frosted
Colour	Warm White
EAN	8718696549230

Energy efficiency label





Specifications - PILA LED 25W B35 E14 WW CL ND 1CT/10

Product description	PILA LED 25W B35 E14 WW CL ND 1CT/10
Dimensions	35*106
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	B35
Type of glass/cover	Clear
Colour	Warm white
Lamp current	30 mA
Diameter	35 mm

SPECIFICATIONS (continued)

Diameter	35 mm
Length	106 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964172
Energy Consumption kWh/1000 h	4
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W E14 WW P45 FR ND

Product description	PILA LED 25W E14 WW P45 FR ND
Light output (lm)	250
Power (W)	3,2
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Lustre
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485309
null	/8718696485309_Pila_LED

Energy efficiency label





Specifications - PILA LED 25W E27 WW P45 FR ND

Product description	PILA LED 25W E27 WW P45 FR ND
Light output (lm)	250
Power (W)	3,2
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Lustre
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485323
null	/8718696485323_Pila_LED

Energy efficiency label





Specifications - PILA LED 40W P45 E14 WW P45 FR ND

Product description	PILA LED 40W P45 E14 WW P45 FR ND
Dimensions	45*90
Light output (lm)	470 lumen
Power (W)	5.5W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	470 lumen
Lamp shape	P45
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	45 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964271
Energy Consumption kWh/1000 h	6
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 40W E14 WW P45 FR ND

Product description	PILA LED 40W E14 WW P45 FR ND
Light output (lm)	470
Power (W)	5,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Lustre
Type of glass/cover	Frosted
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485347
null	/8718696485347_Pila_LED

Energy efficiency label





Specifications - PILA LED 40W P45 E27 WW P45 FR ND

Product description	PILA LED 40W P45 E27 WW P45 FR ND
Dimensions	45*90
Light output (lm)	470 lumen
Power (W)	5.5W
CCT (K)	2700K
Colour consistency	6 steps
CRI	90
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240
Luminous intensity	470 lumen
Lamp shape	P45
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	45 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A ₊
Average lifespan	15000h
EAN	8727900964295
Energy Consumption kWh/1000 h	6
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W P45 E27 WW CL ND 1CT/10

Product description	PILA LED 25W P45 E27 WW CL ND 1CT/10
Dimensions	45*90
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	P45
Type of glass/cover	Clear
Colour	Warm white
Lamp current	30 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964257
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W P45 E14 WW FR ND

Product description	PILA LED 25W P45 E14 WW FR ND
Dimensions	45*90
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	P45
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	30 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964752
Energy Consumption kWh/1000 h	4
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W E14 WW P45 CL ND

Product description	PILA LED 25W E14 WW P45 CL ND
Light output (lm)	250
Power (W)	3,3
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Lustre
Type of glass/cover	Clear
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485286
null	/8718696485286_Pila_LED

Energy efficiency label





Specifications - PILA LED 25W P45 E14 WW CL ND 1CT/10

Product description	PILA LED 25W P45 E14 WW CL ND 1CT/10
Dimensions	45*90
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	P45
Type of glass/cover	Clear
Colour	Warm white
Lamp current	30 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964233
Energy Consumption kWh/1000 h	4
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W P45 E27 WW FR ND 1CT/10

Product description	PILA LED 25W P45 E27 WW FR ND 1CT/10
Dimensions	45*90
Light output (lm)	250 lumen
Power (W)	3.2W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240
Luminous intensity	250 lumen
Lamp shape	P45
Type of glass/cover	Frosted
Colour	Warm white
Lamp current	30 mA
Diameter	45 mm

SPECIFICATIONS (continued)

Diameter	45 mm
Length	90 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964417
Energy Consumption kWh/1000 h	4
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 25W G9 WW ND

Product description	PILA LED 25W G9 WW ND
Light output (lm)	250
Power (W)	2,8
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50-60Hz
Lamp shape	Spot
Colour	Warm White
Energy efficiency class	A++
Average lifespan	15000
EAN	8718696485446
null	/8718696485446_Pila_LED1

Energy efficiency label





Specifications - PILA LED 35W GU5.3 WW 12V 36D ND

Product description	PILA LED 35W GU5.3 WW 12V 36D ND
Light output (lm)	345
Power (W)	5,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	12V
Lamp shape	Spot
Colour	Warm White
Energy efficiency class	A
Average lifespan	15000
EAN	8718696485163
null	/8718696485163_Pila_LED

Energy efficiency label





Specifications - PILA LED 50W GU5.3 WW 12V 36D ND

Product description	PILA LED 50W GU5.3 WW 12V 36D ND
Dimensions	50*46
Light output (lm)	680 lumen
Power (W)	8W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	12V
Voltage type	12V
Luminous intensity	680 lumen
Lamp shape	MR16
Colour	Warm white
Lamp current	710 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	46 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964790
Energy Consumption kWh/1000 h	9
Rated peak intensity (cd)	1400 cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 65W GU10 CW 36D ND

Product description	PILA LED 65W GU10 CW 36D ND
CCT (K)	4000
CRI	80
Dimming	No
Voltage	220-240V/50HZ
Lamp shape	Spot
Colour	Cool white
Average lifespan	15000
EAN	8718696534229

Energy efficiency label





Specifications - PILA LED 20W GU5.3 WW 12V 36D ND

Product description	PILA LED 20W GU5.3 WW 12V 36D ND
Dimensions	50*46
Light output (lm)	250 lumen
Power (W)	2.8W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	12V
Voltage type	12V
Luminous intensity	250 lumen
Lamp shape	MR16
Colour	Warm white
Lamp current	350 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	46 mm
Energy efficiency class	A++
Average lifespan	15000h
EAN	8727900964639
Energy Consumption kWh/1000 h	4
Rated peak intensity (cd)	600 cd

Energy efficiency label





Specifications - PILA LED 50W GU10 CW 36D ND

Product description	PILA LED 50W GU10 CW 36D ND
Dimensions	50*54
Light output (lm)	420 lumen
Power (W)	4.7W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	420 lumen
Lamp shape	GU10
Colour	Cool white
Lamp current	38 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	54 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964899
Energy Consumption kWh/1000 h	5
Rated peak intensity (cd)	1000cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 35W GU10 CW 36D ND

Product description	PILA LED 35W GU10 CW 36D ND
Dimensions	50*54
Light output (lm)	280 lumen
Power (W)	3W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	280 lumen
Lamp shape	GU10
Colour	Cool white
Lamp current	27 mA
Diameter	50 mm
Length	54 mm

SPECIFICATIONS (continued)

Energy efficiency class	A++
Average lifespan	15000
EAN	8727900964875
Energy Consumption kWh/1000 h	3
Rated peak intensity (cd)	700 cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 50W GU5.3 CW 12V 36D ND

Product description	PILA LED 50W GU5.3 CW 12V 36D ND
Dimensions	50*46
Light output (lm)	700 lumen
Power (W)	8W
CCT (K)	4000K
Colour consistency	6 steps
CRI	90
Lumen maintenance	70%
Dimming	No
Voltage	12V
Voltage type	12V
Luminous intensity	700 lumen
Lamp shape	MR16
Colour	Cool white
Lamp current	710 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	46 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964851
Energy Consumption kWh/1000 h	9
Rated peak intensity (cd)	1400 cd
Average life (at 2.7 hrs/day)	0 mg

Energy efficiency label





Specifications - PILA LED 50W GU10 WW 36D ND

Product description	PILA LED 50W GU10 WW 36D ND
Light output (lm)	345
Power (W)	5,5
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Spot
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485200
null	/8718696485200_Pila_LED

Energy efficiency label





Specifications - PILA LED 65W GU10 WW 36D ND

Product description	PILA LED 65W GU10 WW 36D ND
Dimensions	50*56
Light output (lm)	460 lumen
Power (W)	5.5W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	460 lumen
Lamp shape	GU10
Colour	Warm white
Lamp current	45 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	56 mm
Energy efficiency class	A++
Average lifespan	15000h
EAN	8727900964592
Energy Consumption kWh/1000 h	6
Rated peak intensity (cd)	1054cd
Mercury content [in mg]	0mg

Energy efficiency label





Specifications - PILA LED 50W GU10 CW 60D ND

Product description	PILA LED 50W GU10 CW 60D ND
Light output (lm)	370
Power (W)	5,5
CCT (K)	4000
CRI	80
Dimming	No
Voltage	220-240/50Hz
Lamp shape	Spot
Colour	Cool White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696537015
null	/8718696537015_Pila_LED

Energy efficiency label





Specifications - PILA LED 50W GU10 WW 36D ND

Product description	PILA LED 50W GU10 WW 36D ND
Dimensions	50*54
Light output (lm)	380 lumen
Power (W)	4.7W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	380 lumen
Lamp shape	GU10
Colour	Warm white
Lamp current	38 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	54 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964516
Energy Consumption kWh/1000 h	5
Rated peak intensity (cd)	900 cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 60W E27 WW R63 36D DIM

Product description	PILA LED 60W E27 WW R63 36D DIM
Light output (lm)	380
Power (W)	5
CCT (K)	2700
CRI	80
Dimming	Yes
Voltage	220-240/50Hz
Lamp shape	Bulb
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696527092
null	/8718696527092_Pila_LED

Energy efficiency label





Specifications - PILA LED 35W GU10 WW 36D ND

Product description	PILA LED 35W GU10 WW 36D ND
Dimensions	50*54
Light output (lm)	250 lumen
Power (W)	3W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	250 lumen
Lamp shape	GU10
Colour	Warm white
Lamp current	27 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	54 mm
Energy efficiency class	A++
Average lifespan	15000h
EAN	8727900964479
Energy Consumption kWh/1000 h	3
Rated peak intensity (cd)	600cd
Mercury content [in mg]	0mg

Energy efficiency label





Specifications - PILA LED 35W GU10 WW 36D ND

Product description	PILA LED 35W GU10 WW 36D ND
Light output (lm)	230
Power (W)	3,3
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50Hz
Lamp shape	Spot
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485187
null	/8718696485187_Pila_LED

Energy efficiency label





Specifications - PILA LED 65W GU10 WW 36D ND

Product description	PILA LED 65W GU10 WW 36D ND
CCT (K)	2700
CRI	80
Dimming	No
Voltage	220-240V/50HZ
Lamp shape	Spot
Colour	Warm White
Average lifespan	15000
EAN	8718696534205

Energy efficiency label





Specifications - PILA LED 40W E14 WW R50 36D DIM

Product description	PILA LED 40W E14 WW R50 36D DIM
Power (W)	3,5
CCT (K)	2700
CRI	80
Dimming	Yes
Voltage	220-240V/50Hz
Lamp shape	Spot
Colour	Warm White
Energy efficiency class	A+
Average lifespan	15000
EAN	8718696485422
null	/8718696485422_Pila_LED

Energy efficiency label





Specifications - PILA LED 65W GU10 CW 36D ND

Product description	PILA LED 65W GU10 CW 36D ND
Dimensions	50*56
Light output (lm)	460 lumen
Power (W)	5.5W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240v
Voltage type	220-240V
Luminous intensity	460 lumen
Lamp shape	GU10
Colour	Cool White
Lamp current	45 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	56 mm
Energy efficiency class	A++
Average lifespan	15000
EAN	8727900964615
Energy Consumption kWh/1000 h	6
Rated peak intensity (cd)	1110cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 35W GU5.3 CW 12V 36D ND

Product description	PILA LED 35W GU5.3 CW 12V 36D ND
Dimensions	50*46
Light output (lm)	420 lumen
Power (W)	4.5W
CCT (K)	4000K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	12V
Voltage type	12V
Luminous intensity	420 lumen
Lamp shape	MR16
Colour	Cool white
Lamp current	550 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	46 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964837
Energy Consumption kWh/1000 h	6
Rated peak intensity (cd)	1000 cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 40W E14 WW R50 36D ND

Product description	PILA LED 40W E14 WW R50 36D ND
Dimensions	50*81
Power (W)	2.9W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Lamp shape	R50
Colour	Warm white
Lamp current	27 mA
Radiation angle	36 degree
Diameter	51 mm
Length	81 mm
Energy efficiency class	A++

SPECIFICATIONS (continued)

Energy efficiency class	A++
Average lifespan	15000h
EAN	8727900964912
Energy Consumption kWh/1000 h	3
Rated peak intensity (cd)	530 cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 35W GU5.3 WW 12V 36D ND

Product description	PILA LED 35W GU5.3 WW 12V 36D ND
Dimensions	50*46
Light output (lm)	380 lumen
Power (W)	4.5W
CCT (K)	2700K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	12V
Voltage type	12V
Luminous intensity	380 lumen
Lamp shape	MR16
Colour	Warm white
Lamp current	550 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	46 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964653
Energy Consumption kWh/1000 h	6
Rated peak intensity (cd)	900 cd
Mercury content [in mg]	0 mg

Energy efficiency label





Specifications - PILA LED 50W GU10 CDL 36D ND

Product description	PILA LED 50W GU10 CDL 36D ND
Dimensions	50*54
Light output (lm)	420 lumen
Power (W)	4.7W
CCT (K)	6500K
Colour consistency	6 steps
CRI	80
Lumen maintenance	70%
Dimming	No
Voltage	220-240V
Voltage type	220-240V
Luminous intensity	420 lumen
Lamp shape	GU10
Colour	Warm white
Lamp current	38 mA
Radiation angle	36 degree
Diameter	50 mm

SPECIFICATIONS (continued)

Length	54 mm
Energy efficiency class	A+
Average lifespan	15000h
EAN	8727900964530
Energy Consumption kWh/1000 h	5
Rated peak intensity (cd)	1000cd
Mercury content [in mg]	0 mg

Energy efficiency label





PILA Halogen Classic offers you the traditional bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - Halogen Classic 2000h 53W E27 230V A55 CL box

Product description	Halogen Classic 2000h 53W E27 230V A55 CL box
Light output (lm)	850
Power (W)	53
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961263
null	/8727900961263_energylabel.png

Energy efficiency label





PILA Halogen Classic offers you the traditional bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - Halogen Classic 2000h 42W E27 230V A55 box

Product description	Halogen Classic 2000h 42W E27 230V A55 box
Light output (lm)	630
Power (W)	42
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961225
null	/8727900961225_energylabel.png

Energy efficiency label





PILA Halogen Classic offers you the traditional bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - Halogen Classic 2000h 70W E27 230V A55CL box

Product description	Halogen Classic 2000h 70W E27 230V A55CL box
Light output (lm)	1200
Power (W)	70
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961294
null	/8727900961294_energylabel.png

Energy efficiency label





PILA Halogen Classic offers you the traditional bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - Halogen Classic 2000h 28W E27 230V A55 box

Product description	Halogen Classic 2000h 28W E27 230V A55 box
Light output (lm)	370
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961201
null	/8727900961201_energylabel.png

Energy efficiency label





PILA Halogen Classic offers you the classic decorative candle bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - EcoCI Pila 28W E27 230V B35 CL 1CT/5x10f

Product description	EcoCI Pila 28W E27 230V B35 CL 1CT/5x10f
Dimensions	36*97
Light output (lm)	370 lumen
Power (W)	28W
CCT (K)	2800K
CRI	100
Dimming	Yes
Voltage	230V
Voltage type	230V
Luminous intensity	370 lumen
Lamp shape	B35
Type of glass/cover	Clear
Colour	Warm white
Lamp current	122 mA
Diameter	36 mm
Length	97 mm
Energy efficiency class	D

SPECIFICATIONS (continued)

Average lifespan	2000h
EAN	8727900961904

Energy efficiency label





PILA Halogen Classic offers you the classic decorative candle bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - EcoCI Pila 28W E14 230V B35 CL 1CT/5x10f

Product description	EcoCI Pila 28W E14 230V B35 CL 1CT/5x10f
Dimensions	36*99
Light output (lm)	370 lumen
Power (W)	28W
CCT (K)	2800K
CRI	100
Dimming	Yes
Voltage	230V
Voltage type	230V
Luminous intensity	370 lumen
Lamp shape	B35
Type of glass/cover	Clear
Colour	Warm White
Lamp current	122 mA
Diameter	36 mm
Length	99 mm
Energy efficiency class	D

SPECIFICATIONS (continued)

Average lifespan	2000h
EAN	8727900961089

Energy efficiency label





PILA Halogen Classic offers you the classic decorative candle bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - EcoCI Pila 42W E27 230V B35 CL 1CT/5x10f

Product description	EcoCI Pila 42W E27 230V B35 CL 1CT/5x10f
Dimensions	36*97
Light output (lm)	630 lumen
Power (W)	42W
CCT (K)	2800K
CRI	100
Dimming	Yes
Voltage	230V
Voltage type	230V
Luminous intensity	630 lumen
Lamp shape	B35
Type of glass/cover	Clear
Colour	Warm white
Lamp current	183 mA
Diameter	36 mm
Length	97 mm
Energy efficiency class	D

SPECIFICATIONS (continued)

Average lifespan	2000h
EAN	8727900961928

Energy efficiency label





PILA Halogen Classic offers you the classic decorative candle bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - Halogen Classic Pila 18W E14 230V B35 1CT/5x10f

Product description	Halogen Classic Pila 18W E14 230V B35 1CT/5x10f
Light output (lm)	204
Power (W)	18
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963359
null	/8727900963359_Pila_Halogen0

Energy efficiency label





PILA Halogen Classic offers you the classic decorative candle bulb shape with a sparkling natural dimmable halogen light and double life. This PILA lamp is the ideal combination for all your home lighting needs.

Specifications - EcoCI Pila 42W E14 230V B35 CL 1CT/5x10f

Product description	EcoCI Pila 42W E14 230V B35 CL 1CT/5x10f
Dimensions	36*99
Light output (lm)	630 lumen
Power (W)	42W
CCT (K)	2800K
CRI	100
Dimming	Yes
Voltage	230V
Voltage type	230V
Luminous intensity	630 lumen
Lamp shape	B35
Type of glass/cover	Clear
Colour	Warm white
Lamp current	183 mA
Diameter	36 mm
Length	99 mm
Energy efficiency class	D

SPECIFICATIONS (continued)

Average lifespan	2000h
EAN	8718291209058

Energy efficiency label





PILA Capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All PILA capsules are fully dimmable.

Specifications - Capsule 20W G4 12V CL box

Product description	Capsule 20W G4 12V CL box
Light output (lm)	255
Power (W)	20
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Specialties
Energy efficiency class	C
Average lifespan	2000
EAN	8710619234377
null	/8710619234377_energylabel.png

Energy efficiency label





PILA Capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All PILA capsules are fully dimmable.

Specifications - Halogen MV Caps Pila 28W G9 230V 2BC/10

Product description	Halogen MV Caps Pila 28W G9 230V 2BC/10
Light output (lm)	370
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Specialties
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963250
null	/8727900963250_energylabel.png

Energy efficiency label





PILA Capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All PILA capsules are fully dimmable.

Specifications - Capsule 35W GY6.35 12V box

Product description	Capsule 35W GY6.35 12V box
Light output (lm)	535
Power (W)	35
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Specialties
Energy efficiency class	C
Average lifespan	2000
EAN	8710619234636
null	/8710619234636_energylabel.png

Energy efficiency label





PILA Capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All PILA capsules are fully dimmable.

Specifications - Capsule 20W G4 12V blister

Product description	Capsule 20W G4 12V blister
Light output (lm)	255
Power (W)	20
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Specialties
Energy efficiency class	C
Average lifespan	2000
EAN	8710619234100
null	/8710619234100_energylabel.png

Energy efficiency label





PILA Capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All PILA capsules are fully dimmable.

Specifications - Capsule 50W GY6.35 12V box

Product description	Capsule 50W GY6.35 12V box
Light output (lm)	850
Power (W)	50
CCT (K)	2900
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Specialties
Energy efficiency class	C
Average lifespan	2000
EAN	8710619234384
null	/8710619234384_energylabel.png

Energy efficiency label





PILA Capsule bulbs provide crisp, sparkling halogen light, bringing out the best in your luminaire. All PILA capsules are fully dimmable.

Specifications - CAPFIGHT Pila 20W G4 12V CL 1CT/10X10F

Product description	CAPFIGHT Pila 20W G4 12V CL 1CT/10X10F
Light output (lm)	255
Power (W)	20
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Specialties
Type of glass/cover	Clear
Energy efficiency class	C
Average lifespan	2000
EAN	8727900963519

Energy efficiency label



Specifications - Halogen Classic 2000h 42W E27 230V P45 CL box

Product description	Halogen Classic 2000h 42W E27 230V P45 CL box
Light output (lm)	630
Power (W)	42
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961140
null	/8727900961140_energylabel.png

Energy efficiency label



Specifications - Halogen Classic 2000h 28W E14 230V P45 CL box

Product description	Halogen Classic 2000h 28W E14 230V P45 CL box
Light output (lm)	370
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961164
null	/8727900961164_energylabel.png

Energy efficiency label



Specifications - Halogen Classic 2000h 28W E27 230V P45 CL box

Product description	Halogen Classic 2000h 28W E27 230V P45 CL box
Light output (lm)	370
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961126
null	/8727900961126_energylabel.png

Energy efficiency label



Specifications - Halogen Classic 2000h 42W E14 230V P45 CL box

Product description	Halogen Classic 2000h 42W E14 230V P45 CL box
Light output (lm)	630
Power (W)	42
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961188
null	/8727900961188_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic Pila 42W E14 230V NR50 1CT/10 SRP

Product description	Halogen Classic Pila 42W E14 230V NR50 1CT/10 SRP
Light output (lm)	250
Power (W)	42
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963212
null	/8727900963212_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Hal-Dich Pila 4y 20W GU5.3 12V 3BC/10

Product description	Hal-Dich Pila 4y 20W GU5.3 12V 3BC/10
Light output (lm)	205 lumen
Power (W)	20W
CCT (K)	3000K
CRI	100
Dimming	Yes
Voltage	12V
Voltage type	12V
Luminous intensity	205 lumen
Lamp shape	Reflector
Colour	Warm white
Radiation angle	36 degree
Diameter	50 mm
Length	46 mm
Energy efficiency class	B
Average lifespan	4000h
EAN	8727900963991

SPECIFICATIONS (continued)

Energy Consumption kWh/1000 h	21W (per 1000h)
Number of switch cycles	16000
Starting time	0 s
Warm-up time to 60% light	0 s
Average life (at 2.7 hrs/day)	4 years

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Hal-Dich Pila 4y 35W GU5.3 12V 3BC/10

Product description	Hal-Dich Pila 4y 35W GU5.3 12V 3BC/10
Light output (lm)	430 lumen
Power (W)	35W
CCT (K)	3000K
CRI	100
Dimming	Yes
Voltage	12V
Voltage type	12V
Lamp shape	Reflector
Colour	Warm white
Radiation angle	36 degree
Diameter	50 mm
Length	46 mm
Energy efficiency class	B
Average lifespan	4000h
EAN	8727900964011
Energy Consumption kWh/1000 h	37W (per 1000h)

SPECIFICATIONS (continued)

Number of switch cycles	16000
Starting time	0s
Warm-up time to 60% light	0 s
Average life (at 2.7 hrs/day)	4 year

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Hal-Twist Pila 25W GU10 230V 25D 2BC/10

Product description	Hal-Twist Pila 25W GU10 230V 25D 2BC/10
Light output (lm)	130
Power (W)	25
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Spot
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963236
null	/8727900963236_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic Pila 18W E14 230V NR50 1CT/10 SRP

Product description	Halogen Classic Pila 18W E14 230V NR50 1CT/10 SRP
Light output (lm)	76
Power (W)	18
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963274
null	/8727900963274_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Dichroic 20W GU5.3 12V 36D box

Product description	Dichroic 20W GU5.3 12V 36D box
Light output (lm)	205
Power (W)	20
CCT (K)	3000
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Spot
Energy efficiency class	B
Average lifespan	2000
EAN	8710619234322
null	/8710619234322_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic 2000h 28W E14 230V NR50 box

Product description	Halogen Classic 2000h 28W E14 230V NR50 box
Light output (lm)	136
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Bulb
Type of glass/cover	Clear
Energy efficiency class	D
Average lifespan	2000
EAN	8727900961102
null	/8727900961102_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Hal-Twist Pila 35W GU10 230V 40D 2BC/10

Product description	Hal-Twist Pila 35W GU10 230V 40D 2BC/10
Light output (lm)	185
Power (W)	35
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Spot
Energy efficiency class	D
Average lifespan	2000
EAN	8727900962949
null	/8727900962949_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic Pila 28W E27 230V NR63 1CT/10 SRP

Product description	Halogen Classic Pila 28W E27 230V NR63 1CT/10 SRP
Light output (lm)	145
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963151
null	/8727900963151_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic Pila 42W E27 230V E80 1CT/10 SRP

Product description	Halogen Classic Pila 42W E27 230V E80 1CT/10 SRP
Light output (lm)	265
Power (W)	42
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963199
null	/8727900963199_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic Pila 42W E27 230V NR63 1CT/10 SRP

Product description	Halogen Classic Pila 42W E27 230V NR63 1CT/10 SRP
Light output (lm)	270
Power (W)	42
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963175
null	/8727900963175_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Hal-Dich Pila 35W GU5.3 12V 36D 3BC/10

Product description	Hal-Dich Pila 35W GU5.3 12V 36D 3BC/10
Light output (lm)	430
Power (W)	35
CCT (K)	3000
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Spot
Energy efficiency class	B
Average lifespan	2000
EAN	8710619234148
null	/8710619234148_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Dichroic 20W GU5.3 12V 36D blister

Product description	Dichroic 20W GU5.3 12V 36D blister
Light output (lm)	205
Power (W)	20
CCT (K)	3000
CRI	100
Dimming	Yes
Voltage	12
Lamp shape	Spot
Energy efficiency class	B
Average lifespan	2000
EAN	8710619234124
null	/8710619234124_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Hal-Twist Pila 50W GU10 230V 40D 2BC/10

Product description	Hal-Twist Pila 50W GU10 230V 40D 2BC/10
Light output (lm)	330
Power (W)	50
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Spot
Energy efficiency class	D
Average lifespan	2000
EAN	8727900962963
null	/8727900962963_energylabel.png

Energy efficiency label





PILA spots provide directional halogen light in natural, sparkling tones. These halogen lamps are designed to provide focused beams, creating bright accents in your home. All PILA halogen spots are fully dimmable.

Specifications - Halogen Classic Pila 28W E14 230V R39 45D 1CT/10 SRP

Product description	Halogen Classic Pila 28W E14 230V R39 45D 1CT/10 SRP
Light output (lm)	150
Power (W)	28
CCT (K)	2800
CRI	100
Dimming	Yes
Voltage	230
Lamp shape	Candle
Energy efficiency class	D
Average lifespan	2000
EAN	8727900963373
null	/8727900963373_energylabel.png

Energy efficiency label





This PILA energy-saving bulb provides warm, soft light that is easy on the eyes. For a cosy atmosphere. With its 6-year lifetime, this low-consumption bulb will save you money while complementing your luminaires beautifully.

Specifications - Economy bulb A70 18W WW E27 box

Product description	Economy bulb A70 18W WW E27 box
Light output (lm)	1050
Power (W)	18
CCT (K)	2700
CRI	81
Dimming	No
Voltage	220-240
Lamp shape	Bulb
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962062
null	/8727900962062_energylabel.png

Energy efficiency label





This PILA energy-saving bulb provides warm, soft light that is easy on the eyes. For a cosy atmosphere. With its 6-year lifetime, this low-consumption bulb will save you money while complementing your luminaires beautifully.

Specifications - Economy bulb A55 11W WW E27 box

Product description	Economy bulb A55 11W WW E27 box
Light output (lm)	580
Power (W)	11
CCT (K)	2700
CRI	81
Dimming	No
Voltage	220-240
Lamp shape	Bulb
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962123
null	/8727900962123_energylabel.png

Energy efficiency label





This PILA energy-saving bulb provides warm, soft light that is easy on the eyes. For a cosy atmosphere. With its 6-year lifetime, this low-consumption bulb will save you money while complementing your luminaires beautifully.

Specifications - Economy Candle 12W WW E14 box

Product description	Economy Candle 12W WW E14 box
Light output (lm)	610
Power (W)	12
CCT (K)	2700
CRI	81
Dimming	No
Voltage	220-240
Lamp shape	Candle
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962604
null	/8727900962604_energylabel.png

Energy efficiency label





If you require a basic energy-saving bulb in a compact design, this Economy light bulb is the best "value for money" choice. Lasting up to 6 years, this PILA compact bulb will save up to 80% energy and money.

Specifications - Economy Stick 11W WW E14 box

Product description	Economy Stick 11W WW E14 box
Light output (lm)	660
Power (W)	11
CCT (K)	2700
CRI	81
Dimming	No
Lamp shape	Stick
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962260
null	/energy-labels/8727900962260_energylabel

Energy efficiency label





If you require a basic energy-saving bulb in a compact design, this Economy light bulb is the best "value for money" choice. Lasting up to 6 years, this PILA compact bulb will save up to 80% energy and money.

Specifications - Economy Stick 8W WW E27 box

Product description	Economy Stick 8W WW E27 box
Light output (lm)	460
Power (W)	8
CCT (K)	2700
CRI	81
Dimming	No
Voltage	220-240
Lamp shape	Stick
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962222
null	/energy-labels/8727900962222_energylabel

Energy efficiency label





If you require a basic energy-saving bulb in a compact design, this Economy light bulb is the best "value for money" choice. Lasting up to 6 years, this PILA compact bulb will save up to 80% energy and money.

Specifications - Economy Stick 14W WW E27 box

Product description	Economy Stick 14W WW E27 box
Light output (lm)	856
Power (W)	14
CCT (K)	2700
CRI	81
Dimming	No
Voltage	220-240
Lamp shape	Stick
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962284
null	/8727900962284_energylabel.png

Energy efficiency label





If you require a basic energy-saving bulb in a compact design, this Economy light bulb is the best "value for money" choice. Lasting up to 6 years, this PILA compact bulb will save up to 80% energy and money.

Specifications - Economy Stick 11W WW E27 box

Product description	Economy Stick 11W WW E27 box
Light output (lm)	660
Power (W)	11
CCT (K)	2700
CRI	81
Dimming	No
Voltage	220-240
Lamp shape	Stick
Colour	Warm White
Energy efficiency class	A
Average lifespan	6000
EAN	8727900962246
null	/8727900962246_energylabel.png

Energy efficiency label





Specifications - LF80 58W Cool Daylight 1SL/25

Product description	LF80 58W Cool Daylight 1SL/25
Light output (lm)	4410
Power (W)	58
CCT (K)	6500
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Cool Daylight
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015706

Energy efficiency label





Specifications - LF80 18W Warm White 1SL/25

Product description	LF80 18W Warm White 1SL/25
Light output (lm)	1300
Power (W)	18
CCT (K)	3000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Warm White
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015546

Energy efficiency label





Specifications - LF80 36W Cool Daylight 1SL/25

Product description	LF80 36W Cool Daylight 1SL/25
Light output (lm)	2800
Power (W)	36
CCT (K)	6500
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Cool Daylight
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015645

Energy efficiency label





Specifications - LF80 36W Warm White 1SL/25

Product description	LF80 36W Warm White 1SL/25
Light output (lm)	3110
Power (W)	36
CCT (K)	3000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Warm White
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015607

Energy efficiency label





Specifications - LF80 36W Cool White 1SL/25

Product description	LF80 36W Cool White 1SL/25
Light output (lm)	3100
Power (W)	36
CCT (K)	4000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Cool White
Energy efficiency class	A
Average lifespan	13000
EAN	8727900961775

Energy efficiency label





Specifications - LF80 36W Natural Daylight 1SL/25

Product description	LF80 36W Natural Daylight 1SL/25
Light output (lm)	2800
Power (W)	36
CCT (K)	5000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Natural Daylight
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015621

Energy efficiency label





Specifications - LF80 58W Natural Daylight 1SL/25

Product description	LF80 58W Natural Daylight 1SL/25
Light output (lm)	4410
Power (W)	58
CCT (K)	5000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Natural Daylight
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015683

Energy efficiency label





Specifications - LF80 18W Natural Daylight 1SL/25

Product description	LF80 18W Natural Daylight 1SL/25
Light output (lm)	1150
Power (W)	18
CCT (K)	5000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Natural Daylight
Energy efficiency class	B
Average lifespan	13000
EAN	8727900015560

Energy efficiency label





Specifications - LF80 58W Cool White 1SL/25

Product description	LF80 58W Cool White 1SL/25
Light output (lm)	4850
Power (W)	58
CCT (K)	4000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Cool White
Energy efficiency class	A
Average lifespan	13000
EAN	8727900961799

Energy efficiency label





Specifications - LF80 58W Warm White 1SL/25

Product description	LF80 58W Warm White 1SL/25
Light output (lm)	4850
Power (W)	58
CCT (K)	3000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Warm White
Energy efficiency class	A
Average lifespan	13000
EAN	8727900015669

Energy efficiency label





Specifications - LF80 18W Cool Daylight 1SL/25

Product description	LF80 18W Cool Daylight 1SL/25
Light output (lm)	1150
Power (W)	18
CCT (K)	6500
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Cool Daylight
Energy efficiency class	B
Average lifespan	13000
EAN	8727900015584

Energy efficiency label





Specifications - LF80 18W Cool White 1SL/25

Product description	LF80 18W Cool White 1SL/25
Light output (lm)	1300
Power (W)	18
CCT (K)	4000
CRI	85
Dimming	Yes
Lamp shape	Tube
Colour	Cool White
Energy efficiency class	A
Average lifespan	13000
EAN	8727900961751

Energy efficiency label

