

PHILIPS

Lighting



Everything you value in a Halogen PAR38 with the benefits of LED. Accent your merchandise or space without distraction.

LED PAR38

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

Light to go

Compatible
configurations

Lamps

12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB
12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB
12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB
12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB

14PAR38/LED/830/F25/DIM/ULW/120V 6/1FB
14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB
10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB
10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB

every
job matters

LED PAR38

Application

- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions



PAR30L



PAR38



PAR38 E26



E26 PAR38



PAR38



LEDspot PAR38 E26



Single Contact Medium Screw PAR
4.75 inch/121mm



Single Contact Medium Screw PAR
3.75 inch/95mm Long

LED PAR38

Versions





Single Contact Medium Screw PAR
3.75 inch/95mm Short



Single Contact Medium Screw PAR
4.75 inch/121mm

Dimensional drawing







Product	D	C
14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm
12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	122 mm	134 mm
14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm

Product	D	C
12PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1	121 mm	132 mm
12PAR38/AMB/835/F25/GL/DIM/FB/1PK 6/1	121 mm	132 mm
14PAR38/AMB/835/F25/GL/DIM/FB/1PK 6/1	121 mm	132 mm
14PAR38/AMB/835/F40/GL/DIM/FB/1PK 6/1	121 mm	132 mm
17PAR38/EXPERTCOLOR/S8/940/DIM/120V	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR/F40/940/DIM	94.8 mm	93.1 mm
17PAR38/EXPERTCOLOR/F25/940/DIM	94.8 mm	93.1 mm
17PAR38/EXPERTCOLOR/F25/927/DIM/120V	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR/S8/927/DIM/120V	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR/F25/927/DIM B	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR/F40/927/DIM	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR RETAIL/S8/930/DIM	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM B	120.7 mm	134.6 mm
17PAR38/EXPERTCOLOR RETAIL/F40/930/DIM	120.7 mm	134.6 mm

LED PAR38

Dimensional drawing



Product	D	C
33PAR38/PER/830/S15/DIM/120V 6/1FB	123 mm	133 mm
33PAR38/PER/830/S15/DIM/120V B 6/1FB	123 mm	133 mm
33PAR38/PER/830/F25/DIM/120V 6/1FB	123 mm	133 mm
33PAR38/PER/830/F25/DIM/120V B 6/1FB	123 mm	133 mm
36PAR38/PER/830/F25/ND/120V 6/1FB	123 mm	133 mm
36PAR38/PER/830/S15/ND/120V 6/1FB	123 mm	133 mm

Product
23PAR30s/PER/930/F25/ND/120V 6/1FB
23PAR30s/PER/930/S15/ND/120V 6/1FB

Product
25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB
25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB
25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB
25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB

Product	D	C
16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	120.7 mm	134.6 mm
16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	120.7 mm	134.6 mm
16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	120.7 mm	134.6 mm

LED PAR38

Operating and Electrical

Starting Time (Nom) 0.5 s

General Information

Cap-Base E26

Light Technical

Llmf At End Of Nominal Lifetime (Nom) 70 %

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
470996	17PAR38/EC RETAIL/S8/930/DIM 6/1	Yes	529685	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	Yes
471003	17PAR38/EC RETAIL/F25/930/DIM 6/1	Yes	529693	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	Yes
471011	17PAR38/EC RETAIL/F40/930/DIM 6/1	Yes	474676	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	Yes
470823	17PAR38/EC/S8/927/DIM/120V 10/1	Yes	474684	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	Yes
470831	17PAR38/EC/F25/927/DIM/120V 6/1	Yes	474692	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	Yes
470849	17PAR38/EC/F40/927/DIM/120V 6/1	Yes	474700	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	Yes
471797	17PAR38/EXPERTCOLOR/S8/940/DIM/120V 6/1	Yes	470872	17PAR38/EC/F25/940/DIM/120V 6/1	Yes
471029	17PAR38/EC RETAIL/F25/930/DIM 6/1	Yes	470880	17PAR38/EC/F40/940/DIM/120V 6/1	Yes
470864	17PAR38/EC/F25/927/DIM/120V B 6/1	Yes	534859	16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	Yes
529503	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	Yes	534867	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	Yes
529529	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	Yes	534883	16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	Yes
529537	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	Yes	534586	36PAR38/PER/830/S15/ND/120V 6/1FB	No
529545	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	Yes	534594	36PAR38/PER/830/F25/ND/120V 6/1FB	No
529552	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	Yes	534602	33PAR38/PER/830/S15/DIM/120V 6/1FB	Yes
529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	Yes	534610	33PAR38/PER/830/F25/DIM/120V 6/1FB	Yes
529602	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	Yes	534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	No
529610	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	Yes	534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	No
529628	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	Yes	534669	25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB	No
529636	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	Yes	534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	No
529644	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	Yes	534685	23PAR30s/PER/930/S15/ND/120V 6/1FB	No
529651	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	Yes	534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	No
529669	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	Yes	534628	33PAR38/PER/830/S15/DIM/120V B 6/1FB	Yes
529677	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	Yes	534636	33PAR38/PER/830/F25/DIM/120V B 6/1FB	Yes

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated)	Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated)
470996	17PAR38/EC RETAIL/S8/930/DIM 6/1	60 Hz	120 V	100 W	17 W	470849	17PAR38/EC/F40/927/DIM/120V 6/1	60 Hz	120 V	120 W	17 W
471003	17PAR38/EC RETAIL/F25/930/DIM 6/1	60 Hz	120 V	120 W	17 W	471797	17PAR38/EXPERTCOLOR/S8/940/DIM/120V 6/1	60 Hz	120 V	100 W	17 W
471011	17PAR38/EC RETAIL/F40/930/DIM 6/1	60 Hz	120 V	120 W	17 W	471029	17PAR38/EC RETAIL/F25/930/DIM 6/1	60 Hz	120 V	120 W	17 W
470823	17PAR38/EC/S8/927/DIM/120V 10/1	60 Hz	120 V	100 W	17 W	470864	17PAR38/EC/F25/927/DIM/120V B 6/1	60 Hz	120 V	120 W	17 W
470831	17PAR38/EC/F25/927/DIM/120V 6/1	60 Hz	120 V	120 W	17 W						

LED PAR38

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
529503	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529529	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	50 to 60 Hz	120 V	120 W	14 W
529537	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529545	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529552	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529602	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529610	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	120 W	14 W
529628	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529636	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529644	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529651	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529669	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529677	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529685	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
529693	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	50 to 60 Hz	120 V	90 W	12 W
474676	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	50 to 60 Hz	120 V	120 W	14 W
474684	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	50 to 60 Hz	120 V	120 W	14 W
474692	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	50 to 60 Hz	120 V	90 W	12 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
474700	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	50 to 60 Hz	120 V	90 W	12 W
470872	17PAR38/EC/F25/940/DIM/120V 6/1	60 Hz	120 V	120 W	17 W
470880	17PAR38/EC/F40/940/DIM/120V 6/1	60 Hz	120 V	120 W	17 W
534859	16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	60 Hz	120 V	120 W	16.5 W
534867	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	60 Hz	120 V	120 W	16.5 W
534883	16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	60 Hz	120 V	120 W	16.5 W
534586	36PAR38/PER/830/S15/ND/120V 6/1FB	50 to 60 Hz	120 V	250 W	36 W
534594	36PAR38/PER/830/F25/ND/120V 6/1FB	50 to 60 Hz	120 V	250 W	36 W
534602	33PAR38/PER/830/S15/DIM/120V 6/1FB	50 to 60 Hz	120 V	250 W	33 W
534610	33PAR38/PER/830/F25/DIM/120V 6/1FB	50 to 60 Hz	120 V	250 W	33 W
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534669	25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534685	23PAR30s/PER/930/S15/ND/120V 6/1FB	50 to 60 Hz	120 V	75 W	23 W
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	50 to 60 Hz	120 V	75 W	23 W
534628	33PAR38/PER/830/S15/DIM/120V B 6/1FB	50 to 60 Hz	120 V	250 W	33 W
534636	33PAR38/PER/830/F25/DIM/120V B 6/1FB	50 to 60 Hz	120 V	250 W	33 W

General Information

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
470996	17PAR38/EC RETAIL/S8/930/DIM 6/1	25000 h	50000X
471003	17PAR38/EC RETAIL/F25/930/DIM 6/1	40000 h	50000X
471011	17PAR38/EC RETAIL/F40/930/DIM 6/1	25000 h	50000X
470823	17PAR38/EC/S8/927/DIM/120V 10/1	40000 h	50000X
470831	17PAR38/EC/F25/927/DIM/120V 6/1	40000 h	50000X
470849	17PAR38/EC/F40/927/DIM/120V 6/1	40000 h	50000X

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
471797	17PAR38/EXPERTCOLOR/S8/940/DIM/120V 6/1	40000 h	50000X
471029	17PAR38/EC RETAIL/F25/930/DIM 6/1	25000 h	50000X
470864	17PAR38/EC/F25/927/DIM/120V B 6/1	40000 h	50000X
529503	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	25000 h	25000X

LED PAR38

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
529529	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	25000 h	25000X
529537	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	25000 h	25000X
529545	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	25000 h	25000X
529552	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529602	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529610	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529628	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	25000 h	25000X
529636	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	25000 h	25000X
529644	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	25000 h	25000X
529651	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	25000 h	25000X
529669	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529677	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529685	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
529693	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	25000 h	25000X
474676	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	25000 h	25000X

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
474684	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	25000 h	25000X
474692	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	25000 h	25000X
474700	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	25000 h	25000X
470872	17PAR38/EC/F25/940/DIM/120V 6/1	40000 h	50000X
470880	17PAR38/EC/F40/940/DIM/120V 6/1	40000 h	50000X
534859	16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	25000 h	50000X
534867	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	25000 h	50000X
534883	16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	25000 h	50000X
534586	36PAR38/PER/830/S15/ND/120V 6/1FB	25000 h	50000X
534594	36PAR38/PER/830/F25/ND/120V 6/1FB	25000 h	50000X
534602	33PAR38/PER/830/S15/DIM/120V 6/1FB	25000 h	50000X
534610	33PAR38/PER/830/F25/DIM/120V 6/1FB	25000 h	50000X
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	25000 h	50000X
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	25000 h	50000X
534669	25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB	25000 h	50000X
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	25000 h	50000X
534685	23PAR30s/PER/930/S15/ND/120V 6/1FB	25000 h	50000X
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	25000 h	50000X
534628	33PAR38/PER/830/S15/DIM/120V B 6/1FB	25000 h	50000X
534636	33PAR38/PER/830/F25/DIM/120V B 6/1FB	25000 h	50000X

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color		
					Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
470996	17PAR38/EC RETAIL/S8/930/DIM 6/1	8 °	930	3000 K	90	1200 lm	22000 cd
471003	17PAR38/EC RETAIL/F25/930/DIM 6/1	25 °	930	3000 K	90	1200 lm	6000 cd
471011	17PAR38/EC RETAIL/F40/930/DIM 6/1	40 °	930	3000 K	90	1200 lm	2700 cd
470823	17PAR38/EC/S8/927/DIM/120V 10/1	8 °	927	2700 K	95	1150 lm	21000 cd
470831	17PAR38/EC/F25/927/DIM/120V 6/1	25 °	927	2700 K	95	1150 lm	5800 cd
470849	17PAR38/EC/F40/927/DIM/120V 6/1	40 °	927	2700 K	95	1150 lm	2600 cd
471797	17PAR38/EXPERTCOLOR/S8/940/DIM/120V 6/1	8 °	940	4000 K	95	1300 lm	25000 cd
471029	17PAR38/EC RETAIL/F25/930/DIM 6/1	25 °	930	3000 K	90	1200 lm	6000 cd
470864	17PAR38/EC/F25/927/DIM/120V B 6/1	25 °	927	2700 K	95	1150 lm	5800 cd
529503	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	25 °	827	2700 K	80	1150 lm	5700 cd
529529	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	25 °	830	3000 K	80	1200 lm	6000 cd
529537	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	25 °	841	4000 K	80	1200 lm	6000 cd
529545	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	25 °	850	5000 K	80	1200 lm	6000 cd

LED PAR38

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color		
					Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
529552	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	40 °	827	2700 K	80	1150 lm	2450 cd
529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	40 °	830	3000 K	80	1200 lm	2500 cd
529602	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	40 °	841	4000 K	80	1200 lm	2500 cd
529610	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	40 °	850	5000 K	80	1200 lm	2500 cd
529628	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	25 °	827	2700 K	80	850 lm	4100 cd
529636	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	25 °	830	3000 K	80	900 lm	4100 cd
529644	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	25 °	841	4000 K	80	900 lm	4100 cd
529651	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	25 °	850	5000 K	80	900 lm	4100 cd
529669	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	40 °	827	2700 K	80	850 lm	1800 cd
529677	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	40 °	830	3000 K	80	900 lm	1900 cd
529685	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	40 °	841	4000 K	80	900 lm	1900 cd
529693	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	40 °	850	5000 K	80	900 lm	1900 cd
474676	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	25 °	835	3500 K	80	1200 lm	6000 cd
474684	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	40 °	835	3500 K	80	1200 lm	2500 cd
474692	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	25 °	835	3500 K	80	900 lm	4100 cd
474700	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	40 °	835	3500 K	80	900 lm	1900 cd
470872	17PAR38/EC/F25/940/DIM/120V 6/1	25 °	940	4000 K	95	1300 lm	6500 cd
470880	17PAR38/EC/F40/940/DIM/120V 6/1	40 °	940	4000 K	95	1300 lm	3000 cd
534859	16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	25 °	930	3000 K	90	1250 lm	6000 cd
534867	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	40 °	930	3000 K	90	1250 lm	2700 cd
534883	16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	40 °	927	2700 K	95	1150 lm	2600 cd
534586	36PAR38/PER/830/S15/ND/120V 6/1FB	15 °	830	3000 K	80	3800 lm	31000 cd
534594	36PAR38/PER/830/F25/ND/120V 6/1FB	25 °	830	3000 K	80	3800 lm	11000 cd
534602	33PAR38/PER/830/S15/DIM/120V 6/1FB	15 °	830	3000 K	80	3000 lm	35000 cd
534610	33PAR38/PER/830/F25/DIM/120V 6/1FB	25 °	830	3000 K	80	3000 lm	10000 cd
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	15 °	830	3000 K	80	2500 lm	16000 cd
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	25 °	830	3000 K	80	2500 lm	11500 cd
534669	25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB	15 °	930	3000 K	90	2150 lm	13500 cd
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	25 °	930	3000 K	90	2150 lm	10000 cd
534685	23PAR30s/PER/930/S15/ND/120V 6/1FB	15 °	930	3000 K	90	1900 lm	12000 cd
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	25 °	930	3000 K	90	1900 lm	9000 cd
534628	33PAR38/PER/830/S15/DIM/120V B 6/1FB	15 °	830	3000 K	80	3000 lm	35000 cd
534636	33PAR38/PER/830/F25/DIM/120V B 6/1FB	25 °	830	3000 K	80	3000 lm	10000 cd

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape	Order Code	Full Product Name	Bulb Shape
470996	17PAR38/EC RETAIL/S8/930/DIM 6/1	PAR38	529552	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	PAR38
471003	17PAR38/EC RETAIL/F25/930/DIM 6/1	PAR38	529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	PAR38
471011	17PAR38/EC RETAIL/F40/930/DIM 6/1	PAR38	529602	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	PAR38
470823	17PAR38/EC/S8/927/DIM/120V 10/1	PAR38	529610	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	PAR38
470831	17PAR38/EC/F25/927/DIM/120V 6/1	PAR38	529628	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	PAR38
470849	17PAR38/EC/F40/927/DIM/120V 6/1	PAR38	529636	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	PAR38
471797	17PAR38/EXPERTCOLOR/S8/940/DIM/120V 6/1	PAR38	529644	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	PAR38
471029	17PAR38/EC RETAIL/F25/930/DIM 6/1	PAR38	529651	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	PAR38
470864	17PAR38/EC/F25/927/DIM/120V B 6/1	PAR38	529669	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	PAR38
529503	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	PAR38	529677	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	PAR38
529529	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	PAR38	529685	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	PAR38
529537	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	PAR38	529693	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	PAR38
529545	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	PAR38	474676	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	PAR38

LED PAR38


Order Code	Full Product Name	Bulb Shape
474684	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	PAR38
474692	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	PAR38
474700	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	PAR38
470872	17PAR38/EC/F25/940/DIM/120V 6/1	PAR38
470880	17PAR38/EC/F40/940/DIM/120V 6/1	PAR38
534859	16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	PAR38
534867	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	PAR38
534883	16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	PAR38
534586	36PAR38/PER/830/S15/ND/120V 6/1FB	PAR38
534594	36PAR38/PER/830/F25/ND/120V 6/1FB	PAR38

Order Code	Full Product Name	Bulb Shape
534602	33PAR38/PER/830/S15/DIM/120V 6/1FB	PAR38
534610	33PAR38/PER/830/F25/DIM/120V 6/1FB	PAR38
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	PAR30L
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	PAR30L
534669	25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB	PAR30L
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	PAR30L
534685	23PAR30s/PER/930/S15/ND/120V 6/1FB	PAR30S
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	PAR30S
534628	33PAR38/PER/830/S15/DIM/120V B 6/1FB	PAR38
534636	33PAR38/PER/830/F25/DIM/120V B 6/1FB	PAR38











Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
470996	17PAR38/EC RETAIL/S8/930/DIM 6/1	90 °C
471003	17PAR38/EC RETAIL/F25/930/DIM 6/1	90 °C
471011	17PAR38/EC RETAIL/F40/930/DIM 6/1	90 °C
470823	17PAR38/EC/S8/927/DIM/120V 10/1	90 °C
470831	17PAR38/EC/F25/927/DIM/120V 6/1	90 °C
470849	17PAR38/EC/F40/927/DIM/120V 6/1	90 °C
471797	17PAR38/EXPERTCOLOR/S8/940/DIM/120V 6/1	90 °C
471029	17PAR38/EC RETAIL/F25/930/DIM 6/1	90 °C
470864	17PAR38/EC/F25/927/DIM/120V B 6/1	90 °C
529503	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	70 °C
529529	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	70 °C
529537	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	70 °C
529545	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	70 °C
529552	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	70 °C
529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	70 °C
529602	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	70 °C
529610	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	70 °C
529628	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	66 °C
529636	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	66 °C
529644	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	66 °C
529651	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	66 °C
529669	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	66 °C
529677	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	66 °C
529685	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	66 °C
529693	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	66 °C
474676	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	80 °C
474684	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	80 °C
474692	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	75 °C
474700	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	75 °C
470872	17PAR38/EC/F25/940/DIM/120V 6/1	90 °C
470880	17PAR38/EC/F40/940/DIM/120V 6/1	90 °C
534859	16.5PAR38/PER/930/F25/DIM/120V 6/1FB T20	90 °C
534867	16.5PAR38/PER/930/F40/DIM/120V 6/1FB T20	90 °C
534883	16.5PAR38/PER/927/F40/DIM/120V 6/1FB T20	90 °C
534586	36PAR38/PER/830/S15/ND/120V 6/1FB	90 °C
534594	36PAR38/PER/830/F25/ND/120V 6/1FB	90 °C
534602	33PAR38/PER/830/S15/DIM/120V 6/1FB	90 °C
534610	33PAR38/PER/830/F25/DIM/120V 6/1FB	90 °C











Order Code	Full Product Name	T-Case Maximum (Nom)
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	95 °C
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	95 °C
534669	25.5PAR30L/PER/930/S15/ND/120-277V 6/1FB	95 °C
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	95 °C
534685	23PAR30s/PER/930/S15/ND/120V 6/1FB	94 °C
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	94 °C
534628	33PAR38/PER/830/S15/DIM/120V B 6/1FB	90 °C
534636	33PAR38/PER/830/F25/DIM/120V B 6/1FB	90 °C













LED PAR38













LED PAR38




LED PAR38




LED PAR38




LED PAR38




Accent Diagrams




PAR38 120V 17-90W 1200lm 8D 3000K E26 D




PAR38 120V 17-120W 25D 3000K E26 D WH




PAR38 120V 17-120W 40D 3000K E26 D




PAR38 120V 17-120W 25D 3000K E26 D BL




14-120W E26 PAR38 25D 827 2700K




14-120W E26 PAR38 25D 830 3000K



LED Classic PAR38 14W E26 835 F25




14-120W E26 PAR38 25D 840 4000K




14-120W E26 PAR38 25D 850 5000K

LED PAR38


Accent Diagrams




14-120W E26 PAR38 40D 827 2700K




14-120W E26 PAR38 40D 830 3000K




LED Classic PAR38 14W E26 835 F40




14-120W E26 PAR38 40D 840 4000K




14-120W E26 PAR38 40D 850 5000K




12-90W E26 PAR38 25D 827 2700K




12-90W E26 PAR38 25D 830 3000K




LED Classic PAR38 12W E26 835 F25




12-90W E26 PAR38 25D 840 4000K



12-90W E26 PAR38 25D 850 5000K




12-90W E26 PAR38 40D 827 2700K




12-90W E26 PAR38 40D 830 3000K

LED PAR38


Accent Diagrams




LED Classic PAR38 12W E26 835 F40




12-90W E26 PAR38 40D 840 4000K




12-90W E26 PAR38 40D 850 5000K




PAR38_17W_1150lm 8D 2700K_E26




PAR38_17W_1150lm 25D 2700K_E26




PAR38_17W_1150lm 40D 2700K_E26




PAR38 17W 1300lm 25D 4000K E26




PAR38 17W 1300lm 40D 4000K E26




PAR38 17W 1300lm 8D 4000K E26



LEDspot PAR38 E26 25°




LEDspot PAR38 E26 40°




LEDspot PAR38 E26 927 40°


Accent Diagrams




LEDspot E26 PAR38 15D




LEDspot E26 PAR38 25D




LEDspot 33W E26 PAR38 S15




LEDspot 33W E26 PAR38 F25




LEDspot 25,5 PAR30L 830 S15




LEDspot 25,5 PAR30L 830 F25




LEDspot 25,5 PAR30L 930 S15



LEDspot 25,5 PAR30L 930 F25



LEDspot 23 PAR30L 930 S15




LEDspot 23 PAR30L 930 F25


LED PAR38

Beam Diagrams


PAR38 120V 17-90W 1200lm 8D 3000K E26 D




PAR38 120V 17-120W 25D 3000K E26 D WH




PAR38 120V 17-120W 40D 3000K E26 D




PAR38 120V 17-120W 25D 3000K E26 D BL




14-120W E26 PAR38 25D 827 2700K




14-120W E26 PAR38 25D 830 3000K




LED Classic PAR38 14W E26 835 F25



14-120W E26 PAR38 25D 840 4000K



14-120W E26 PAR38 25D 850 5000K




14-120W E26 PAR38 40D 827 2700K

14-120W E26 PAR38 40D 830 3000K


LED Classic PAR38 14W E26 835 F40

LED PAR38


Beam Diagrams




14-120W E26 PAR38 40D 840 4000K




14-120W E26 PAR38 40D 850 5000K




12-90W E26 PAR38 25D 827 2700K




12-90W E26 PAR38 25D 830 3000K




LED Classic PAR38 12W E26 835 F25




12-90W E26 PAR38 25D 840 4000K




12-90W E26 PAR38 25D 850 5000K




12-90W E26 PAR38 40D 827 2700K




12-90W E26 PAR38 40D 830 3000K



LED Classic PAR38 12W E26 835 F40




12-90W E26 PAR38 40D 840 4000K




12-90W E26 PAR38 40D 850 5000K

LED PAR38


Beam Diagrams




PAR38_17W_1150lm 8D 2700K_E26




PAR38_17W_1150lm 25D 2700K_E26




PAR38_17W_1150lm 40D 2700K_E26




PAR38 17W 1300lm 25D 4000K E26




PAR38 17W 1300lm 40D 4000K E26




PAR38 17W 1300lm 8D 4000K E26




LEDspot PAR38 E26 25°




LEDspot PAR38 E26 40°




LEDspot PAR38 E26 927 40°



LEDspot E26 PAR38 15D




LEDspot E26 PAR38 25D




LEDspot 33W E26 PAR38 S15

LED PAR38


Beam Diagrams




LEDSpot 33W E26 PAR38 F25




LEDspot 25,5 PAR30L 830 S15




LEDspot 25,5 PAR30L 830 F25




LEDspot 25,5 PAR30L 930 S15



LEDspot 25,5 PAR30L 930 F25



LEDspot 23 PAR30L 930 S15



LEDspot 23 PAR30L 930 F25

