

PHILIPS

Lighting



Affordable LED replacements for compact fluorescent 4-pin & 2-pin lamps

PL-C/T

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Benefits

- Reduced lighting costs
- Excellent lighting uniformity and lumen maintenance
- Unmatched compatibility with existing ballasts

Features

- Excellent energy efficiency
- Horizontal lamps rotate to ensure the best possible lighting effect
- Easy installation. Plug-and-play replacement of existing CFL-ni lamps
- Conventional form factor fits into existing luminaires

Application

- Retail & hospitality
- Residential
- Healthcare

Light to go

Compatible configurations

Lamps

10.5PL-C/T LED/26V-3500 IF 4P 10/1
10.5PL-C/T LED/26V-4000 IF 4P 10/1
12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1
12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1
12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1

12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1
5.5PL-C/LED/13V/840/IF5.5/P/4P 20/1
5PL-C/LED/13H/840/IF5/P/2P 20/1
5PL-C/LED/13V/840/IF5/P/2P 20/1

5PL-S/LED/13H/835/IF5/P/2P 20/1
5PL-S/LED/13H/840/IF5/P/2P 20/1
8.5PL-C/T LED/26H-3500 IF 4P 10/1
8.5PL-C/T LED/26H-4000 IF 4P 10/1


every
job matters

PL-C/T

Versions



G24q/GX24q



G24q/GX24q



LEDtube GX23-2



LEDtube GX23-2




LEDtube G24Q






LEDtube G24Q

Dimensional drawing



Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-2700 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-3500 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-4000 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm

Dimensional drawing





Product	D1	D2	A1	A2	A3
8.5PL-C/T LED/26H-4000 IF 4P 10/1	24.3 mm	28.4 mm	128.3 mm	147.5 mm	163.1 mm
12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm
12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm
12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm
12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm
8.5PL-C/T LED/26H-3000 IF 4P 10/1	24.3 mm	28.4 mm	128.3 mm	147.5 mm	163.1 mm
8.5PL-C/T LED/26H-2700 IF 4P 10/1	24.3 mm	28.4 mm	128.3 mm	147.5 mm	163.1 mm
8.5PL-C/T LED/26H-3500 IF 4P 10/1	24.3 mm	28.4 mm	128.3 mm	147.5 mm	163.1 mm

Product	D	A1	A2	A3
5.5PL-C/LED/13V/830/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/840/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/827/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/835/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm

Product	D	D1	A1	A2	A3
5PL-C/LED/13H/830/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/840/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/827/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/835/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Dimensional drawing



Product	D	A1	A2	A3
5PL-C/LED/13V/827/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/830/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/840/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/835/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm

Product	D	D1	A1	A2	A3
5.5PL-C/LED/13H/840/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/830/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/835/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/827/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Operating and Electrical

Starting Time (Nom)	0.5 s
---------------------	-------

General Information

Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X

Light Technical

Color Rendering Index (Nom)	82
Llmf At End Of Nominal Lifetime (Nom)	70 %

Temperature

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	Yes
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	Yes
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	Yes
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	Yes
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	Yes
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	Yes
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	Yes
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	Yes
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	Yes
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	Yes
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	Yes
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	Yes
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	Yes
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	Yes
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	Yes
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	No
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	No
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	No
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	No
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	No
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	No
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	No
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	No
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	Yes
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	Yes

Order Code	Full Product Name	Dimmable
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	Yes
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	Yes
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	Yes
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	Yes
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	Yes
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	Yes

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W

General Information

Order Code	Full Product Name	Cap-Base
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	G24Q
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	G24Q
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	G24Q
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	G24Q
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	G24Q
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	G24Q
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	G24Q
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	G24Q
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	GX24q
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	GX24q
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	GX24q
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	GX24q
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	GX24q
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	GX24q
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	GX24q
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	GX23-2

Order Code	Full Product Name	Cap-Base
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	GX23-2
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	GX23-2
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	GX23-2
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	GX23-2
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	GX23-2
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	GX23-2
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	GX23-2
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	G24Q
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	G24Q
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	G24Q
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	G24Q
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	G24Q
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	G24Q
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	G24Q
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	G24Q

Light Technical (1/2)

Order Code	Full Product Name	Correlated			
		Beam Angle (Nom)	Color Code	Temperature (Nom)	Luminous Flux (Nom)
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	-	827	2700 K	850 lm
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	-	830	3000 K	900 lm
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	-	835	3500 K	900 lm
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	-	841	4000 K	950 lm
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	-	827	2700 K	1300 lm
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	-	830	3000 K	1350 lm

Order Code	Full Product Name	Correlated			
		Beam Angle (Nom)	Color Code	Temperature (Nom)	Luminous Flux (Nom)
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	-	835	3500 K	1400 lm
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	-	841	4000 K	1450 lm
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	-	827	2700 K	1200 lm
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	-	835	3500 K	1200 lm
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	-	841	4000 K	1300 lm
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	-	827	2700 K	1350 lm

PL-C/T

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux (Nom)
			Color Code	Temperature (Nom)	
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	-	830	3000 K	1400 lm
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	-	835	3500 K	1450 lm
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	-	841	4000 K	1500 lm
532309	5PL- C/LED/13H/827/IF5/P/2P 20/1	150 °	827	2700 K	520 lm
532317	5PL- C/LED/13H/830/IF5/P/2 P 20/1	150 °	830	3000 K	550 lm
532333	5PL- C/LED/13H/835/IF5/P/2 P 20/1	150 °	835	3500 K	550 lm
532341	5PL- C/LED/13H/840/IF5/P/2 P 20/1	150 °	841	4000 K	580 lm
532358	5PL- C/LED/13V/827/IF5/P/2P 20/1	150 °	827	2700 K	520 lm
532366	5PL- C/LED/13V/830/IF5/P/2 P 20/1	150 °	830	3000 K	550 lm
532374	5PL- C/LED/13V/835/IF5/P/2P 20/1	150 °	835	3500 K	550 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux (Nom)
			Color Code	Temperature (Nom)	
532382	5PL- C/LED/13V/840/IF5/P/2 P 20/1	150 °	841	4000 K	580 lm
532390	5.5PL- C/LED/13H/827/IF5/P/4 P 20/1	150 °	827	2700 K	520 lm
532408	5.5PL- C/LED/13H/830/IF5/P/4 P 20/1	150 °	830	3000 K	550 lm
532416	5.5PL- C/LED/13H/835/IF5/P/4 P 20/1	150 °	835	3500 K	550 lm
532424	5.5PL- C/LED/13H/840/IF5/P/4 P 20/1	150 °	841	4000 K	580 lm
532432	5.5PL- C/LED/13V/827/IF5/P/4P 20/1	150 °	827	2700 K	520 lm
532440	5.5PL- C/LED/13V/830/IF5/P/4 P 20/1	150 °	830	3000 K	550 lm
532457	5.5PL- C/LED/13V/835/IF5/P/4 P 20/1	150 °	835	3500 K	550 lm
532465	5.5PL- C/LED/13V/840/IF5/P/4 P 20/1	150 °	841	4000 K	580 lm

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	850 lm
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	900 lm
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	900 lm
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	950 lm
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	1300 lm
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	1350 lm
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	1400 lm
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	1450 lm
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	1200 lm
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	1200 lm
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	1300 lm
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	1350 lm
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	1400 lm
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	1450 lm
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	1500 lm

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	-
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	-
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	-
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	-
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	-
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	-
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	-
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	-
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	-
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	-
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	-
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	-
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	-
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	-
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	-

PL-C/T

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	Frosted	-
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	Frosted	-
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	Frosted	-
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	Frosted	-
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	Frosted	PL-C
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	Frosted	PL-C
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	Frosted	PL-C
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	Frosted	PL-C
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	Frosted	-
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	Frosted	-
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	Frosted	-
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	Frosted	PL-C
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	Frosted	PL-C
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	Frosted	PL-C
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	Frosted	PL-C
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	-	-

Order Code	Full Product Name	Bulb Finish	Bulb Shape
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	-	-
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	-	-
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	-	-
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	-	-
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	-	-
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	-	-
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	-	-
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	-	-
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	-	-
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	-	-
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	-	-
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	-	-
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	-	-
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	-	-
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	-	-

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	60 °C
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	60 °C
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	60 °C
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	60 °C
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	-
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	-
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	-
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	-
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	60 °C
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	60 °C
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	60 °C
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	-
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	-
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	-
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	-
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	70 °C
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	70 °C
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	70 °C
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	70 °C
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	70 °C
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	70 °C
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	70 °C
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	70 °C
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	75 °C
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	75 °C
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	75 °C
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	70 °C
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	70 °C
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	70 °C
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	70 °C

