

PHILIPS

LED lamps

A-shape lamps



No matter the application, get the right light

Philips A-shape lamps provide a wide variety of features such as dimming and 3-way. Filament style, omni-directional light and various color temperatures make sure you always have the right light.

Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, government buildings, and multi-unit residences.

Light to go

Compatible configurations


Lamps

5A19/LED/950/P/E26/ND 4/4FB T20
5A19/PER/927/P/E26/DIM 6/1FB T20
5A19/PER/950/P/E26/DIM 6/1FB T20
8A19/LED/827/ND D2D 120V 6/1
8.8A19/PER/927/P/E26/DIM 6/1FB T20
8.8A19/PER/950/P/E26/DIM 6/1FB T20

12.2A21/PER/927/P/E26/DIM 6/1FB T20
12.5A19/LED/850/FR/P/ND 4/2FB
16A21/16A21/PER/927/P/E26/DIM 6/1FB T20
16A21/PER/950/P/E26/DIM 6/1FB T20
16.6A21/LED/950/P/E26/ND 6/1FB T20

every
job matters

Philips A-shape and decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

	Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	Lifetime ¹ (hrs)	CCT (K)	MC/CP ²	Material	Finish	Legend	
A19 - 25W lamp equivalent dimming															
W	543116	929002000703	4A19/MOD/840/E26/CL/GL/DIM 4/1BC	4	150	E26	120	80	15,000	4000	CP	Glass	Smokey	A	
A19 - 40W lamp equivalent non-dimming															
D	559229	929002311104	5A19/LED/827/FR/P/ND 4/2FB	5	450	E26	120	80	11,000	2700	CP	Plastic	Frosted	B	
D	554501	929002227003	5A19/LED/927/P/E26/ND 4/4FB T20	5	450	E26	120	90	11,000	2700	CP	Plastic	Frosted	C	
D	559518	929002311204	5A19/LED/850/FR/P/ND 4/2FB	5	450	E26	120	80	11,000	5000	CP	Plastic	Frosted	B	
D	554519	929002227103	5A19/LED/950/P/E26/ND 4/4FB T20	5	450	E26	120	90	11,000	5000	CP	Plastic	Frosted	C	
A19 - 40W lamp equivalent dimming															
W	556795	929001950933	4.5A19/VIN/820/E26/CL/GL/DIM 4/4FBH T20	4.5	350	E26	120	80	15,000	2000	CP	Glass	Amber	D	
W	549485	929001969504	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	5	450	E26	120	90	15,000	2700-2200	MC	Glass	Clear	E	
W	E	557595	929002327803	5A19/PER/927-22/FR/G/WGD 4/2FB T20	5	450	E26	120	90	15,000	2700-2200	MC	Glass	Frosted	F
D	E	479428	929001940704	5A19/PER/927-22/P/E26/WG 6/1FB T20	5	450	E26	120	90	15,000	2700-2200	MC	Plastic	Frosted	G
D	E	550400	929002035704	5A19/PER/927/P/E26/DIM 6/1FB T20	5	450	E26	120	90	15,000	2700	CP	Plastic	Frosted	C
D	E	550418	929002035804	5A19/PER/930/P/E26/DIM 6/1FB T20	5	450	E26	120	90	15,000	3000	CP	Plastic	Frosted	H
D	E	547042	929002035904	5A19/PER/940/P/E26/DIM 6/1FB T20	5	450	E26	120	90	15,000	4000	CP	Plastic	Frosted	C
W	E	549220	929002207804	5A19/PER/950/CL/G/E26/DIM 1FB T20	5	450	E26	120	90	15,000	5000	CP	Glass	Clear	I
D	E	550426	929002036004	5A19/PER/950/CL/P/E26/DIM 1FB T20	5	450	E26	120	90	15,000	5000	CP	Plastic	Frosted	C
A19 - 60W lamp equivalent non-dimming															
D	554428	929002227204	8.8A19/LED/927/P/E26/ND 6/1FB T20	8.8	800	E26	120	90	11,000	2700	CP	Plastic	Frosted	C	
D	559252	929002311304	8.5A/LED/827/FR/P/ND 4/2FB	8.5	800	E26	120	80	11,000	2700	CP	Plastic	Frosted	B	
D	559351	929002311404	8.5A19/LED/850/FR/P/ND 4/2FB	8.5	800	E26	120	80	11,000	5000	CP	Plastic	Frosted	B	
D	554444	929002227304	8.8A19/LED/950/P/E26/ND 6/1FB T20	8.8	800	E26	120	90	11,000	5000	CP	Plastic	Frosted	C	
A19 - 60W lamp equivalent dimming															
W	E	549493	929001969604	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	8	800	E26	120	90	15,000	2700-2200	MC	Glass	Clear	J
W	E	557587	929002327703	8.5A19/PER/927-22/FR/G/WGD 4/2FB T20	8.5	800	E26	120	90	15,000	2700-2200	MC	Glass	Frosted	F
D	E	479444	929001940904	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	8.8	800	E26	120	90	15,000	2700-2200	MC	Plastic	Frosted	G
D	E	550434	929002036104	8.8A19/PER/927/P/E26/DIM 6/1FB T20	8.8	800	E26	120	90	15,000	2700	CP	Plastic	Frosted	C
D	E	550442	929002036204	8.8A19/PER/930/P/E26/DIM 6/1FB T20	8.8	800	E26	120	90	15,000	3000	CP	Plastic	Frosted	C
D	E	557660	929002327504	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	8.8	800	GU24	120	90	15,000	3000	CP	Plastic	Frosted	K NEW
D	E	545897	929002032304	8.8A19/PER/940/P/E26/DIM 6/1FB T20	8.8	800	E26	120	90	15,000	4000	CP	Plastic	Frosted	H
W	E	549238	929002207904	8.8A19/PER/950/CL/G/E26/DIM 1FB T20	5	800	E26	120	90	15,000	5000	CP	Glass	Clear	I
D	E	550459	929002036304	8.8A19/PER/950/P/E26/DIM 6/1FB T20	8.8	800	E26	120	90	15,000	5000	CP	Plastic	Frosted	C

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures ■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20

Philips A-shape and decorative lamps



Ordering, electrical and technical data (Subject to change without notice)


Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	Lifetime ¹ (hrs)	CCT (K)	MC/CP ²	Material	Finish	Legend	
A19 / A21 - 75W lamp equivalent non-dimming														
D	559492	929002311504	10A19/LED/827/FR/P/E26/ND 4/2FB	10	1000	E26	120	80	11,000	2700	CP	Plastic	Frosted	A
D	554543	929002227433	12.2A21/LED/927/P/E26/ND 4/2FB T20	12.2	1100	E26	120	90	11,000	2700	CP	Plastic	Frosted	B
D	463000	929001958103	10A19/LED/850/FR/P/ND 4/2FB	10	1000	E26	120	80	11,000	5000	CP	Plastic	Frosted	C
D	554568	929002227533	12.2A21/LED/950/P/E26/ND 4/2FB T20	12.2	1100	E26	120	90	11,000	5000	CP	Plastic	Frosted	B
A21 - 75W lamp equivalent dimming														
D	479469	929001941104	12.2A21/PER/927-22/P/E26/WG 6/1FB T20	12.2	1100	E26	120	90	15,000	2700-2200	MC	Plastic	Frosted	B
D	550475	929002036404	12.2A21/PER/927/P/E26/DIM 6/1FB T20	12.2	1100	E26	120	90	15,000	2700	CP	Plastic	Frosted	B
D	550483	929002036504	12.2A21/PER/930/P/E26/DIM 6/1FB T20	12.2	1100	E26	120	90	15,000	3000	CP	Plastic	Frosted	B
D	547091	929002036604	12.2A21/PER/940/P/E26/DIM 6/1FB T20	12.2	1100	E26	120	90	15,000	4000	CP	Plastic	Frosted	B
D	550491	929002036704	12.2A21/PER/950/P/E26/DIM 6/1FB T20	12.2	1100	E26	120	90	15,000	5000	CP	Plastic	Frosted	B
A19/A21 - 100W equivalent lamps non-dimming														
D	559500	929002311704	13.5A19/LED/827/FR/P/ND 4/2FB	13.5	1500	E26	120	80	11,000	2700	CP	Plastic	Frosted	D
D	479989	929001825804	18A21/LED/927/P/E26/ND 6/1FB T20	18	1500	E26	120	90	11,000	2700	CP	Plastic	Frosted	B
D	554469	929002227604	16.6A21/LED/927/P/E26/ND 6/1FB T20	16.6	1500	E26	120	90	11,000	2700	CP	Plastic	Frosted	B
D	548248	929001958204	12.5A19/LED/850/FR/P/ND 4/2FB	12.5	1500	E26	120	80	11,000	5000	CP	Plastic	Frosted	D
D	559419	929002311804	13.5A19/LED/850/FR/P/ND 4/2FB	13.5	1500	E26	120	80	11,000	5000	CP	Plastic	Frosted	D
D	479997	929001860204	18A21/LED/950/P/E26/ND 6/1FB T20	18	1500	E26	120	90	11,000	5000	CP	Plastic	Frosted	B
D	554485	929002227704	16.6A21/LED/950/P/E26/ND 6/1FB T20	16.6	1500	E26	120	90	11,000	5000	CP	Plastic	Frosted	B
A21 - 100W equivalent lamps dimming														
D	479485	929001941304	16A21/PER/927-22/P/E26/WG 6/1FB T20	16	1600	E26	120	90	25,000	2700-2200	MC	Plastic	Frosted	B
D	550509	929002036804	16A21/PER/927/P/E26/DIM 6/1FB T20	16	1600	E26	120	90	15,000	2700	CP	Plastic	Frosted	B
D	557678	929002327604	16A21/PER/930/P/GU24/DIM 6/1FB T20	16	1600	GU24	120	90	15,000	3000	CP	Plastic	Frosted	E NEW
D	550517	929002036904	16A21/PER/930/P/E26/DIM 6/1FB T20	16	1600	E26	120	90	15,000	3000	CP	Plastic	Frosted	B
D	547125	929002037004	16A21/PER/940/P/E26/DIM 6/1FB T20	16	1600	E26	120	90	15,000	4000	CP	Plastic	Frosted	B
D	550525	929002037104	16A21/PER/950/P/E26/DIM 6/1FB T20	16	1600	E26	120	90	15,000	5000	CP	Plastic	Frosted	B
A21 - 150W equivalent lamps dimming														
D	558221	929002343003	29A21/PER/827-22/P/E26/WG/HO 4/1FB	29	2610	E26	120	80	15,000	2700-2200	MC	Plastic	Frosted	B NEW
D	558239	929002343103	29A21/PER/850/P/E26/DIM/HO 4/1FB	29	2610	E26	120	80	15,000	5000	CP	Plastic	Frosted	B NEW
Large A lamps - 160W-200W-300W equivalent														
E	479287	929001854715	20A30/LED/865/P/E26/ND 4/1FB	20	2300	E26	120	80	25,000	6500	CP	Plastic	Frosted	F
E	479295	929001854815	24A35/LED/865/P/E26E39/ND 4/1FB	24	3000	E26 / E39	120	80	25,000	6500	CP	Plastic	Frosted	G
E	479303	929001854915	42A40/LED/865/P/E26E39/ND 4/1FB	42	5000	E26 / E39	120	80	25,000	6500	CP	Plastic	Frosted	H

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures ■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20

Philips A-shape and decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Lgd
3-way switching lamps													
D	E	556928	929002285003	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	5/8/14	450/800/1600	E26	120	90	2700	25,000	MC	Plastic Frosted A
D	E	459164	929001174204	18A21/LED/827 3WAY ND 120V	5/8/18	450/800/1600	E26	120	80	2700	25,000	MC	Plastic Frosted A
D	E	556936	929002285103	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	6/13/18.5	620/1600/2150	E26	120	90	2700	15,000	MC	Plastic Frosted A
D	E	472548	929001356004	23A21/LED/827/E26d/3WAY/ND 120V FB 1PK	8/16/23	620/1600/2150	E26d	120	80	2700	15,000	MC	Plastic Frosted A
SceneSwitch lamps													
D	E	464965	929001261304	9.5A19/LED/827-25-22/ND SSWG 120V 6/1	9/4/2	800/320/80	E26	120	80	2700/2500/2200	15,000	MC	Plastic Frosted B
D	E	464973	929001261404	9.5A19/LED/850/ND SSDL 120V 6/1	9/3/1	800/320/80	E26	120	80	5000	15,000	MC	Plastic Frosted B
D	E	464957	929001263204	9.5A19/LED/827-50-22/ND SSSC 120V	9.5	800/800/80	E26	120	80	2700/5000/2200	15,000	MC	Plastic Frosted B
Dusk to Dawn lamps													
D	E	466581	929001261504	8A19/LED/827/ND D2D 120V 6/1	8.0	800	E26	120	80	2700	25,000	MC	Plastic Frosted C
D	E	557728	929002333603	8.8A19/AMB/927/ND D2D 4/1FB T20	8.8	800	E26	120	90	2700	15,000	MC	Plastic Frosted C

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures ■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.