

# Day-Brite

## CFI

by  Signify

Linear

Valueline SL undercabinet

T5



Day-Brite / CFI Valueline SL undercabinet is an economical T5 luminaire with electronic ballast. It is available in 12", 21", 24", 33", and 42" lengths.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide

Example: SL281-120-EB-LP

| Family                          | Lamping   | Voltage                            | Ballast                           | Options                         |
|---------------------------------|---|------------------------------------|-----------------------------------|---------------------------------|
| <input type="text" value="SL"/> | -   | <input type="text" value="120"/> - | <input type="text" value="EB"/> - | <input type="text" value="LP"/> |
| SL                              | 18 1-8WT5 (12.25")<br>113 1-13WT5 (21.25")<br>28 2-8WT5 (24.50")<br>281 1-8WT5/1-13WT5 (33.50")<br>213 2-13WT5 (42.50") | 120 120V                           | EB Electronic ballast             | LP Lamp provided (4100K)        |

### Replacement Lenses (order separately)

| Lens cat. # | Product |
|-------------|---------|
| • LSL12     | SL18    |
| • LSL21     | SL113   |
| • LSL24     | SL28    |
| • LSL33     | SL281   |
| • LSL42     | SL213   |

## Light to go

Compatible configurations

Luminaire

SL113-120      SL213-120  
 SL18-120-EB-LP  
 SL28-120-EB-LP  
 SL281-120



# SL Valueline undercabinets

## T5


### Construction/Finish

- Finish is baked white enamel.
- "L" shaped lens (luminous front) is white acrylic.
- 1-1/8" ultra slim styling creates an unobtrusive hidden light source.

### Electrical

- All units include electrical fitting to accept flexible conduit or romex.
- Rocker switch and convenience outlet supplied, shipped loose.
- cULus listed for damp locations.
- 841 4100K color temperature T5 lamp included.
- Available with 120V electronic ballast only.

### Dimensions



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at [www.lamprecycle.org](http://www.lamprecycle.org)

