


Ledinaire Surface Downlight

DN065C

























	10NC	Output (lm)	P (W)	A1	A2	В	kg
DN065C LED10S 830	9290026644	1000	11	100	120-130	175	0.47
DN065C LED10S 840	9290026645	1000	11				
DN065C LED20S 830	9290026646	2000	20	100	120-130	225	0.70
DN065C LED20S 840	9290026647	2000	20				



## **Inrush current**



	LED10S	LED20S		
	Electrical characteristics			
lmax (A)	5.05	5.18		
Tref (µs)	30	31		
МСВ	Luminaires Max.			
B-10 A	175	93		
B-13 A	227	122		
B-16 A	280	150		
C-10 A	175	93		
C-13 A	227	122		
C-16 A	280	150		

© 2021 Signify Holding Signify


Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.


3241 658 39791


Signify I.B.R.S. / C.C.R.I. Numéro 10461 


Signify Commercial UK Limited Unit 3, Guildford Business Park,

























- Please read this manual carefully before using the product.

  1. For indoor use only.

  2. Do not switch on before complete installation.

  3. The luminaries shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the
- national requirements.
  4. The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the luminaire shall be destroyed.
  5. The luminaire is complied with IEC 60598.
- 6. Luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, phthalates, etc,
- Authilitate indiction be used of stored in consider environment where negatives indicated stored as capital, plantage of the stored in consideration and present.
   Non-replaceable light source: The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
   This product contains a light source of energy efficiency class F.



This marking indicates that this product should not be disposed with other household wastes throughout the EU. To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.

2/2