



Dimensions




Specifications

Application	Solar Street Light
Туре	BRP710
Lamp	LED(2000 lumen)
Voltage	12 V DC
IP Classification	IP 65
Net Weight	9 Kg (2000 lumen 10.5 Kg (3000 lumen)
Max. Projected	Area 0.286 m ²
Battery Type	LiFePO4
PIR Sensor	Available
Luminiare CCT	5000 K- 6500 K


Installation Instructions




Remove shrink wrap and protective cover before installation.




Mount the luminaire with pole, tighten the bolts with torque of 8 Nm.




For vertical mounting unscrew and remove pole mounting bracket and assemble it as shown in Fig. B.



For tilt mounting to suit various geography, luminaire can be tilt mounted from 0 to 15 deg



For accurate angle positioning, match pole marks mounting piece marking with luminaire marking



To switch ON the luminaire press the switch button shown in below figure.

Precaution:

- 1. Maximum installation height luminaire from gorund is 5meters.
- 2. Before installation check if luminaire is glowing by pressing the switch on housing.
- 3. After three months of manufacturing, check if luminaire is the glowing (by switch), if it is not working then contact customer care.
- 4. This luminaire will not operate below 0 degree ambient.

