



by  **Signify**

Garage & Canopy

SoftView

SVPG Parking garage luminaire



Parking with confidence

Gardco SoftView LED parking garage luminaires use indirect illumination and upright to reduce glare and eliminate the cave effect so that your patrons can feel comfortably secure. Utilizing LED technology reduces energy and maintenance costs compared to conventional technologies, and savings are further enhanced through a variety of dimming and control options.



SVPG SoftView

Parking garage luminaire



Features and benefits

- Comfort optics create soft, uniform illumination that increases visual comfort without compromising performance or exposing viewers to harsh glare
- Uplight directed onto the ceiling eliminates cave effect
- Achieves up to 148 LPW for lower energy costs even during constant operation
- A variety of lumen packages available, with output ranging from approximately 2,000–17,900 lumens
- Four distribution patterns are available to create your ideal parking garage environment
- A full range of color temperatures, 80CRI options available for parking garage and low bay applications
- Long LED life reduces maintenance time and expenses compared to conventional technologies
- Added flexibility and further enhance savings through optional controls, including 0-10V dimming, motion response and Wireless controls

Ordering guide

example: SVPG-140L-2100-NW-G2-SM-5-120-BL-IMRI2-MGY

Luminaire	Number of LEDs	Drive Current	Color Temperature	Mounting	Distribution	Emergency	Voltage	Options				
								Dimming controls	Sensing	Electrical	Finish	
SVPG												
SVPG SoftView Parking Garage	140L 140 LEDs (comfort engine)	450 450mA 800 800mA 1200 1200mA 1675 1675mA 2100 2100mA	WW-G2 Warm White 3000K (70 CRI) Generation 2 NW-G2 Neutral White 4000K (70 CRI) Generation 2 CW-G2 Cool White 5000K (70 CRI) Generation 2 BW-G2 Balanced White 3500K (80 CRI) Generation 2 830-G2 3000K (80CRI) Generation 2 840-G2 4000K (80CRI) Generation 2	SM Surface / indirect pendant Mount, Normal vibration rated (pendant and junction box by others) SBO Surface Mount, Bridge / Overpass vibration rated PM Direct Pendant Mount, Bridge / Overpass vibration rated (pendant and junction box by others) T Trunnion Mount (must also order separate line item TM mounting kit, see Accessories) WM Wall Mount (must also order separate line item WM mounting kit, see Accessories)	1R Type IR Rectangular 3 Type III Asymmetric 5 Type V CD Concentrated Downlight	none leave blank EBP Emergency Battery pack EBPC Emergency Battery pack cold rated	120 120V 208 208V 240 240V 277 277V UNV Universal 120-277V 347 347V 480 480V HVV Universal 347-480V	none leave blank DD 0-10V Dimming external leads (controls by others) BL Bi-level with motion sensor LLC Wireless Controls	none leave blank IMRI2 Integral Motion Response, #2 lens IMRI3 Integral Motion Response, #3 lens IMRI7 Integral Motion Response, #7 lens (factory customizable, contact factory)	Fusing none leave blank F1 Single Fuse (120, 277, 347V) F2 Double Fuse (208, 240, 480V) F3 Double Fuse Canadian double pull (208, 240, 480V) Surge Protection blank SP1 10KV 10KA (standard) SP2 20KV 10KA (option)	BZ Bronze MGY Medium Gray WH White OC Optional Color Specify optional color or RAL ex: OC-LGP or OC-RAL7024. SC Special Color Must supply color chip. Requires factory quote.	

Accessories (ordered separately)

FSIR-100 Hand-held programmer (For use with 'IMRI2' and 'IMRI3' motion response when field programming is required). If desired, only one is needed per job.

ES External House Side Shield (field installed)

WG Wire Guard (field installed)

SVPG-G2-TM-(F) Trunnion Mount kit (field installed)

SVPG-G2-WM-(F) Wall Mount (field installed)

(F) = specify finish

BXC Bird excluding coil (field installed, fits on all mounting options)

BXK Bird excluding spikes (field installed, fits on Pendant, Trunnion, and Wall mounts only)

BXS Bird excluding shroud (field installed, fits on Pendant mount only)

Prior to ordering, consult specification sheets on gardcolighting.com for the most current information, notes, and exclusions.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

