

Stonco

by @signify

Garage & Canopy

General purpose lights

GC20/GC40/GC57/GC88



Compact & efficient, built to last

The Stonco LED Garage and Canopy light is slim and durable with a light-weight design, and provides you with a visually appealing lighting experience.

This luminaire can be surface mounted directly to the ceiling or pendant mounted using rigid conduit. Its light-weight design with quick and easy mounting plate allows simple installation and hands-free wiring. Whether it's new construction, or a retrofit installation, the Garage and Canopy light will provide years of trouble free operation and keep you on budget.

A perfect solution to replace up to 150W HID luminaires with the added benefit of low maintenance*.


*Based on comparison between 150W PSMH luminaires and GC88-NW-G1-SM-5-8-BZ per delivered lumens and in-situ application layout comparisons.



GC LED Garage & Canopy lights



- Cost-effective and efficient lighting for parking garages, covered walkways and canopies.
- Great choice for new construction or retrofit installation.
- Slim and compact design.
- Durable, weather-tight IP66 rated construction with a rugged, UV stabilized, frosted lens.
- Easy to install with the integral quick-mount plate, or pendant mount with 3/4" rigid conduit.
- 5 year limited warranty.



Ordering guide

Example: GC57-NW-G1-SM-5-8-BZ

Luminaire	LED Color	Generation	Mounting	Distribution	Voltage	Finish
	NW	G1	SM	5	8	BZ
GC20 Garage & Canopy LED 20W	NW Neutral White 4000K, 70CRI	G1 Generation 1	SM Surface Mount	5 Type 5 Symmetric	8 120-277VAC	BZ Bronze
GC40 Garage & Canopy LED 40W						
GC57 Garage & Canopy LED 57W						
GC88 Garage & Canopy LED 88W						

Performance data

Catalog Code	Lumens
GC20-NW-G1-SM-5-8-BZ	2071
GC40-NW-G1-SM-5-8-BZ	4735
GC57-NW-G1-SM-5-8-BZ	6322
GC88-NW-G1-SM-5-8-BZ	10,519

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

