




Distance between movement detectors for optimal coverage

Maximum cable lenght between linesens and last movement detector: 70m
Recomendation for mounting height of 5 m and lenght 70m light line: 1 linsens+8 movement detectors
Recomendation for mounting height of 15 m and lenght 70m light line: 1 linsens+3 movement detectors






Remark:
it is possible to mount the sensor with bracket only on an empty unit in light line (LL121X..BC or LL122X...)



LL120Z LCB

Mounting instructions

Instructions de montage	Instrucciones de montaje	Kokoonpano- ja kiinnitysohjeet	Návod k montáži
Montageanleitung	Instruções de montagem	Montaj yönergesi	Návod k montáži
Montage instructie	Monteringsinstruktioner	Szerelési utasítások	
Istruzioni di montaggio	Monteringsvejledning	Instrukcja montażu	




- LineSense Dim (DALI) with 9 wires
- LineSense Dim (DALI) with 7 wires
- Movement Detector

Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei
Demonteren voor onderhoud
Togliere tensione prima di fare manutenzione
Desconectar antes de manipular
Bryt strömmen före lampbyte

12NC 4427 101 59720
Versiondate: 23/03/2015
Data subject to change without notice
Printed in Poland
www.philips.com/lighting

PHILIPS



1

2 3

4

5 6

7

LI120Z LCB 7

8

LL120Z LCB 9

8

9 10 11 12

12

RJ-12 (6p/6c)

1 2 3 4 5 6

Pin/Core	Colour wire	Function
1	White	+12V supply
2	Black	Common
3	Red	
4	Green	
5	Yellow	
6	Blue	Signal

AWG 26

RJ-12 (6p/6c)

1 2 3 4 5 6

RJ-12 cable to be ordered separately

Time delay

On

1 2 3 4

LED

PHILIPS

default

1 2 3 = 1 min.

1 2 3 = 5 min.

1 2 3 = 10 min.

1 2 3 = 15 min.

1 2 3 = 20 min.

1 2 3 = 25 min.

1 2 3 = 30 min.

1 2 3 = 35 min.

4 + = default

4 + =