


PHILIPS

LUXSPACE2 Square

DN572B



50Hz
60Hz



GLOW
WIRE
850 °C












220V
240V




Model	Lumen package	Color Temperature [K]	 kg
	LED12S	830/840/927/930/940	1,17
DN572B	LED20S	830/840/927/930/940	1,17
	LED24S	830/840/927/930/940	1,17


Product info







DALI dimming range 1-100%



	Xtanium 20W/m 0.15- 0.5A 54V 230V	Xtanium 36W/m 0.3- 1.05A 54V 230V	Xtanium 20W WH 0.15-0.5A 54V Is	Xtanium 36W WH 0.3- 1.05A 54V Is	Xtanium 20W WH 0.15-0.5A 54V TD/Is CL	Xtanium 36W WH 0.3- 1A 54V TD/Is CL	XITANIUM 36W/M 0.3- 1.05A 54V TD 230V
Inom (A)	0.12	0.2	0.11	0.19	0.11	0.19	0.2
Imax (A)	18	18	15.8	16	20.4	20.4	18
Tref (μs)	250	250	224	216	195	195	250
MCB	Max number of drivers						
B-10A	x21	x21	x21	x21	x15	x15	x21
B-16A	x34	x34	x36	x36	x24	x24	x34
C-10A	x34	x34	x34	x34	x24	x24	x34

CLO Version

		CCT/CRI	Pmax (W)	Pmax (W)
			@ t=0h	@ t=50kh
DN572B	LED12S	830/840	9	11
DN572B	LED12S	927/930	10	13
DN572B	LED20S	830/840	14	17,6
DN572B	LED20S	927/930	17	21,8
DN572B	LED24S	830/840	17	21,8
DN572B	LED24S	927/930	21	26,8

CLO Table		
Step	time (h)	P %
0	0	80%
1	3000	81%
2	7000	83%
3	10000	84%
4	13000	85%
5	17000	87%
6	20000	88%
7	23000	89%
8	27000	91%
9	30000	92%
10	33000	93%
11	37000	95%
12	40000	96%
13	43000	97%
14	47000	99%
15	50000	100%



DO NOT REPROGRAM THE DRIVER
Constant light Output Option stopped @ 50 000h



DO NOT REPROGRAM THE DRIVER

Constant light Output Option stopped @ 50 000h

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person

© 2018 Signify Holding.

All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding.
The Netherlands