



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: B_4 N A S

Product Code	B_4	HID Aluminum Bullyte	
Reflector	N	Narrow Reflector	*1
	W	Wide Reflector	*1
Finish	A	Black	
	H	Bronze	

Specifications

HOUSING:

Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. Gasketing is silicone. Fasteners are 300 series stainless steel. Fully rotatable shroud, gasketed die-cast brass. Shroud is optional. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

OPTICAL ASSEMBLY:

Clear tempered flat glass lens.

LAMPING:

150W maximum PAR38/R40 incandescent lamp. HID PAR38 MH or MV acceptable with remote ballast (not included). 150 watt maximum HID lamp. Lamp is not included. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

BALLAST:

Must order inground (IBH) or above ground (ABH) ballast housing separately.

CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations.

WARRANTY:

Three-year limited warranty.

Height :	Width:	Length:	Max. Weight:
2 5/16" (59mm)	6 1/4" (159mm)	16 1/2" (419mm)	8.15 lb.

