






























Housing	Lumen package	Color temperature [K]	kg	CoB type	Driver type	
ST712T	LED17S	PW9-3000	0,52	1203 L2C5	PSU	_
TrueFashion					5011	_
Compact	LED20S	PW9-3500	0,52	1203 L2C5	PSU	_
Driver-in-Track		PW9-4000	0,52	1203 L2C5	PSU	_
	LED24S	PW9-3000	0,61	1208 L2C5	PSU	Product Info Label
						-
	LED27S	PW9-3500	0,61	1208 L2C5	PSU	-
	LED27S	W9-4000	0,61	1208 L2C5	PSU	



























CA/TRACK ADAPTER GA17 DRIVER IN TRACK					
Ipeak [A]	5				
Tref[us]	50				
MCB	Max products pcs *				
B -1 6AtypeB	50				











LUIMNAIRES MUST BE INSTALLED OUT OF ARM REACH DISTANCE/HEIGHT!

THE SPOT HEAD CAN BE PERCEIVED AS HOT.

ADJUST THE SPOTHEAD AFTER THE LUMINAIRE IS COOLED DOWN OR WHEN USING HEAT INSULATING GLOVES.

LUMINAIRE CAN NOT BE OPENED, LIGHTSOURCE CANOT BE REPLACED!

