



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: IF2 26 G H

Product Code	IF2	Fluorescent
<b>Wattage</b>	26	26W CFL
	32	32W CFL
	18	18W CFL
<b>Rock Guard</b>	G	Rock Guard *1
<b>Finish</b>	H	Bronze
	N	Natural Brass
	SS	Stainless steel (MATTE FINISH)

\*1 Rock guard is optional and available in bronze and natural brass only.

### Specifications

#### HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Trim ring is a compression molded polyester. Rock guard used for directional glare control made of compression molded polyester.

#### FINISH:

Composite is textured, pressure formed, molded-in-color.

#### OPTICAL ASSEMBLY:

Clear convex, tempered soda-lime glass for high impact resistance. 2,200-pound live-load rated, standard walk-over lens.

#### LAMPING:

Lamp is not included. Lower wattage lamps are acceptable.

#### ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact. 26W Fluorescent socket is a GX24Q-3 base. 32W Fluorescent socket is a GX24Q-3 base. 18W Fluorescent is a GX24q-2 socket.

#### WARRANTY:

Ten-year limited warranty.

#### CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. ADA Compliant when flush mounted with CP2 or CPS2.

**Height :** 8 1/4" (210mm)      **Width:** 6 5/8" (169mm)      **Max. Weight:** 3.45 lb.

