


Anchor Base Post (401-) Specification Sheet

Project Name:	Location:	MFG: Philips Lighting
Fixture Type:	Catalog No.:	Qty:



Ordering Guide

Example: 401- 96 ABS B B

Product Code	401-	Anchor Base Post
Height(s)	96 116	(9 1/2 ft.) (11 1/2 ft.)
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Photoeye (Optional)	B C	120V 208V - 277V
Outlet Location (Optional)	B T	4" from Top of Base 12" from Top of Pole

Specifications

CONSTRUCTION:

Cast aluminum round anchor base. Cast aluminum removable access door. Fluted Tapered post welded to base.

Anchor Base Post (401-) Specification Sheet

Project Name:	Location:	MFG: Philips Lighting
Fixture Type:	Catalog No.:	Qty:

FINISH:
Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

WARRANTY:
Three-year limited warranty.

Tenon/Top:
3" O.D.

Bolt Circle:
7" dia.

Anchor Rods:
(4) 1/2" dia. x 18" long zinc plated steel

Base Dimensions:
13 1/4" dia. x 11 1/8"

Shaft:
5" to 3" Fluted Tapered

Wall Thickness:
.250"

Height:
9 1/2', 11 1/2'

Pole EPA Values

Windspeed(mph)	Height	
	96'	116'
80	22.1000	17.2100
110	10.9400	8.1800
130	5.9800	3.9200