

# Stonco

by Signify

## Special Purpose

### Roughlyte

Ceiling and wall mounted,  
incandescent



VCXL



VWXL

Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

Stonco Roughlyte is available in wattages ranging from 60 to 200. Applications include wall, columns, ceilings and canopies in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

### Ordering guide

Example: VCXL11GC

| Series                                | Wattage                      | Lens  |
|---------------------------------------|------------------------------|---|
| <b>VCXL</b><br>Ceiling 4" box mounted | <b>11</b><br>100W            | <b>GC<sup>1</sup></b><br>Glass globe and cast guard |
| <b>VWXL</b><br>Wall 4" box mounted    | <b>21</b><br>200W            | <b>A<sup>2</sup></b><br>Lexan globe                 |
|                                       | <b>5<sup>1</sup></b><br>60W  |   |
|                                       | <b>10<sup>1</sup></b><br>75W |   |

1. For use with 100W and 200W units only.
2. 60W and 75W available with lexan globe only.

### Product Specifications

- All incandescent Roughlyte ceiling and wall fixtures are not supplied with a lamp. This fixture requires a medium base incandescent A lamp. The lamp can be clear or coated.
- Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only).
- cULus listed for wet locations.
- **Not recommended for use in hazardous locations.**

# VCXL/VWXL Roughlyte ceiling and wall mounted


## VCXL/VWXL

- Complete with 4" die-cast aluminum box, four side and top hole tapped 1/2" NPT (four plugs included).
- Heat and shock resistant glass or polycarbonate globe.
- Sockets are pre-wired with extra long 1/2" stripped leads.
- To use VCXL units with 3/4" conduit use VK Series with VXL13 universal box.
- To use VWXL units with 3/4" conduit, use VW Series with VXL13 universal box.


## Dimensions

**Catalog No.**      **Height (H)**      **Dia. (D)**

|          |         |        |
|----------|---------|--------|
| VCXL11GC | 9-1/8"  | 4-1/4" |
| VCXL21GC | 10-7/8" | 5-1/4" |
| VCXL5A   | 8-5/8"  | 4-1/4" |
| VCXL10A  | 10-3/8" | 5-1/8" |



|          |         |         |
|----------|---------|---------|
| VWXL11GC | 9-3/4"  | 7-1/4"  |
| VWXL21GC | 11-3/8" | 7-1/2"  |
| VWXL5A   | 9-1/4"  | 7-1/8"  |
| VWXL10A  | 10-7/8" | 7-7/16" |



## Accessories



V131

Cast Aluminum Guard

### Guards

Cast aluminum guards are twist on/off bayonet type, includes allen head security screws. Shipped with threaded ring adapter for use with standard threaded bases or the new RoughLyte bases.

| Catalog No. | Cast guard<br>Fits globe diameter |
|-------------|-----------------------------------|
| V131        | 3-1/2"                            |

### Colored and specialty globes

Full molded threads. Fit all Stonco housings. Globes for vertical mounting only.

| Catalog No.                                    | Description                 | Catalog No.                                  | Description                 |
|--|-----------------------------|--|-----------------------------|
| <b>3-1/2" Globe dia.<br/>Height - 6 11/16"</b> |                             | <b>4-3/8" Globe dia.<br/>Height - 8 3/8"</b> |                             |
| VGC100   | Clear*                      | VGC200                                       | Clear*                      |
| VGP100   | Clear, prismatic            |  |                             |
| VGA100   | Amber (60W max.)            |  |                             |
| VGB100   | Blue (60W max.)             |  |                             |
| VGR100   | Ruby (60W max.)             |  |                             |
| <b>3-1/2" Globe dia.      LEXAN</b>            |                             | <b>4-3/8" Globe dia.      LEXAN</b>          |                             |
| VPRC5  | Clear, prismatic (60W Max.) | VPRC10                                       | Clear, prismatic (75W Max.) |

\*Standard with all incandescent glass fixtures.

**NOTE:** Use of colored globes will down-rate wattage.



VGC100

Clear Glass Globe



VGP100

Clear Prismatic Globe



VGR100

Ruby Glass Globe



VPRC10

Prismatic Lexan Globe

