





Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

VWXL

Stonco Roughlyte is available in wattages ranging from 60 to 200. Applications include wall, columns, ceilings and canopies in exterior applications. Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only). Features include heat and shock resistant glass or polycarbonate globe and cast aluminum bayonet guard with Allen head security screws. Not recommended for hazardous locations.

Ordering guide Example: VCXL11GC

Series	Wattage	Lens
VCXL Ceiling 4" box mounted	11 100W	GC¹ Glass globe and cast guard
VWXL Wall 4" box mounted	21 200W 5 ¹ 60W	A ² Lexan globe
	10 ¹ 75W	

- 1. For use with 100W and 200W units only.
- 2. 60W and 75W available with lexan globe only.

Product Specifications

- All incandescent Roughlyte ceiling and wall fixtures are not supplied with a lamp. This fixture requires a medium base incandescent A lamp. The lamp can be clear or coated.
- Roughlyte fixtures guard against moisture and debris in exterior applications (for globe down mounting only).
- cULus listed for wet locations.
- · Not recommended for use in hazardous locations.



VCXL/VWXL Roughlyte ceiling and wall mounted


VCXL/VWXL


- · Complete with 4" die-cast aluminum box, four side and top hole tapped 1/2" NPT (four
- · Heat and shock resistant glass or polycarbonate globe.
- Sockets are pre-wired with extra long 1/2" stripped leads.
- To use VCXL units with 3/4" conduit use VK Series with VXL13 universal box.
- To use VWXL units with 3/4" conduit, use VW Series with VXL13 universal box.

Dimensions

Catalog No.	Height (H)	Dia. (D)
VCXL11GC	9-1/8"	4-1/4"
VCXL21GC	10-7/8"	5-1/4"
VCXL5A	8-5/8"	4-1/4"
VCXL10A	10-3/8"	5-1/8"

VWXL11GC	9-3/4"	7-1/4"
VWXL21GC	11-3/8"	7-1/2"
VWXL5A	9-1/4"	7-1/8"
VWXL10A	10-7/8"	7-7/16"





Accessories



V131 Cast Aluminum Guard

Guards

Cast aluminum guards are twist on/off bayonet type, includes allen head security screws. Shipped with threaded ring adapter for use with standard threaded bases or the new RoughLyte bases.

Cast guard		
Catalog No. Fits globe diameter		
V131	3-1/2"	



VGC100 Clear Glass Globe



VGP100



VGR100 Ruby Glass Globe



Clear Prismatic Globe



VPRC10 Prismatic Lexan Globe

Colored and specialty globes

Full molded threads. Fit all Stonco housings. Globes for vertical mounting only.

Catalog No.	Description	Catalog No.	Description
3-1/2" Globe dia. Height - 6 11/16"	Glass	4-3/8" Globe dia. Height - 8 3/8"	Glass
VGC100	Clear*	VGC200	Clear*
VGP100	Clear, prismatic		
VGA100	Amber (60W max.)		
VGB100	Blue (60W max.)		
VGR100	Ruby (60W max.)		
3-1/2" Globe dia.	LEXAN	4-3/8" Globe dia.	LEXAN
VPRC5	Clear, prismatic (60W Max.)	VPRC10	Clear, prismatic (75W Max.)

^{*}Standard with all incandescent glass fixtures. NOTE: Use of colored globes will down-rate wattage.

