

Stonco

by @signify

Floodlights

Slim flood

TF10/30/50/100/150/200



Illuminate with style

The Stonco LED Slim flood is your best value for discreet and modern design on your floodlighting projects.

Versatile and stylish with six different sizes to choose from, Slim flood provides application flexibility for ground, wall, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications. The discreet low profile design will not interfere with your landscape layouts.

Energy savings don't get better than this – up to 85% savings compared to HID*.

* Based on comparison between 50W PSMH luminaires (at 68W) and TF10-NW-G1-K-FL-8-BZ (at 10W).



Slim flood LED

Shine light where you need it

- Complete family of LED floodlights ideal for illuminating signs, building facades or other dark areas.
- Can be mounted on the ground, wall, or pole-mounted.
- Low profile design with durable construction
- All sizes arrive fully assembled and ready to install. All sizes have a yoke mount and the three smaller sizes have a unique Yoke/Knuckle combo mount.
- Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant.
- IP65 rated.



Ordering guide


example: TF200-NW-G1-Y-FL-8-BZ

Luminaire	LED Color	Generation	Mounting	Distribution	Voltage	Finish
		G1		FL	8	BZ
TF10 LED SlimFlood 10W	WW³ Warm White 3000, 80CRI	G1 Generation 1	K¹ Knuckle (½" NPS male) and Yoke Mount combination	FL Flood	8 120-277VAC	BZ Bronze
TF30 LED SlimFlood 30W	NW Neutral White 4000K, 80CRI					
TF50 LED SlimFlood 50W	CW Cool White 5000K, 80CRI					
TF100 LED SlimFlood 100W	NW Neutral White 4000K, 80CRI		Y² Yoke Mount only			
TF150 LED SlimFlood 150W	CW Cool White 5000K, 80CRI					
TF200 LED SlimFlood 200W						

1. K Knuckle Mount and Yoke Mount combination available with TF10 / TF30 / TF50.

2. Y Yoke Mount only available with TF100 / TF150 / TF200.

3. WW Warm White only available with TF10 / TF30 / TF50.



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.