

# HADCO


by @signify

## Landscape

### Floodlyte

#### WBMT14 Aluminum

Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_



### Ordering Guide

Example: WBMT14 F A

Product Code	WBMT14	Aluminum Floodlyte
Lens	F	Frosted Lens *1
Finish	A	Black
	H	Bronze

\*1 Frosted lens is optional.

### Specifications

#### HOUSING:

Die-cast aluminum. Gasketing is silicone. Fully-adjustable swivel arm with vibration-proof locking teeth. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

#### OPTICAL ASSEMBLY:

Clear tempered glass lens. Frosted tempered glass lens.

#### LAMPING:

50W maximum T4 halogen. Lamp is included with fixture. Lower wattage lamps are acceptable.

#### ELECTRICAL ASSEMBLY:

Bi-pin socket type (GY6.35) with 250° C high temperature teflon coated wire leads. Fixture is pre-wired with 18 AWG black, white, and ground wires. Step-down transformer reduces line voltage to 12 volts. Transformer is potted/encapsulated and features thermal overload protection. Can be used with energy-efficient halogen lamp.

#### WARRANTY:

Three-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

#### Height :

7 7/16" (189mm)

#### Width:

6 7/8" (175mm)

#### Length:

3 7/16" (128mm)

#### Max. Weight:

2.57 lb.

# @signify