

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: P295 12 A T D

Product Code	P295	
Pole Height	12	12'
	14	14'
	15	15'
	16	16'
	18	18'
	20	20'
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	I	Gray
	J	Green
Outlet Location (Optional)	T	12" Down from Top - Aligned with House Side
Outlet Options (Optional)	D	Standard Duplex
	G	GFI Duplex

Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . Die-cast aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel .

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P295 P295

Pole

Specifications

Tenon/Top:

4" SQ

Bolt Circle:

9 1/2"

Anchor Rods:

(4) 3/4" dia. x 19"

Base Dimensions:

11 1/2" sq. x 2 "

Base Cover:

(Included) 17 5/16" x 3 1/4"

Hand Hole :

2" x 4" Oval

Shaft:

4" Straight

Wall Thickness:

0.188 Aluminum

Height :

12', 14', 15', 16', 18', 20'

Pole EPA Values

Windspeed(mph)	Height					
	12'	14'	15'	16'	18'	20'
80	17.5200	11.5600	10.2100	9.4900	7.7400	6.2300
100	10.2900	6.5200	5.6500	5.0200	3.7300	2.6000

