

Made from a seamless 4" round 8 fluted (102 mm) extruded-aluminum shaft welded to a decorative cast-aluminum base incorporating an anchor plate. A 4" by 9" (102 by 229 mm) maintenance opening is complete with cover and copper ground lug. The pole comes with cast-aluminum bolt covers.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

example: R80A-12-BA-BKTX

Pole Family	Wall Thickness	Nominal Height	Options	Finish
R80A				
R80A	0.167"	8 8'	LS Provision for loudspeaker outlet	BE2TX Midnight Blue Textured
		10 10'	PH7 Button-type photoelectric cell (specify operating voltage)	BE6TX Ocean Blue Textured
		12 12'	PH8 Quarter-turn type photoelectric cell (specify operating voltage)	BE8TX Royal Blue Textured
		14 14'	DR Duplex receptacle (120V line voltage, only)	BG2TX Sandstone Gold Textured
		15 15'	GFI DR with common ground fault interrupter (120V line voltage only)	BKTX Black Textured
		16 16'	BA Banner arm	BRTX Bronze Textured
		18 18'	PS Plant support	GN4TX Blue Green Textured
			MPL Mid-pole luminaire	GN6TX Forest Green Textured
			Two-piece round decorative base cover:	GN8TX Dark Forest Green Textured
			TBC1 Round cast-aluminum	GNTX Green Textured
			TBC2 Cast-aluminum hexagonal	GY3TX Medium Grey Textured
				RD2TX Burgundy Textured
				RD4TX Scarlet Textured
				WHTX White Textured
				GR Gray Sandtex
				NP Natural Alum.
				TG Hammer-tone
				TS Hammer-tone Silver

Note: The recommended method for calculating EPA (Effective Projected Area) is in accordance with AASHTO 2001 standards: for three seconds, the pole is tested in wind gusts equivalent to the strongest winds on record over the past 50 years, and with a 50 pound load (22.7 kg) placed at 1 foot (305 mm) above its center.

Important: Do not obstruct space between anchor plate and concrete base.

Outdoor Poles and Brackets

R80A – Traditional Aluminum Pole

Pole Data

Pole Family	Catalog Number	Nominal Height (ft)	Nominal Height (m)	Tenon Section (in)	Tenon Section (mm)	Wall Thickness (in)	Wall Thickness (mm)	Weight (lbs)	Weight (kg)	EPA Rating 90 MPH (sq. ft.)	EPA Rating 110 MPH (sq. ft.)	EPA Rating 120 MPH (sq. ft.)	EPA Rating 150 MPH (sq. ft.)	Anchor Bolts (in)	Anchor Bolts (mm)
R80A	R80A-8	8	2.44	4	102	0.167	4.2	60	27	21.84	14.69	12.32	7.81	3/4-20	19-508
R80A	R80A-10	10	3.05	4	102	0.167	4.2	63	29	15.96	10.53	8.74	5.38	3/4-20	19-508
R80A	R80A-12	12	3.66	4	102	0.167	4.2	67	30	12.13	7.78	6.35	3.76	3/4-20	19-508
R80A	R80A-14	14	4.27	4	102	0.167	4.2	70	32	9.42	5.79	4.61	2.54	3/4-20	19-508
R80A	R80A-15	15	4.57	4	102	0.167	4.2	73	33	8.31	4.99	3.91	2.04	3/4-20	19-508
R80A	R80A-16	16	4.88	4	102	0.167	4.2	75	34	7.37	4.28	3.29	1.58	3/4-20	19-508
R80A	R80A-18	18	5.49	4	102	0.167	4.2	78	36	5.59	2.97	2.13	-	3/4-27	19-686

Specifications


Finish

Color to be in accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with ± 1 mils/24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard.

Outdoor Poles and Brackets

R80A – Traditional Aluminum Pole

Dimensions



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.