



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: IL116 G H LED7 NF W

Product Code	IL116	LED Composite Inground	
Rock Guard	G	Rock Guard	*2
Finish	H	Bronze	
	N	Natural Brass	*1
Source/Lumens	LED7	7W LED	
Optics	NF	Narrow Flood	
	FL	Flood	
CCT	W	Warm	

*1 Natural Cast Bronze
 *2 Rock Guard is not available in stainless steel.
 *3 Fixture will be shipped with lamp. Lamp not sold separately.

Specifications

HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Trim ring is a compression molded polyester.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Clear convex, tempered soda-lime glass for high impact resistance. 2,200-pound live-load rated, standard walk-over lens. Lamps have 15° articulation either side of vertical and 358° rotation without interruption of beam pattern.

LAMPING:

7W lamp with 25° or 35° beam spread, 25,000 hours life. Color temperature (CCT): Warm White (3,000K nominal). No Mercury. Dimmable. Approximately 460 lumens.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Five-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. ADA Compliant when flush mounted with CP2 or CPS2.

Height : 8 7/16" (214mm) **Width:** 6 5/8" (169mm) **Max. Weight:** 3.5 lb

