

Technical Data and Lamp Matrix												
Lamp Wattage	Lamp Type	Product description	12NC	Input power (W)	Lamp power (W)	Ploss (W)	THD (%)	Power Factor	EI	Tc Point Max.	Ambient Temperature Ta	BLF
1x39W	TL5	HF-R 139 TL5 EI	913700632966	43	35	4,00	5,00	0,98	A1 BAT	75°C	-20 °C to +50 °C	1,2
1x40W	PL-L			46	41	5,00	4,40	0,96	A1 BAT	75°C	-20 °C to +50 °C	1,02

