

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 201 3 V ABS A B WHT 12

Product Code	201	Street Sign
Fitter Size	3 4 5	3" Round 4" Round 5" Round
Lettering	V	Vinyl
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Print	A B N	Single Sided Double Sided None
Vinyl Lettering Style	B	Block *1
Letter Color	WHT	White
Wording	12	Spaces (12)

*1 Vinyl Lettering Style Only

Specifications

CONSTRUCTION:

Turned aluminum knob. Stamped aluminum 30" x 9" sign attached to arm with cast aluminum clamp-on brackets. (Sign has 29" x 7" lettering area on both sides.) Solid cast aluminum ladder rest. Engineer grade reflective green vinyl both sides. Vinyl number and/or letter both sides.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

Clamps onto a 3", 4" or 5" dia. post. (Post must be ordered separately.)

WARRANTY:

Three-year limited warranty.

201 Accessories

Street sign

Specifications

Height:

11"

Width:

40 1/2"

