



Dimensions



BRP 340


Street Lighting Luminaire



Type	:	BRP 340
Lamp	:	LED
Voltage	:	240 V, 50 Hz
IP Classification	:	IP 66
Net Weight	:	4 kgs
Max. Projected Area	:	0.106 m ²
Application	:	Outdoor use only


4415 109 21660

Installation




BRP 340


Mounting Position: Horizontal
Application height: 7-11m
Suitable Cable Diameter: 8-12mm
Pole Size: 48-60mm diameter




1 Take the product out of the packing box.




2 Open the rear cover by screw driver as shown.




3 Open the rear Cover as shown.




4 Allow the incoming cable to pass through the gland and tighten it with spanner




5 Fix the street light over the pole and tighten the bolts. Tightening Torque: 8Nm




7 Make the electrical connections as per the LN marking




9 Remove the polythene over front diffuser.




11 CAUTION: Do not open front cover



8 Fix the rear cover using the screw driver as shown.



10 Luminaire is ready for use.



12 CAUTION: Broken Glass/ front diffusers should be immediately replaced.

