

PHILIPS

GreenSpace Gen 5

Downlight



The **Energy-Efficient** retrofit commercial downlight

The new GreenSpace Gen 5 range comes packed with all the performance and solutions for most retrofit projects in the commercial space. With the new InterAct platform, the perfect smart solutions are simple and fuss free.

Features and benefits

- Connected lighting options
- Excellent light quality with multiple cut-outs and sizes
- IP54 options available for outdoor under canopy installation
- Comprehensive range, from 650-2200lms, three cut out sizes and two colour temperatures. Available in white and aluminium reflector choices.
- Easy to install, comes with 1.2m flex and plug


Product data

Model	GreenSpace Gen 5			
Type	DN390B	DN391B	DN392B	DN393B
Equivalent of	2 x13W CFL	2X18W CFL	2X26W CFL	2X32W CFL
System wattage	Fixed - 5.5W DALI - 8W	Fixed - 9.5W DALI - 11.5W	Fixed - 14.5W DALI - 15.5W	Fixed - 19W DALI - 20.5W
System lumen	D105 - 650lm	D150 - 1150lm	D150 - 1650lm D200 - 1650lm	D200 - 2200lm
Power factor	0.9			
CCT	3000K (WW), 4000K (NW)			
CRI	>80			
SDCM	<5			
UGR	22 - 25			
Beam Angle	80° (White reflector), 60° (Aluminium coated reflector)			
Operating Temperature	25°C (0 - 40°C)			
Lifetime	50,000 (L70)*			
Driver/ Systems	Fixed output (PSU), DALI (PSD), InterAct Office Pro (IAR)**, Coded light (PSD-VLC)***			
IP rating	IP20, IP54 (WP)			
Insulation Rating	CA90			
Electrical Class	Class I			
Input Voltage	220V-240V, 50/60Hz			
Mounting Type	Recessed			
Housing colour	White powder coated (RAL9003)			
Material	Diffuser: PC Reflector type: high reflectance painted plastic (White or ALU coating) Housing: PC and die cast aluminium			
Application	Commercial buildings, general lighting, hospitality, healthcare			

*When a new fitting reaches 70% of full potential. **InterAct Office Pro (IAR) available in DN393B only

***Coded light (PSD-VLC) is available on Engineered to Order basis

Dimensions



Model	Cut-out/ (mm)	Height A (mm)	Diameter/ B (mm)	Weight (kg)
DN390B Fix	Ø 105-110	95	Ø 120	0.34
DN391B Fix/DALI	Ø 150-155	97	Ø 162	0.44/0.76
DN392B Fix/DALI	Ø 200-205	105	Ø 216	0.61/0.96
DN393B Fix/DALI	Ø 200-205	105	Ø 216	0.61/0.96
DN390B WP	Ø 105-110	98	Ø 120	0.39
DN391B WP	Ø 150-155	100	Ø 162	0.55
DN392B WP	Ø 200-205	108	Ø 216	0.78
DN393B WP	Ø 200-205	108	Ø 216	0.78

Dimensions shown above are nominal measurement. Slight variation in dimension may occur in production.

Order Placement Information

12NC	New Description	Specification
911401582841	DN390B LED6/830 PSU D100 WH CAU	5.5W,600lm,3000K,Fixed out-put,cut-out : 100mm,White reflector
911401582941	DN390B LED6/840 PSU D100 WH CAU	5.5W,600lm,4000K,Fixed out-put,cut-out : 100mm,White reflector
911401583041	DN391B LED11/830 PSU D150 WH CAU	9.5W,1100lm,3000K,Fixed out-put,cut-out : 150mm,White reflector
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	9.5W,1100lm,3000K,Fixed out-put,cut-out : 150mm,White reflector,IP54
911401583141	DN391B LED11/840 PSU D150 WH CAU	9.5W,1100lm,4000K,Fixed out-put,cut-out : 150mm,White reflector
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	9.5W,1100lm,4000K,Fixed out-put,cut-out : 150mm,White reflector,IP54
824110148651	DN391B LED11/840 PSU D150 ALU CAU	9.5W,1100lm,4000K,Fixed out-put,cut-out : 150mm,Aluminium reflector
824110148661	DN391B LED11/840 PSU D150 ALU WP CAU	9.5W,1100lm,4000K,Fixed out-put,cut-out : 150mm,Aluminium reflector,IP54
824110148671	DN392B LED16/830 PSU D150 WH CAU	14.5W,1600lm,3000K,Fixed out-put,cut-out : 150mm,White reflector
824110148681	DN392B LED16/840 PSU D150 WH CAU	14.5W,1600lm,4000K,Fixed out-put,cut-out : 150mm,White reflector
824110148691	DN392B LED16/840 PSU D150 WH WP CAU	14.5W,1600lm,4000K,Fixed out-put,cut-out : 150mm,White reflector,IP54
824110148701	DN392B LED16/840 PSU D150 ALU CAU	14.5W,1600lm,4000K,Fixed out-put,cut-out : 150mm,Aluminium reflector
911401583441	DN393B LED22/830 PSU D200 WH CAU	19W,2200lm,3000K,Fixed out-put,cut-out : 200mm,White reflector
824110148711	DN393B LED22/830 PSU D200 ALU CAU	19W,2200lm,3000K,Fixed out-put,cut-out : 200mm,Aluminium reflector
911401583541	DN393B LED22/840 PSU D200 WH CAU	19W,2200lm,4000K,Fixed out-put,cut-out : 200mm,White reflector
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	19W,2200lm,4000K,Fixed out-put,cut-out : 200mm,White reflector, IP54
824110148721	DN393B LED22/840 PSU D200 ALU CAU	19W,2200lm,4000K,Fixed out-put,cut-out : 200mm,Aluminium reflector
824110148731	DN393B LED22/840 PSU D200 ALU WP CAU	19W,2200lm,4000K,Fixed out-put,cut-out : 200mm,Aluminium reflector,IP54
911401584241	DN391B LED11/830 PSD D150 WH CAU	9.5W,1100lm,3000K,Dali Dimming,cut-out : 150mm,White reflector
911401584341	DN391B LED11/840 PSD D150 WH CAU	9.5W,1100lm,4000K,Dali Dimming,cut-out : 150mm,White reflector
911401584541	DN391B LED11/840 PSD D150 ALU CAU	9.5W,1100lm,4000K,Dali Dimming,cut-out : 150mm,Aluminium reflector
911401585141	DN393B LED22/840 PSD D200 WH CAU	19W,2200lm,4000K,Dali Dimming,cut-out : 200mm,White reflector
911401585341	DN393B LED22/840 PSD D200 ALU CAU	19W,2200lm,4000K,Dali Dimming,cut-out : 200mm,Aluminium reflector
911401570641	DN393B LED22/840 IAR WH CAU	19W,2200lm,4000K,InterAct Pro Enabled,cut-out : 200mm,White reflector

© 2018 Koninklijke Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.

Version: 16 April 2018



Philips Lighting New Zealand
 Level 3, 123 Carlton Gore Road
 Newmarket, Auckland 1023
 New Zealand
 Ph: 0800 454 448 / 0800 4 LIGHT
connected.nz@philips.com
www.philips.co.nz/lighting